



PEL - Peloton™ High Performance High Bay

- 4000K and 5000K Color Choices
- 12,000, 18,000, and 24,000 Lumen Packages
- 150+ LPW
- Mounting Accessories and Wireguard
- DesignLights Consortium**



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 100

MODEL	CRI	LUMEN OUTPUT ¹	LENS	UPLIGHT	VOLTAGE	OPTIONS
PEL Peloton™ High Performance High Bay	Blank 80	LH Low Lumen Package / High Range, 8,000 (2FT ONLY) LX Low Lumen Package / Extra High Range, 12,000 (2FT ONLY)	FA Frosted Acrylic Blank No Lens	Blank No Uplight	U 120-277V	C6TL20_ 6' Cord and Twist-Lock™ Plug 20A (Add Voltage 1=120, 2=277) C6TL15_ 6' Cord and Twist-Lock™ Plug 15A (Add Voltage 1=120, 2=277) C6P151 6' Cord and Straight Blade Plug 15A, 120V
SIZE	COLOR TEMP	ML Medium Lumen Package / Low Range, 15,000 (2FT ONLY) MM Medium Lumen Package / Medium Range, 18,000 (2FT ONLY) MH Medium Lumen Package / High Range, 24,000 (2FT ONLY) MV Medium Lumen Package / Very High Range, 30,000 (4FT ONLY) MX Medium Lumen Package / Extra High Range, 36,000 (4FT ONLY)	EFFICACY Blank Standard Efficacy	DRIVER E Fixed Output ED 0-10V Dimming		F3C5 5', 3-Conductor Cord F4C5 5', 4-Conductor Cord WG Wire Guard ELL14 Emergency Battery Pack, 1400 Lumens, 10 watt
			DISTRIBUTION W Wide Distribution N Narrow Distribution			CONTROL OPTIONS OS1360 Factory Installed On/Off Occupancy/Daylight, Sensor, 1-relay, 360° lens 120/277 ¹

¹ OS1360/A sensor option will use [HCS Wasp2 surface mount sensor](#).

*DLC® (DesignLights Consortium) Qualified, with some Premium Qualified configurations. Please refer to the DLC website for specific product qualifications at www.designlights.org.