



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

LF4SQSL	DM1	WW	•	4SQSL	11L	35K	8	WW	WT	
HOUSING	DRIVER OPTIONS	HOUSING OPTIONS		TRIM APERTURE	OUTPUT	KELVIN	CRI	REFLECTOR OPTIONS	TRIM OPTIONS	LENS OPTIONS
LF4SQSL Standard Lumen 0-10V 10% dimming 120V-277V LF4SQML Medium Lumen 120V-277V 0-10V 10% dimming	<i>Standard 0-10V 10% Dimming</i> DM1 0-10V 1% dimming, 120-277V	EMR Emergency Battery Pack with remote test switch and indicator light WW Wall Wash		4SQSL Standard Lumen Semi-Diffuse Clear Alzak 4SQML Medium Lumen Semi-Diffuse Clear Alzak	11L 1100 Lumen Module 15L 1500 Lumen Module 20L 2000 Lumen Module 30L¹ 3000 Lumen Module	30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	WW² Wall Wash	WT Painted White Flange only	CL Regressed Clear Lens DL Regressed Diffuse Lens PL Regressed Prismatic Lens
								¹ 30L is only available with LF4SQML housing and 4SQML trim. ² Lens Options not available on WW. (WW comes standard with DL lens.)		