



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

LF6SL		DM1		EMR		6LFSL		20L		35K		8		REFLECTOR OPTIONS		WT	
HOUSING		DRIVER OPTIONS		HOUSING OPTIONS		TRIM APERTURE		OUTPUT		KELVIN		CRI		REFLECTOR OPTIONS		TRIM OPTIONS	
LF6SL	Standard Lumen 0-10V 10% dimming 120V-277V		<i>Standard 0-10V 10% Dimming</i>	EM	Emergency Battery Pack with integral test switch and indicator light	6LFSL	Standard Lumen Semi-Diffuse Clear Alzak	11L	1100 Lumen Module	30K	3000 Kelvin	8	80+ CRI	WW	Wall Wash	WT	Painted White Flange only
LF6ML	Medium Lumen 0-10V 10% dimming 120V-277V	DM1	0-10V 1% dimming, 120-277V	EMR	Emergency Battery Pack with remote test switch and indicator light	6LFML	Medium Lumen Semi-Diffuse Clear Alzak	15L	1500 Lumen Module	35K	3500 Kelvin	9	90+ CRI	EM	Integral Battery with pre-punched reflector		
								20L	2000 Lumen Module	40K	4000 Kelvin						
								30L¹	3000 Lumen Module								

¹ 30L is only available with LF6ML housing and 6LFML trim.