



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

LF6SQSL		DM1		•	6SQSL	11L	35K	8		WT	
HOUSING		DRIVER OPTIONS	HOUSING OPTIONS		TRIM APERTURE	OUTPUT	KELVIN	CRI	REFLECTOR OPTIONS	TRIM OPTIONS	LENS OPTIONS
LF6SQSL	Standard Lumen 0-10V 10% dimming 120V-277V	<i>Standard 0-10V 10% Dimming</i> DM1 0-10V 1% dimming, 120-277V	EM Emergency Battery Pack with integral test switch and indicator light	EMR Emergency Battery Pack with remote test switch and indicator light	6SQSL Standard Lumen Semi-Diffuse Clear Alzak	11L 1100 Lumen Module 15L 1500 Lumen Module 20L 2000 Lumen Module 30L ² 3000 Lumen Module	30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	WW ¹ Wall Wash EM Integral Battery with pre-punched reflector	WT Painted White Flange only	CL Regressed Clear Lens DL Regressed Diffuse Lens PL Regressed Prismatic Lens
LF6SQML	Medium Lumen 120V-277V 0-10V 10% dimming		WW Wall Wash		6SQML Medium Lumen Semi-Diffuse Clear Alzak						

¹ Lens Options not available on WW.
 WW comes standard with DL Lens
² 30L is only available with LF6SQML housing and 6SQML trim.