



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

RLF6SL		DM1	SD	•	6LFSL	20L	35K	8	SS		WT
HOUSING		DRIVER OPTIONS	HOUSING OPTIONS		TRIM APERTURE	OUTPUT	KELVIN	CRI	REFLECTOR FINISH OPTIONS	REFLECTOR COLOR	REFLECTOR OPTIONS
RLF6SL	Standard Lumen 0-10V 10% dimming 120V-277V	<i>Standard 0-10V 10% Dimming</i> DM1 0-10V 1% dimming	SD Small Diameter		6LFSL Standard Lumen Semi-Diffuse Clear Alzak 6LFML Medium Lumen Semi-Diffuse Clear Alzak	11L 1100 Lumen Module 15L 1500 Lumen Module 20L 2000 Lumen Module 30L¹ 3000 Lumen Module	30K 3000 Kelvin 35K 3500 Kelvin 40K 4000 Kelvin	8 80+ CRI 9 90+ CRI	SP Specular SS Semi-Specular MFC American Matte™ V Kurt Versen Specular VS Kurt Versen Softglow VSS Kurt Versen SoftSheen™	<i>Standard Clear Alzak</i>	WT Painted White Flange only WF Wide Flange
RLF6ML	Medium Lumen 0-10V 10% dimming 120V-277V										

¹ 30L is only available with RLF6ML housing and 6LFML trim.