



10-Day Quick Ship Ordering Guide

Order Limit Per Fixture Selection: 50 Pieces or Less

RLF8ML		DM1		SD		=		8LFML		30L		35K		8		SS				WT	
HOUSING		DRIVER OPTIONS		HOUSING OPTIONS		TRIM APERTURE		OUTPUT		KELVIN		CRI		REFLECTOR FINISH OPTIONS		REFLECTOR COLOR		REFLECTOR OPTIONS			
RLF8SL	Standard Lumen 0-10V 10% dimming 120V-277V	<i>Standard 0-10V 10% Dimming</i>		SD	Small Diameter	8LFSL	Standard Lumen Semi-Diffuse Clear Alzak	11L	1100 Lumen Module	30K	3000 Kelvin	8	80+ CRI	SP	Specular	<i>Standard Clear Alzak</i>		WT	Painted White Flange only		
RLF8ML	Medium Lumen 0-10V 10% dimming 120V-277V	DM1 0-10V 1% dimming				8LFML	Medium Lumen Semi-Diffuse Clear Alzak	15L	1500 Lumen Module	35K	3500 Kelvin	9	90+ CRI	MFC	American Matte™			WF	Wide Flange		
								20L	2000 Lumen Module	40K	4000 Kelvin			V	Kurt Versen Specular						
								30L¹	3000 Lumen Module					VS	Kurt Versen Softglow™						
														VSS	Kurt Versen SoftSheen™						

¹ 30L is only available with RLF8ML housing and 8LFML trim.