



## Arceos™ ARS LED Series

The Arceos™ ARS LED luminaire has been designed from the ground up for surface, ceiling, canopy and parking structure illumination. Available in two lumen packages, the ARS provides excellent uniformity, energy efficiency and control for surface mount applications. ARS is suitable for mounting heights of 8 to 18 ft. with choices of symmetric and asymmetric distributions.



### 10-Day Quick-Ship Ordering Guide

Order Limit Per Luminaire Selection: 15 (Contact factory for larger quantities)

ARS	-		-		-	070	-		-	U	-	
SERIES	NUMBER OF LEDS		CCT	DRIVE CURRENT		IES DIST.		VOLTAGE		FINISH		
ARS Arceos Surface	24L	24 LEDs	4K 4000K	070	700mA	5M	Type V Square	U	120-277V	BL	Black Textured	
	36L	36 LEDs	5K 5000K			5R	Type V Rectangle			DB	Dark Bronze Textured	
						5W	Type V Wide			PS	Platinum Silver Smooth	