




# CANOPY

## PRODUCT SELECTION GUIDE

		GOOD			BETTER			BEST		
		<b>tradeSELECT<sup>®</sup></b>  SLING CANOPY			Additional Canopy  LUMASQUARE			Additional Canopy  BEACON DRIVE		
FEATURES	Easy to Install	Yes			Yes			Yes		
	Mounting Options	Standard J-Box-3/4" Pendant, 3 sided 1/2" 14 NPS threaded conduit entry			Standard J-Box or 3/4" Pendant			Standard J-Box or 3/4" Pendant		
	Features	++			++			+++		
	Maintenance	Low			Low			Low		
PERFORMANCE	Lumens	3200-8000			3000-9000			2,500-16,000		
	Watts	20-60W			25-75W			20-55W		
	Efficacy (maximum LPW)	134-142			120-127			109-125		
	Distribution	Type V			Type V			Type V, Type VC, Type VRW, Type IV		
	CCT	4000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K		
	CRI	70			70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	>60,000hrs.			>60,000hrs.			>60,000hrs.		
	HID Equivalence	100-250W			175-250W			175-250W		
Energy Savings	75%			75%			78%			
Voltage	120-277V			120-277V			120-277V			
CONTROLS	Basic occupancy	-			Yes			Yes		
	Occupancy and Daylight Harvesting	-			Yes			Yes		
	Integrated Controls	-			SiteSync™			NX		