






FLOODLIGHTS

PRODUCT SELECTION GUIDE

		GOOD						BETTER						BEST		
		tradeSELECT [™]			tradeSELECT [™]			tradeSELECT [™]			tradeSELECT [™]			tradeSELECT [™]		
																
		Colt Mini			Marshal			Colt LBUL			Lightscaper [®]			Ratio Flood		
FEATURES	Easy to Install	Yes						Yes						Yes		
	Mounting Options	½" 14 NPS			Junction box			½" 14 NPS			½" 14 NPS			Threaded Knuckle, Slipfitter & Trunnion		
	Features	+			+			++			++			+++		
	Maintenance	Low, Aiming			Low, Aiming			Low, Aiming			Med, Aiming, Adjustment			Low, Aiming		
PERFORMANCE	Lumens	1115			2104			2000			984, 2009			3500-30,000		
	Watts	13W			20W			21W			8W, 16W			25-265W		
	Efficacy (maximum LPW)	85			100			89-94			116-128			140		
	Distribution	NEMA 6X6 Wide			NEMA 6X6 Wide			NEMA 6X6 Wide			NEMA 7X6 Wide			Narrow, Medium, Wide		
	CCT	3000K			3000K			4000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K		
	CRI	70			80			70			70-100			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	60,000hrs.			60,000hrs.			>60,000 hrs.			60,000hrs.			>60,000hrs.		
	HID Equivalence	70W			100W			150W			100W, 120-277V			100W, w1000W		
	Energy Savings (Based on HID Equivalence)	86%			85%			83%			86%			76%		
Voltage	120V			120V			120-277V			120-277V			120-277V, 347-480V			
CONTROLS	Basic occupancy	-			Yes			-			-			Yes		
	Occupancy and Daylight Harvesting	-			Yes			-			-			Yes		