

SERIES "A" CABLE REELS

COMMERCIAL / INDUSTRIAL APPLICATIONS
MOUNT ON CEILING, WALL OR UNDER BENCH



Series "A" Cable Reel Features:

- Cast Aluminum Construction
- Slip Ring in Gasketed Enclosure
- Durable Baked Polyester Powder Painted Finish
- Unitized 20 Amp Slip Ring
- Easily Accessible Gasketed Junction Box
- Spool Configuration Prevents "Lock-out"
- Field Adjustable Cord Guide with Four Rollers
- Positive Locking Dog with Field Adjustable Disengage Feature
- Maintenance Free Enclosed Power Spring
- Type SO Cable Included On All Reels
- Field Adjustable Cord Stop

CABLE DATA							
AMP RATING @ 600 VAC	AWG	NO. COND	LENGTH		WEIGHT		MODEL NUMBER
			FEET	(METER)	lbs	(kg)	
9	16	3	20	(6.1)	32.7	(14.7)	A-232B
9	16	3	30	(9.1)	33.9	(15.2)	A-224B
9	16	3	40	(12.2)	35.0	(15.7)	A-231B
9	16	3	50	(15.2)	36.1	(16.2)	A-228B
<hr/>							
7	16	4	20	(6.1)	33.5	(15.1)	A-242B
7	16	4	30	(9.1)	35.0	(15.7)	A-234B
7	16	4	40	(12.2)	36.5	(16.4)	A-244B
7	16	4	50	(15.2)	38.0	(17.1)	A-238B
<hr/>							
13	14	3	20	(6.1)	30.7	(13.8)	A-332C
13	14	3	30	(9.1)	36.1	(16.2)	A-233C
13	14	3	40	(12.2)	37.9	(17.1)	A-334C
13	14	3	50	(15.2)	39.8	(17.9)	A-358C
<hr/>							
11	14	4	20	(6.1)	34.9	(15.7)	A-342C
11	14	4	30	(9.1)	37.1	(16.7)	A-343C
11	14	4	40	(12.2)	39.3	(17.7)	A-344C
11	14	4	45	(13.7)	41.5	(18.7)	A-367C
<hr/>							
18	12	3	20	(6.1)	35.6	(16.0)	A-332D
18	12	3	30	(9.1)	38.1	(17.1)	A-333D
18	12	3	40	(12.2)	40.6	(18.3)	A-434D
18	12	3	50	(15.2)	43.1	(19.4)	A-435D
<hr/>							
14	12	4	20	(6.1)	36.4	(16.4)	A-342D
14	12	4	30	(9.1)	39.4	(17.7)	A-394D
14	12	4	40	(12.2)	42.4	(19.1)	A-444D

