

GEOPAK™
S E R I E S

HUBBELL
Outdoor Lighting



HUBBELL
Lighting



New, high performance, energy-efficient, GeoPak™ series is an outdoor architectural wall sconce family featuring superior performance, two versatile sizes, and integrated controls.



SIZE 1




TRAPEZOID

RADIUS

QUARTERSHPERE

SIZE 2



GeoPak series is available in **THREE** architectural forms and **TWO** sizes to optimize scale in a wide variety of applications including **Up/Down** lighting, **Inverted** mounting and **Low Glare**

SHAPE + SCALE + PERFORMANCE + CONTROL

Available in the most popular paint finishes and architectural shapes including trapezoid, radius and quartersphere. These wall sconce luminaires feature high lumen output, excellent uniformity, photocontrol and occupancy sensor for optimum performance and energy savings.



VERSATILITY IN APPLICATION

PRIMARY DISTRIBUTIONS

DOWN MOUNTING

High performance IES distributions types II, III & IV provide best in class performance for lighting building perimeters and walkways.

TRP1	RDI1	QSP1
✓	✓	✓
TRP2	RDI2	QSP2
✓	✓	✓



INVERTED/UP MOUNTING

A wide range of asymmetric optics offer the perfect distribution for highlighting building facades and under canopy lighting when inverted mounting.

TRP2	RDI2	QSP2
✓	✓	✓



SECONDARY DISTRIBUTIONS

UPLIGHT GRAZE



Available with uplight wall graze, canopy, and spot distributions, GeoPak 2 offers the ideal solution for lighting building facades, canopies and tall columns without sacrificing down lighting performance.

TRP2	RDI2
✓	✓


UPLIGHT SPOT/COLUMN



LOW GLARE - DIFFUSER

FEATURES

- Trapezoid and Radius housing shapes in GeoPak size 2
- Low glare zero pixelation lens
- Three uplight distributions
- Control capabilities offer additional energy savings
- DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org



STANDARD VERSION

FEATURES

- Two housing sizes in three shapes
- Optional diffused lens for increased visual comfort
- Inverted mounting – Size 2 only
- Control capabilities offer additional energy savings
- Integral battery backup options
- DesignLights Consortium® (DLC) qualified. Please refer to the DLC website for specific product qualifications at www.designlights.org.



LOW GLARE



Designed for optimal visual comfort and maximum performance, the low glare versions provide excellent illumination and uniformity with zero LED pixelation.

UPLIGHT



Optional uplight distributions provide accent lighting for columns, canopies or building facades

The wall graze also creates a 50/50 appearance on the wall while still providing general illumination on the ground

CONTROL OPTIONS



Programmable occupancy sensor offers greater control and energy savings with adjustable delay and dimming levels (Factory default is 10%)

EMERGENCY EGRESS



Specialized emergency lighting optics (highlighted) and integral battery back up feature with Spectron self diagnostics push-to-test status indicator, (EH) option includes heater for operation to -30°C




Delivers Life Safety Code average illuminance of 1.0 fc. (See pg. 8 for performance)

POWERED BY DUALITE


More Info: www.hubbelloutdoor.com/products/wall-mount/

More Info: www.hubbelloutdoor.com/products/wall-mount/

PERFORMANCE – SIZE 1 – TRP1, RD11, QSP1 – 15Ft. Mounting Height







EGRESS MODE PERFORMANCE SIZE 1 & 2





Provides Life Safety Code average illuminance of 1.0 fc. Assumes open space with no obstructions. Diagrams for illustration purposes only, please consult factory for application layout.

PERFORMANCE – SIZE 2 – TRP2, RD12, QSP2 – 15Ft. Mounting Height



LOW GLARE PERFORMANCE – SIZE 2 – TRP2 – 15Ft. Mounting Height



PERFORMANCE DATA

GeoPak size 1 Series Number	HID Equivalency		Lumens Delivered	System Watts	Lumens Per Watt 4K, Type III
	MH	HPS			
12L - 15	70w	70w	1,600	14	114
12L - 20	100w	100w	2,200	21	110
12L - 30	150w	150w	2,900	28	107

PERFORMANCE DATA

GeoPak size 2 Series Number	HID Equivalency		Lumens Delivered	System Watts	Lumens Per Watt 4K, Type III
	MH	HPS			
24L-30	150w	150w	3,800	28	134
24L-50	175w	175w	5,800	49	120
24L-70	250w	250w	7,900	71	112
24L-90	400w	400w	9,900	87	114
32L-70	250w	250w	7,900	67	118
32L-90	400w	400w	9,900	83	120

LOW GLARE

GeoPak size 2 Series Number	HID Equivalency		Lumens Delivered	System Watts	Lumens Per Watt 4K, Type FT
	MH	HPS			
D-20	100w	100w	3,000	20	155
D-30	150w	150w	5,000	30	150
D-50	175w	175w	7,000	50	145
D-70	250w	250w	9,000	70	140

ORDERING INFORMATION - SIZE 1 - TRP1, RD11, QSP1

HOUSING/FAMILY	VERSION	WATTAGE	CCT	DISTRIBUTION	VOLTAGE	FINISH	CONTROL OPTIONS	OPTIONS
TRP1	Trapezoid	12L 12 LEDs	15 15 watts	2 Type II	U 120V-277V	BL Black Textured	PCU Button Photocontrol	F ⁴ Fusing
RD11	Radius	20 20 watts	4K7 4000K, 70CRI	3 Type III	1 120V	DB Dark Bronze Textured	SCP ^{2,3} Programmable motion sensor	E ¹ Battery Pack (0° C)
QSP1	Qtr-Sphere	30 30 watts	5K7 5000K, 70CRI	4 Type IV	2 208V 3 240V 4 277V	GT Graphite Textured GYS Light Gray Smooth PS Platinum Silver Smooth WH White Textured CC Custom Color		EH ¹ Battery Pack (-30° C) with heater
							SPEC SCP MOUNT HT.	
							-8F Up to 8ft mount height	
							-20F Up to 20ft mount height	

- ¹ Voltage specific (120 or 277V only)
² Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings, 120-277V only
³ PCU option not applicable, included in sensor
⁴ Must specify input voltage (120, 208, 240 or 277)


ACCESSORIES (ORDER SEPARATELY)

Catalog Number	Description
SCP-REMOTE	Remote control for SCP option. Order at least one per project to program and control dimming settings
BB-GEO-XX	Back box with 4 - 1/2" threaded conduit holes, specify finish by replacing "XX" with finish selection, eg. Dark Bronze "DB"


STOCK - SIZE 1 - TRP1, RD11, QSP1

Part Number	Catalog Number	Description	Wt. each
93066586	RD114KUDBE	Radius Hsg, Dark Brz, Emergency with Battery	11.5 lbs
93066587	RD114KUDBEH	Radius Hsg, Dark Brz, Emergency with Battery and Heater	11.5 lbs
93067831	RD114KUWHE	Radius Hsg, White, Emergency with Battery	11.5 lbs
93067832	RD114KUWHEH	Radius Hsg, White, Emergency with Battery and Heater	11.5 lbs
93068340	RD114KUPSE	Radius Hsg, Silver, Emergency with Battery	11.5 lbs
93068341	RD114KUPSEH	Radius Hsg, Silver, Emergency with Battery and Heater	11.5 lbs
93068342	RD114KUBLE	Radius Hsg, Black, Emergency with Battery	11.5 lbs
93068343	RD114KUBLEH	Radius Hsg, Black, Emergency with Battery and Heater	11.5 lbs
93066588	TRP14KUDBE	Trapezoid Hsg, Dark Brz, Emergency with Battery	11.5 lbs
93066589	TRP14KUDBEH	Trapezoid Hsg, Dark Brz, Emergency with Battery and Heater	11.5 lbs
93067833	TRP14KUWHE	Trapezoid Hsg, White, Emergency with Battery	11.5 lbs
93067834	TRP14KUWHEH	Trapezoid Hsg, White, Emergency with Battery and Heater	11.5 lbs
93067835	TRP14KUPSE	Trapezoid Hsg, Silver, Emergency with Battery	11.5 lbs
93067836	TRP14KUPSEH	Trapezoid Hsg, Silver, Emergency with Battery and Heater	11.5 lbs
93067837	TRP14KUBLE	Trapezoid Hsg, Black, Emergency with Battery	11.5 lbs
93067838	TRP14KUBLEH	Trapezoid Hsg, Black, Emergency with Battery and Heater	11.5 lbs
93066584	QSP14KUDBE	Quartersphere Hsg, Dark Brz, Emergency with Battery	10.5 lbs
93066585	QSP14KUDBEH	Quartersphere Hsg, Dark Brz, Emergency with Battery and Heater	10.5 lbs
93068344	QSP14KUWHE	Quartersphere Hsg, White, Emergency with Battery	10.5 lbs
93068345	QSP14KUWHEH	Quartersphere Hsg, White, Emergency with Battery and Heater	10.5 lbs
93068346	QSP14KUPSE	Quartersphere Hsg, Silver, Emergency with Battery	10.5 lbs
93068347	QSP14KUPSEH	Quartersphere Hsg, Silver, Emergency with Battery and Heater	10.5 lbs
93068348	QSP14KUBLE	Quartersphere Hsg, Black, Emergency with Battery	10.5 lbs
93068349	QSP14KUBLEH	Quartersphere Hsg, Black, Emergency with Battery and Heater	10.5 lbs


DIMENSIONS



Trapezoid (TRP1)



Quartersphere (QSP1)



Round (RD11)

ORDERING INFORMATION - SIZE 2 - TRP2, RD12, QSP2

FAMILY	LEDS - WATTAGE	CCT	DISTRIBUTION	VOLTAGE	FINISH	CONTROL OPTIONS	OPTIONS
TRP2	Trapezoid	24L-30 24 LEDs, 30 watts	1 Type I	UNV 120-277V	BL Black Textured	PC Button Photocontrol	SF ³ Single Fuse & Fuse Holder
RD12	Radius	24L-50 24 LEDs, 50 watts	2 Type II	120 120V	DB Dark Bronze Textured	SCP ^{4,5} Programmable occupancy sensor, factory default is 10% light output	DF ³ Double Fuse & Fuse Holder
QSP2	Qtr-sphere	24L-70 24 LEDs, 70 watts	3 Type III	208 208V	GT Graphite Textured	SCO ⁴ Sensor Control, On/Off	E ³ Battery Pack (0° C)
		24L-90 24 LEDs, 90 watts	4 Type IV	240 240V	GR Gray Textured Matte	SWP ^{3,7} SiteSync Pre-Commission	EH ³ Battery Pack (-30° C) with heater
		32L-70 32 LEDs, 70 watts		277 277V	GYS Light Gray Smooth	SWPM ^{3,4,7,8} SiteSync Pre-commission w/Occupancy Sensor	EH ³ Battery Pack (-30° C) with heater
		32L-90 32 LEDs, 90 watts		UHV ¹ 347/480V	PS Platinum Silver Smooth	SPEC SCP/SCO & SWPM MOUNT HEIGHT	2DR ⁶ Dual Drivers
				347 ¹ 347V	WH White Textured	-8F Up to 8ft mount height	2PF ⁶ Dual Power Feeds
				480 ¹ 480V	CC Custom Color	-20F Up to 20ft mount height	CS Comfort Shield
					SECONDARY MOUNTING		
					BLANK Downlight Only		
					NV ² Inverted/Up Mounting		

- ¹ 70 & 90 watt versions only, or available with PC, SCP or SCO sensors
² Not available with SCP, SCO or SWPM sensor options
³ Must specify voltage (120, 277 or 347V only for SWP & SWP, 120 or 277V only for E & EH)
⁴ PCU option not applicable, included in sensor
⁵ Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings
⁶ Not available with 30w version
⁷ Not available with E/H options. Must specify group and zone information at time or order. See www.hubbellighting.com/products/sitesync for future details
⁸ Specify time delay, dimming level and mounting height

ACCESSORIES (ORDER SEPARATELY)

Catalog Number	Description
SCP-REMOTE	Remote control for SCP option. Order at least one per project to program and control dimming settings
BB-GEO-XX	Black box with 4 - 1/2" threaded conduit holes, specify finish by replacing "XX" with finish selection, eg. Dark Bronze "DB"
SWUSB*	SiteSync loaded on USB flash drive (Windows based only)
SWTAB**	SiteSync Windows Tablet
SWBRG*	SiteSync Wireless Bridge Node


- * Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings.
** When ordering with SiteSync, one of the following interface options must be chosen an ordered separately. Each option contains the SiteSync License, GUI and Bridge Node.
* If needed, an additional Bridge Node can be ordered.

ORDERING INFORMATION - TRP2, RD12, LOW GLARE


FAMILY	LEDS - WATTAGE	DISTRIBUTION	VOLTAGE	FINISH	CONTROL OPTIONS	OPTIONS
TRP2	Trapezoid	D-20 20w Low Glare Diffuse	UNV 120-277V	BL Black Textured	PC Button Photocontrol	SF ³ Single Fuse & Fuse Holder
RD12	Radius	D-30 30w Low Glare Diffuse	120 120V	DB Dark Bronze Textured	SCP ^{4,5} Programmable occupancy sensor, factory default is 10% light output	DF ³ Double Fuse & Fuse Holder
		D-50 50w Low Glare Diffuse	208 208V	GT Graphite Textured	SCO ⁴ Sensor Control, On/Off	2DR ⁶ Dual Drivers
		D-70 70w Low Glare Diffuse	240 240V	GYS Light Gray Smooth	SPEC SCP/SCO MOUNT HEIGHT	2PF ⁶ Dual Power Feeds
			277 277V	PS Platinum Silver Smooth	-8F Up to 8ft mount height	
			UHV ¹ 347/480V	WH White Textured	-20F Up to 20ft mount height	
			347 ¹ 347V	CC Custom Color		
			480 ¹ 480V			
					SECONDARY DISTRIBUTION	
					BLANK Downlight Only	
					UG ² Uplight Wall Graze	
					UC ² Uplight Canopy	
					US ² Uplight Spot/Column	

- ¹ 70 watt version only
² Not available with SF, DF, 2DR or 2PF electrical options
³ Must specify voltage
⁴ PCU option not applicable, included in sensor
⁵ Must order minimum of one remote control to program dimming settings, 0-10V fully adjustable dimming with automatic daylight calibration and different time delay settings
⁶ Not available with 20w, 30w or uplight versions


DIMENSIONS



Trapezoid (TRP2)



Quartersphere (QSP2)



Round (RD12)



HUBBELL
Lighting

ALERA LIGHTING

ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HUBBELL CONTROL SOLUTIONS

HUBBELL INDUSTRIAL LIGHTING

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE

WHITEWAY



HUBBELL
Outdoor Lighting

701 Millennium Blvd. Greenville, SC 29607
Tel 864.678.1000
www.hubbelloutdoor.com

HOL00336 5K August 23, 2019 9:10 AM

Copyright © 2017 Hubbell Outdoor Lighting, a division of Hubbell Lighting, Inc. All rights reserved.
Please refer to online specifications for most up-to-date content as specifications are subject to change without notice.
Due to our continued efforts to improve our products, product specifications are subject to change without notice.