



CAPTIVATE™

Illuminated Mirror Light


CAPTIVATE

Captivate provides a clean, architecturally pleasing solution for illuminating the vanity that is ideal for healthcare, hospitality, commercial and residential applications. The indirect, backlit solution delivers soft illumination that is well suited for facial rendering.

FEATURES

- The perimeter etched panels are indirectly backlit to provide soft illumination for rendering facial features.
- Mirror edges have a brushed, radius treatment for consistency in appearance.
- Available in four sizes (18"x39", 25"x43", 31"x43" and 37"x43") and in three different light color temperatures (3000K, 3500K and 4000K.)
- An optional integrated night light is positioned in the lower etched panel and can be specified in either a 3000K white or 590nm amber light source.
- All models are ADA compliant and simple to install.
- The housing comes with a standard antimicrobial paint finish to inhibit the growth of microbes.
- Captivate comes standard with 0-10V dimming.

DIMENSIONS



| | MODEL # | | | |
|-----------|--------------------|---------------------|---------------------|---------------------|
| | 1839 | 2543 | 3143 | 3743 |
| H1 | 39.0" (990.6mm) | 43.0" (1092.2mm) | 43.0" (1092.2mm) | 43.0" (1092.2mm) |
| H2 | 31.3 (795.0mm) | 34.3" (992.0mm) | 34.3" (992.0mm) | 34.3" (992.0mm) |
| W1 | 17.7" (449.6mm) | 24.7" (627.4mm) | 31.0" (787.4mm) | 37.0" (939.8mm) |
| W2 | 10.0" (254.0mm) | 16.0" (406.4mm) | 22.3" (566.4mm) | 28.3" (718.8mm) |
| A | 1.8" (45.7mm) | 1.8" (45.7mm) | 1.8" (45.7mm) | 1.8" (45.7mm) |
| B | 2.0" (50.8mm) | 2.5" (50.8mm) | 2.5" (50.8mm) | 2.5" (50.8mm) |
| C | 37.1" (942.3mm) | 40.1" (1018.5mm) | 40.1" (1018.5mm) | 40.1" (1018.5mm) |
| D | 15.8" (401.3mm) | 21.8" (553.7mm) | 28.1" (713.7mm) | 34.1" (916.9mm) |
| E | 7.4" (188.0mm) | 5.0" (127.0mm) | 8.0" (203.2mm) | 8.0" (203.2mm) |
| F | 13.0" (330.2mm) | 13.0" (330.2mm) | 13.0" (330.2mm) | 13.0" (330.2mm) |

CAPTIVATE PERFORMANCE CHART

| Model # | 3500K | | | Input Current | |
|-------------|-------------|---------|------|---------------|---------|
| | With Mirror | | | 120V | 277V |
| | Lumen | Wattage | LPW | | |
| 1839 | 912 | 24.9 | 36.6 | 0.208 A | 0.088 A |
| 2543 | 1140 | 24.4 | 46.7 | 0.205 A | 0.088 A |
| 3143 | 1653 | 36.2 | 45.7 | 0.304 A | 0.131 A |
| 3743 | 1689 | 35.9 | 47.0 | 0.302 A | 0.130 A |

ORDERING GUIDE

EXAMPLE: CML1-3143-830-U-NA

| CML1 | MODEL | LENGTH | CRI | COLOR TEMP | VOLTAGE | OPTIONS |
|------|------------------------|--|--------------|---|-------------------------------|---|
| CML1 | Captivate Mirror Light | 1839 18"W x 39"H (nom.) 2543 25" x 43" (nom.) 3143 31" x 43" (nom.) 3743 37" x 43" (nom.) | 8 >80 | 30 3000K 35 3500K 40 4000K | U Universal (120-277V) | NW Night light-white (3000K) NA Night light-amber (590nm) TR Tamper-resistant hardware |



Healthcare
Solutions

701 Millennium Blvd.
Greenville, SC 29607
hubbellighting.com

ALERA LIGHTING

ARCHITECTURAL AREA LIGHTING

BEACON PRODUCTS

COLUMBIA LIGHTING

COMPASS

DUAL-LITE

HEALTHCARE SOLUTIONS

HUBBELL CONTROL SOLUTIONS

HUBBELL INDUSTRIAL LIGHTING

HUBBELL OUTDOOR LIGHTING

KIM LIGHTING

KURT VERSEN

LITECONTROL

PRESCOLITE

WHITEWAY



701 Millennium Blvd. Greenville, SC 29607
Tel 864.678.1000
www.hubbellighting.com

HHS0064 Revised: 10/17

Copyright © 2017 Hubbell Lighting, Inc. All rights reserved. Please refer to
online specifications for most up-to-date content as specifications are subject to change without notice.