




LIGHTSCAPER SERIES


Versatile, linear floodlight for landscape, accent, pole, sign, facade and small area illumination



Hubbell Outdoor Lighting's compact sleek and stylish Lightscaper® floodlight provides energy-efficient small area floodlighting solution featuring two lumen packages and three color temperatures in one product. This versatile LED luminaire is the perfect choice for many floodlighting applications including: accent, landscape, facade or small area illumination.

**Features and Benefits:**

- 8 & 16 Watt - Switchable 1,000 - 2,000 lumens replaces 100w HID or 84w CFL
- 3000K, 4000K, 5000K color temperatures
- Traditional 1/2" x 14 NPS threaded adjustable knuckle mounting
- 120-277V operation
- Die-cast aluminum housing
- Decorative dark bronze textured finish
- 7x6 distribution
- IP66 and certified to UL 1598 for use in wet locations
- Certified up to 40°C ambient per UL 1598



**Performance Data**

Series Number	Equivalency	CCT	CRI	Voltage	Lumens Delivered	Lumens Per Watt	Distribution Type
LSP-LSCS (1000 Lumens)	75W CFL	3000k	70	120V-277V	984	122	7x6
		4000k			1015	128	
		5000k			1025	126	
LSP-LSCS (2000 Lumens)	100W HID	3000k	70	120V-277V	1906	116	7x6
		4000k			2009	125	
		5000k			1991	120	





## Applications



3000K




4000K




5000K

## Performance




**LSP-LSCS 1000 Lumens**  
SET BACK 10'



**LSP-LSCS 2000 Lumens**  
SET BACK 10'

## Dimensions



A	B	C	D	Weight
12.0"	4.0"	7.5"	2.8"	3.3 lbs.
305 mm	102 mm	191 mm	71 mm	1.49 kg

