



A DIVISION OF HUBBELL



Fire Pump Engine Starter Solenoid

Type 1804A



These high power rated starter solenoids are available with or without an emergency start lever with either 12 or 24V DC coils.

Maximum coil current: 12v units= 6A max, 24v units =10A
max Contact voltage 30v DC (All models)
Contact rolling current: 1000A DC
Contact breakaway current: 2000A DC

1804A-12 = 12V DC coil with emergency start lever
1804A-24 = 24V DC coil with emergency start lever



Hubbell Industrial Controls, Inc. - Metron Fire Pump Control Division
4301 Cheyenne Dr., Archdale, NC 27263 Phone: 336-434-2800 · Fax: 336-434-2809
Email: salesmail@metroninc.com · www.metroninc.com