

Hubbell Industrial Controls, Inc.

Jockey Pump Controllers

LX-600

For Electric Pressure Maintenance Pumps

Price List 6420 • July 2010, Replaces June 2002

The standard LX-600 includes a type 3R enclosure, combination motor controller, overload protection, 15-290 psi pressure switch and 3 position selector switch (H-O-A).

Standard Controller List Prices					
HP	200-208 Volt	220-240 Volt	380-415 Volt	440-480 Volt	575-600 Volt
1/3	\$740	\$740	\$740	\$740	\$740
1/2	\$740	\$740	\$740	\$740	\$740
3/4	\$740	\$740	\$740	\$740	\$740
1	\$740	\$740	\$740	\$740	\$740
1 1/2	\$740	\$740	\$740	\$740	\$740
2	\$740	\$740	\$740	\$740	\$740
3	\$740	\$740	\$740	\$740	\$740
5	\$740	\$740	\$740	\$740	\$740
7 1/2	\$740	\$740	\$740	\$740	\$740
10	\$1,050	\$1,050	\$740	\$740	\$740
15	\$1,155	\$1,155	\$1,155	\$1,155	\$1,155
20	\$1,518	\$1,518	\$1,155	\$1,155	\$1,155
25	\$1,518	\$1,518	\$1,155	\$1,155	\$1,155
30	\$1,518	\$1,518	\$1,587	\$1,587	\$1,587
40	\$2,834	\$2,834	\$1,587	\$1,587	\$1,587
50	\$3,034	\$3,034	\$1,587	\$1,587	\$1,587

Controller Options		
Option	Description	List Price
	Space Heaters - Price includes line circuit breaker. Must be connected to separate power source.	
	120V	
G1	Space heater only	\$200
G2	Space heater and thermostat	\$320
G3	Space heater and humidistat	\$320
	240V	
G4	Space heater only	\$200
G5	Space heater and thermostat	\$320
G6	Space heater and humidistat	\$320
K	Tropicalization	\$300
F	Export boxing	\$250
	Enclosures	
M2	Type 12	\$200
M3	Type 4	\$700
M4	Type 4X - #304 stainless steel	\$1,200
	Pressure Switches	
N1	12-464 psi, freshwater	\$75
X	Consult factory for seawater applications.	

Prices subject to change without notice.



Controller Options		
Option	Description	List Price
AB	Run period timer	\$160
R2	Pump running pilot light	\$120
R3	Pump run contacts	\$90
AC	Power on light	\$120
AD	Elapsed time meter	\$125
R8	Fail to start contacts	\$180
AE	Power failure contacts	\$320
AF	Phase failure and phase reversal contacts	\$350
R12	Motor overload contacts	\$160
AG	Motor overload light	\$180
AH	Operations counter	\$175
R18	Common trouble contacts	\$90
R19	Common trouble light	\$120
RX	Additional contacts, specify alarm if not found above	\$160
	Special Labeling	
S2	New York City MEA	N/C
S5	Service entrance rating	N/C

Notes: When ordering, specify hp, voltage, frequency, motor full load current and options required. Consult factory for options not shown.

Prices subject to change without notice.



Hubbell Industrial Controls, Inc.
a subsidiary of Hubbell Incorporated
 4301 Cheyenne Drive, Archdale, NC 27263
 Phone (336) 434-2800 | Fax (336) 434-2803
 www.hubbell-icd.com
 sales@hubbell-icd.com