


WALLPACK



Optional Photocontrol


- Rugged die cast aluminum housing with dark bronze corrosion resistant powder coat finish
- Impact resistant, UV stabilized, field replaceable polycarbonate refractor
- Capable of mounting on a 3 - 3 1/2" junction box
- Conduit entry for surface conduit applications




STOCK SKUs	LEDs	Wattage	Voltage	CCT/CRI	Lumens	LPW	Equivalency	Photocontrol
• PRS-20-4K-PC	60 LEDs	22W	120-277V	4000K/70	2131	96	150W	Yes
• PRS-20-5K-PC	60 LEDs	23W	120-277V	5000K/70	2104	92	150W	Yes
• PRS-20-4K	60 LEDs	22W	120-277V	4000K/70	2131	96	150W	No
• PRS-20-5K	60 LEDs	23W	120-277V	5000K/70	2104	92	150W	No

PERFORMANCE

■ 2.0 fc ■ 1.0 fc ■ 0.5 fc



DIMENSIONS



A	B	C	Weight
10.9" 277 mm	6.8" 172 mm	4.8" 121 mm	2.75 lbs. 1.25 kg