



WIEGMANN®

Commercial and Industrial Enclosures

Get the most durable & reliable polycarbonate enclosures available!

PROTECT FROM



Latches and nonmetallic hinges do not penetrate the enclosure

Easy to remove lid cover



High impact polycarbonate

DIN Rail mounting embosses in back

Flush-fit side mount swing panel and DIN rail system included

Channel and T-nut allows for infinite adjustment of panels

Multi-directional mounting feet

Integrated hasp provides secure loop for padlock
(padlock not included)

(Clear or opaque covers available)

Sizes range from 6" x 6" to 24" x 24"

Meet or Beat Industry Standards!

- Rated Type 3R, 4, 4X, 6P, 12
- Rated IEC IP66, IP6
- UL/cUL Approved
- UL 94 - Flame Rating - 5VA
- Temperature Range: -20°F to 240°F




Polycarbonate Enclosures

Catalog Number		Enclosure Overall Size HxWxD	Aluminum Back Panel	Swing Panel Kits (mounts, screws and panel included)
Opaque	Clear			
HW-P60604CHQR	HW-PCC60604CHQR	6x6x4	HW-MP606A	HW-P606SPK
HW-P80604CHQR	HW-PCC80604CHQR	8x6x4	HW-MP806A	HW-P806SPK
HW-P80804CHQR	HW-PCC80804CHQR	8x8x4	HW-MP808A	HW-P808SPK
HW-P100804CHQR	HW-PCC100804CHQR	10x8x4	HW-MP1008A	HW-P1008SPK
HW-P100806CHQR	HW-PCC100806CHQR	10x8x6	HW-MP1008A	HW-P1008SPK
HW-P101006CHQR	HW-PCC101006CHQR	10x10x6	HW-MP1010A	HW-P1010SPK
HW-P121006CHQR	HW-PCC121006CHQR	12x10x6	HW-MP1210A	HW-P1210SPK
HW-P141206CHQR	HW-PCC141206CHQR	14x12x6	HW-MP1412A	HW-P1412SPK
HW-P161408CHQR	HW-PCC161408CHQR	16x14x8	HW-MP1614A	HW-P1614SPK
HW-P181604CHQR	HW-PCC181604CHQR	18x16x4	HW-MP1816A	HW-P1816SPK
HW-P181610CHQR	HW-PCC181610CHQR	18x16x10	HW-MP1816A	HW-P1816SPK
HW-P201608CHQR	HW-PCC201608CHQR	20x16x8	HW-MP2016A	HW-P2016SPK
HW-P242410CHQR	HW-PCC242410CHQR	24x24x10	HW-MP2424PCA	HW-P2424SPK

DIMENSIONS (INCHES)

Enclosure	AxB	CXD	Back Panel	Swing-Panel
6 x 6 x 4	4.25 x 4.25	6.75 x 6.75	4.88 x 4.88	5.63 x 5.63
8 x 6 x 4	6.25 x 4.25	8.75 x 6.75	6.88 x 4.88	7.63 x 5.63
8 x 8 x 4	6.25 x 6.25	8.75 x 8.75	6.88 x 6.88	7.63 x 7.63
10 x 8 x 4	8.25 x 6.25	10.75 x 8.75	8.88 x 6.88	9.63 x 7.63
10 x 8 x 6	8.25 x 6.25	10.75 x 8.75	8.88 x 6.88	9.63 x 7.63
10 x 10 x 6	8.25 x 8.25	10.75 x 10.75	8.88 x 8.88	9.63 x 9.63
12 x 10 x 6	10.25 x 8.25	12.75 x 10.75	10.88 x 8.88	11.63 x 9.63
14 x 12 x 6	12.25 x 10.25	14.75 x 12.75	12.88 x 10.88	13.63 x 11.63
16 x 14 x 8	14.25 x 12.25	16.75 x 14.75	14.88 x 12.88	15.63 x 13.63
18 x 16 x 4	16.25 x 14.25	18.75 x 16.75	16.88 x 14.88	17.63 x 15.63
18 x 16 x 10	16.25 x 14.25	18.75 x 16.75	16.88 x 14.88	17.63 x 15.63
20 x 16 x 8	18.25 x 14.25	20.75 x 16.75	18.88 x 14.88	19.63 x 15.63
24 x 24 x 10	22.25 x 22.25	24.75 x 24.75	22.88 x 22.88	23.63 x 23.63



COMMERCIAL CONSTRUCTION
A Division of Hubbell Incorporated (Delaware)

© 2020 Hubbell. All rights reserved. Information subject to change.
Trademarks are property of their respective owners.

Hubbell Canada Inc. 905-839-1138
Hubbell de Mexico, S.A. de C.V. 52-55-9151-9999

Wiegmann
Freeburg, IL 62243
618-539-3193

hubbell.com/wiegmann/en

WIEGMANN®

WG_015 rev4
7/20