

WALL PACK

PRODUCT SELECTION GUIDE

GOOD

GOOD

BETTER

BEST

	tradeSELECT® NRG® 300L			tradeSELECT® PRS PERIMASHIELD			tradeSELECT® WGH1			tradeSELECT® WGH2/WGH3			tradeSELECT® SLING WALL			tradeSELECT® PRELUDE WALLPACKS			Additional Wallpack Ratio Wall			
FEATURES	Yes																					
	Junction box			Junction Box			Junction box			Junction box			Side door, Junction box			Mounting Plate, Junction box			Junction box, Conduit			
	+																					
	Low																					
PERFORMANCE	1800			2841–2899			3000–7000			4600–17,200			2200–8100			2500–8600			1000–19,500			
	17W			20W			20–50W			30–120W			21–80W			18W–60W			10–155W			
	110			106			140–146			140–147			110–115			139–144			148			
	Type IV			Type IV			Type IV			Type IV			Type IV			Type III (Cut Off), Type IV (Reflector)			Type II, Type III, Type IV			
	4000K, 5000K			4000K, 5000K			4000K			4000K, 4500, 5000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K			
	70			70			70			70			70			70			70			
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	UL1598	IP65	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	–	Yes	Yes	–	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.		
	HID Equivalence	70W			100W			Up to 200W			150–400W			100–250W			70–250W			42–400W		
Energy Savings (Based on HID Equivalence)	75%			77%			75–80%			75–80%			70–80%			75–80%			76%			
Voltage	120–277V			120–277V			120–277V			120–277V			120–277V			120–277V			120–277V & 347–480V			
Basic occupancy	Yes			Yes			Yes			Yes			Yes			–			Yes			
Occupancy and Daylight Harvesting	Photocontrol			Photocontrol			Optional Photocontrol			Photocontrol			Yes			–			Yes			
Integrated Controls	–			–			–			–			SiteSync™			Switchable			SiteSync™, NX Integrated Intelligence™			