



LED Site Wallforms®

Star View.
DarkSky
compliant



Supplement:
18 or 36 LED Wall Mounted Luminaires



SW1/36L5KUV/DB



SW3/36L5KUV/SG



18 or 36 LED

Wall Mounted Luminaires

LED module




SW1/36L5KUV/DB



SW3/36L5KUV/SG



- New super bright white LED technology with comfortable 3500K color temperature.
- LED Site Wallforms are constructed of heavy-duty cast aluminum with a flat tempered glass lens and concealed hardware for vandal resistance.
- StarView® DarkSky Compliant with flat glass lens meets IES/IDA full cutoff designation.



Uniquely canted LED modules improve light distribution and throw.

Ordering Information

1 Fixture	2 Electrical Module	3 Finish
SW1 SW3	18L3KUV ¹ 18L5KUV ¹ 36L3KUV ¹ 36L5KUV ¹	BL Black DB Dark Bronze LG Light Gray SG Stealth Gray® PS Platinum Silver WH White

EXAMPLE: / /

 1 2 3


Site Wallforms are also available with the following lamp sources:

- 50W Metal Halide
- 50W High Pressure Sodium
- 60W Incandescent
- 13-42W Compact Fluorescent

Refer to full catalog or website for additional details.

Typical Half for 18 LED


Isofootcandle Lines of Horizontal Illumination
8' Mounting Height



1/2 Maximum Candela trace --- Maximum Candela point x

Typical Half for 60 Watt LED

Isofootcandle Lines of Horizontal Illumination
8' Mounting Height



1/2 Maximum Candela trace --- Maximum Candela point x

¹ For LED, 18L = 18 LED Emitters; 36L = 36 LED Emitters; 3K = 3500K color temperature; 5K = 5100K color temperature; UV = Universal Voltage from 120 to 277V with a ± 10% tolerance.



Mailing Address:
P.O. Box 60080
City of Industry, CA
91716-0080

Business Address:
16555 East Gale Avenue
City of Industry, CA 91745
Phone: 626.968.5666
FAX: 626.369.2695

Because of a continuing product improvement program, Kim Lighting reserves the right to change specifications without notice.

Printed in U.S.A.
93019032
Version 1.1 (8/11)

