

NEW!
Egress LED
Integral Battery
Plus Controls

Laredo **LED** LMC-30 Integral Battery BBU



- 4000K and 5000K high CRI LEDs
- 35w – up to 3400 lumens (1546 lumens in battery mode)
- Provides 1 footcandle minimum over 16 square feet from 12 ft. mounting height
- Type III distribution up to 63 lumens per watt
- Long Life – 50,000+ hours, 350 mA driver
- IDA compliant – zero uplight
- Die-cast aluminum housing and door with distinctive decorative ribs
- 4 to 1 max to min footcandle levels
- Five standard finishes: Bronze, Black, Gray, White and Platinum
- Listed to UL1598 for use in wet locations
- Photocell and occupancy sensor options available for complete on/off and dimming control



Quick Mounting



Quick-mount – easy mounting without opening fixture. Attach adapter plate to wall, connect wires, hang fixture and tighten set screws.

Indicator/Test Button



Fixture diagnostic charging indicator light and emergency lighting system test button.

Photo Control




Optional factor installed button photocontrols. Specify voltage 120/208/240/277V.

Motion Control



Optional motion sensor available for complete on/off and dimming control.

30 High Power LEDs



30 – 4000K or 5000K high CRI LEDs precisely aligned for optimal photometric performance. Available in Type III distribution. Provides excellent uniformity and 5 to 1 spacing to mounting height ratio at 10-14 ft.

ORDERING INFORMATION ON REVERSE SIDE ▼

Laredo LED LMC-30 Applications



Healthcare


The LMC 30 LED Egress Laredo is designed for perimeter illumination for safety, security and identity. Typical mounting height is 10-14 feet and units can be powder paint finished to either blend or contrast with your building façade. The optical design choices provides wider spacing for new construction or retrofit applications.

Key product features include:

- 50,000+ hour rated life with a minimum 70% lumen maintenance – eleven plus years in typical applications
- 4000K and 5000K LED for excellent color rendition
- Type III distribution, Standard 350 mA driver
- Egress unit goes beyond safety standards with 16x16 ft. and 1 footcandle minimum coverage
- No uplight, IDA compliant, neighbor friendly
- Rugged die-cast aluminum housing and door with weather tight lenses protecting the LED system
- 'Quick-Mount' adapter allows one person installation without ever opening the luminaire, adapter mounts to wall box and after wiring connections are made, fixture is secured to the adapter
- Motion sensor and photocell options provide energy saving, automatic on/off and dimming control
- Five year limited warranty provides assurance for your lighting investment


Application Template

Full Output
12ft. Mounting height - 12ft. Grids



Application Template

Egress Output
12ft. Mounting height - 12ft. Grids



Dimensions

