

NEW!
350 mA Version!

Laredo **LED** LMC-30



- 4000K and 5000K high CRI LEDs
 - 71w – up to 4673 lumens - 66 LPW - 700 mA
 - 35w - up to 2700 lumens - 77 LPW - 350 mA
- Available in Type II, Type III and Type IV distributions
- Standard 700 mA driver with optional 350 mA
- Long Life – 50,000+ hours
- IDA compliant – no uplight
- Die-cast aluminum housing and door with distinctive decorative ribs
- Superior Performance
 - 5 to 1 spacing to mounting height ratio
 - 4 to 1 max to min footcandle levels
- Five standard finishes: Bronze, Black, Gray, White and Platinum
- Listed to UL1598 for use in wet locations
- Part of the Southwest Series design & build outdoor lighting solutions

Quick Mounting



Quick-mount – easy mounting without opening fixture. Attach adapter plate to wall, connect wires, hang fixture and tighten set screws.

Photo Control



Factory installed button photocontrols. Specify voltage 120/208/240/277V.

30 High Power LEDs



30 – 3000K, 4000K or 5000K high CRI LEDs precisely aligned for optimal photometric performance. Available in Type II, Type III and Type IV distributions. Provides excellent uniformity and 5 to 1 spacing to mounting height ratio at 15-18 ft.

Polycarbonate Shield



1/8" clear polycarbonate, protects lens and LEDs from vandalism. Field installed.



ORDERING INFORMATION ON REVERSE SIDE

Laredo LED LMC-30 Applications



Healthcare

The LMC 30 LED Laredo is designed for perimeter illumination for safety, security and identity. Typical mounting height is 15 to 18 feet and units can be powder paint finished to either blend or contrast with your building façade. The optical design choices provides wider spacing or forward throw capability for new construction or retrofit applications.

Key product features include:


- 50,000+ hour rated life with a minimum 70% lumen maintenance – eleven plus years in typical applications
- 3000K, 4000K and 5000K LED for excellent color rendition
- Type III and Type IV distributions are available
- Standard 700 mA driver or optional 350 mA control
- Wide spacing at typical 15-18 ft mounting heights – 70-80 ft (700 mA unit)
- No uplight, IDA compliant, neighbor friendly
- Rugged die-cast aluminum housing and door with weather tight lenses protecting the LED system
- 'Quick-Mount' adapter allows one person installation without ever opening the luminaire, adapter mounts to wall box and after wiring connections are made, fixture is secured to the adapter
- Photocontrol option provides energy saving, automatic on/off for dusk-to-dawn lighting
- Five year limited warranty provides assurance for your lighting investment

ORDERING INFORMATION (EXAMPLE)

LMC	-	30LU	-		-		-		-		-	PC(4)
SERIES	LEDS / SOURCE / VOLTAGE		COLOR TEMPERATURE	DISTRIBUTION ¹	DRIVE CURRENT	FINISH	OPTIONS					
LMC Laredo Medium Cut-off	30LU 30 LEDs, 71w input 30LF 30 LEDs, 71w input, 347V		3K Nominal 3000K 4K Nominal 4000K 5K Nominal 5000K	2 Type II 3 Type III 4 Type IV	BLANK Standard is 700mA 035² 350mA	1 Bronze 2 Black 3 Gray 4 White 5 Platinum	PC(X) Button photocontrol, replace X with voltage, specify 1-120V, 2-208V, 3-240V, 4-277V F(X) Fusing (specify voltage per above)					


¹ Type III 4673 absolute lumens 66 LPW
Type IV 4507 absolute lumens 63 LPW
² 350mA produces 2500-2700 lumens at 35w

Dimensions



Application Template Type IV

15ft. Mounting Height - 15ft Grids - 700 mA



Application Template Type III

15ft. Mounting Height - 15ft Grids - 700 mA

