



# LED

## Product Guide

# LED Round

## Round Remote Phosphor LED Downlights

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	F1332	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 <sup>3</sup> / <sub>8</sub> ", 8 <sup>13</sup> / <sub>16</sub> "	Wide
4"	F1334	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 <sup>3</sup> / <sub>8</sub> ", 8 <sup>13</sup> / <sub>16</sub> "	Medium
4"	F1336	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 <sup>3</sup> / <sub>8</sub> ", 8 <sup>13</sup> / <sub>16</sub> "	Narrow



## Round Remote Phosphor LED Directionals

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	F2333	Xicato®	Directional Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	7 <sup>3</sup> / <sub>16</sub> ", 9"	Wide
4"	F2335	Xicato®	Directional Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	7 <sup>3</sup> / <sub>16</sub> ", 9"	Medium
4"	F2337	Xicato®	Directional Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	7 <sup>3</sup> / <sub>16</sub> ", 9"	Narrow
4"	F2339	Xicato®	Directional Accent	1100, 1500	7 <sup>3</sup> / <sub>16</sub> "	Very Narrow



## Round Remote Phosphor LED Directional/Accent Pinhole

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
1 <sup>3</sup> / <sub>4</sub> "	A7104	Xicato®	Directional Pinhole	1100, 1500, 2100	6 <sup>5</sup> / <sub>8</sub> "	Medium

## Round Remote Phosphor LED Wall Washers

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	F1355	Xicato®	Lens Wall Washer	1100, 1500, 2100, 2800, 4000, 5000	6 <sup>15</sup> / <sub>16</sub> ", 9"	N/A



## Xicato® XTM Round - Install From Below

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
3"	F213	Xicato®	Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Wide
3"	F215	Xicato®	Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Medium
3"	F217	Xicato®	Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Narrow
3"	F242	Xicato®	Directional Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Wide
3"	F244	Xicato®	Directional Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Medium
3"	F246	Xicato®	Directional Downlight with Lens	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	Narrow
3"	F255	Xicato®	Lens Wall Washer	1100, 1500, 2100	6 <sup>3</sup> / <sub>8</sub> "	N/A

# LED Round Surface Forms

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	DEPTH	BEAM ANGLE
4" Ap/ 5" Dia.	L332	Xicato®	Surface Downlight	1100, 1500, 2100	7 <sup>1</sup> / <sub>2</sub> ", 10 <sup>1</sup> / <sub>2</sub> "	Wide
4" Ap/ 5" Dia.	L334	Xicato®	Surface Downlight	1100, 1500, 2100	7 <sup>1</sup> / <sub>2</sub> ", 10 <sup>1</sup> / <sub>2</sub> "	Medium
4" Ap/ 5" Dia.	L336	Xicato®	Surface Downlight	1100, 1500, 2100	7 <sup>1</sup> / <sub>2</sub> ", 10 <sup>1</sup> / <sub>2</sub> "	Narrow

# LED Square

## Square Remote Phosphor LED Downlights

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	J1342	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 1/4", 8 7/8"	Wide
4"	J1344	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 1/4", 8 7/8"	Medium
4"	J1346	Xicato®	Downlight with Lens	1100, 1500, 2100, 2800, 4000, 5000	6 1/4", 8 7/8"	Narrow



## Square Remote Phosphor LED Directionals

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	J2333	Xicato®	Directional Downlight	1100, 1500, 2100, 2800, 4000, 5000	7 5/8", 9 7/8"	Wide
4"	J2335	Xicato®	Directional Downlight	1100, 1500, 2100, 2800, 4000, 5000	7 5/8", 9 7/8"	Medium
4"	J2337	Xicato®	Directional Downlight	1100, 1500, 2100, 2800, 4000, 5000	7 5/8", 9 7/8"	Narrow



## Square Remote Phosphor LED Wall Washers

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4"	J1353	Xicato®	Lens Wall Washer	1100, 1500, 2100, 2800, 4000, 5000	7", 9 7/8"	N/A



## Xicato® XTM Square - Install From Below

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
3"	J312	Xicato®	Downlight with Lens	1100, 1500, 2100	6 3/4"	Wide
3"	J314	Xicato®	Downlight with Lens	1100, 1500, 2100	6 3/4"	Medium
3"	J316	Xicato®	Downlight with Lens	1100, 1500, 2100	6 3/4"	Narrow
3"	J315	Xicato®	Lens Wall Washer	1100, 1500, 2100	6 3/4"	N/A
3"	J343	Xicato®	Directional Downlight	1100, 1500, 2100	6 3/4"	Wide
3"	J345	Xicato®	Directional Downlight	1100, 1500, 2100	6 3/4"	Medium
3"	J347	Xicato®	Directional Downlight	1100, 1500, 2100	6 3/4"	Narrow

# LED Square Surface Forms

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	DEPTH	BEAM ANGLE
4" Ap/ 5" Dia.	L342	Xicato®	Surface Downlight	1100, 1500, 2100	7 1/2", 9 1/2"	Wide
4" Ap/ 5" Dia.	L344	Xicato®	Surface Downlight	1100, 1500, 2100	7 1/2", 9 1/2"	Medium
4" Ap/ 5" Dia.	L346	Xicato®	Surface Downlight	1100, 1500, 2100	7 1/2", 9 1/2"	Narrow

# LED Rectangle

## Rectangle Remote Phosphor LED Directional and Wall Washers

APERTURE	MODEL	SOURCE	FUNCTION	INITIAL LUMENS	HEIGHT	BEAM ANGLE
4" x 8"	D4216	Xicato®	Directional Downlight	2 x 1100, 1500	10"	Various
4" x 8"	D4516	Xicato®	Lens Wall Washer Parallel	2 x 1100, 1500	10"	N/A
4" x 9"	D4646	Xicato®	Lens Double Wall Washer	2 x 1100, 1500	10"	N/A



ALERA LIGHTING  
ARCHITECTURAL AREA LIGHTING  
BEACON PRODUCTS  
COLUMBIA LIGHTING  
COMPASS LIFE SAFETY  
DUAL-LITE  
HUBBELL CONTROL SOLUTIONS  
HUBBELL INDUSTRIAL LIGHTING  
HUBBELL OUTDOOR LIGHTING  
KIM LIGHTING  
KURT VERSEN  
LITECONTROL  
PRESCOLITE  
WHITEWAY

