

3 lumen Packages!



HUBBELL Outdoor Lighting

LNC LED COMPACT ARCHITECTURAL WALLPACK

COMPACT BY DESIGN

PACKED WITH PERFORMANCE



- Compact LED wallpack for entry/perimeter applications - 3 lumen output selections!
- Full cut-off neighbor friendly IDA approved
- DesignLights Consortium (DLC) qualified³
- 3000K, 4000K, 5000K high CRI LEDs
- Long life – 60,000hr L90 rating*
- Acrylic diffuser included! Use for applications near entrances or locations where reduced brightness is desired
- Quick-mount adapter provides easy installation

- Die-cast aluminum housing with decorative Laredo styling
- Designed for both recessed box or surface conduit wiring
- Up to 4:1 spacing to mounting height ratio means greater coverage – fewer fixtures to install
- Choice of bronze, black, white or platinum on LNC 7L/9L fixtures, LNC 5L is bronze only
- Photocontrol option for dusk-to-dawn control
- Listed to UL1598 for use in wet locations



LNC-9L 1806 Lumens



LNC-7L 1441 Lumens



LNC-5L 980 Lumens

High Power LEDs



5/7/9 – 5000K high CRI LEDs precisely aligned for optimal photometric performance. Provides excellent uniformity and spacing up to 40ft as well as mounting heights to 12ft.

Acrylic Diffuser




Frosted acrylic diffuser accessory – included with fixture! Softens output and protects LED lenses. Use near pedestrian entry applications.

Photo Control



Optional factory installed button photocontrols, 120V only.

Quick Mounting



Quick mount – easy mounting without opening fixture. Attach adapter plate to wall, connect wires, hang fixture and tighten set screws.



Hubbell Outdoor Lighting • 701 Millennium Boulevard Greenville, SC 29607
www.hubbelloutdoor.com • 864-678-1000 – Rev 3.15



ORDERING INFORMATION ON REVERSE SIDE

LNC LED COMPACT ARCHITECTURAL WALLPACK



The compact Laredo LED LNC is designed for perimeter illumination for safety, security and identity. Typical mounting height is up to 12 feet with 40ft fixture spacing (without acrylic diffuser) and 30ft spacing with acrylic diffuser installed. Photocontrol option is available on 120V configured fixtures.


ORDERING INFORMATION (EXAMPLES)

SERIES	NUMBER OF LEDS/SOURCE/VOLTAGE	CCT	IES DISTRIBUTION	FINISH	OPTIONS
LNC	5LU	3K	2	1	PC(X) ¹
LNC	7LU	4K ³	3 ³	2	Button photocontrol, replace X with voltage, specify 1-120V, 2-208V, 3-240V, 4-277V
LNC	9LU ³	5K ³	4 ³	3	
		AM ²		4	
				5	


1 When PC is ordered, input must match PC voltage
 2 Amber LEDs only available on 7LU and 9LU configurations, 350 mA only
 3 DesignLights Consortium (DLC) qualified 5/7/9 models 4K and 5K only

AM² Amber (590 nm) available for "Turtle Friendly"/observatory applications, 350 mA (consult factory)


LNC9LU - Type II



LNC9LU - Type III



LNC9LU - Type IV



HUBBELL
Outdoor Lighting

Hubbell Outdoor Lighting • 701 Millennium Boulevard Greenville, SC 29607
 www.hubbelloutdoor.com • 864-678-1000 – Rev 3.15



HUBBELL
Lighting