

HUBBELL OUTDOOR LIGHTING

combines innovative technology with practical lighting solutions and service oriented performance based on in-depth knowledge of the electrical distributor and contractor markets.

OUTDOOR TABLE OF CONTENTS

FLOODLIGHT	SLING43	PATROLMAN52
BEAM SPREAD GUIDE..... 37	PRELUDE44	DUSK TO DAWN
LIGHTSCAPER®.....38	PRELUDE44	PRODUCT SELECTION GUIDE..... 53
COLT LBUL38	WGH 1/2/346	SLING CANOPY54
MINI COLT39	PRS47	CANOPY
MARSHAL39	NRG® 300L47	PRODUCT SELECTION GUIDE..... 55
FLOODLIGHTS	WALL PACK	VAPORTITES56
PRODUCT SELECTION GUIDE..... 40	PRODUCT SELECTION GUIDE..... 48	VAPORTITE
WALL PACK	AIRO50	PRODUCT SELECTION GUIDE..... 57
MOUNTING HEIGHT GUIDE..... 42	SLING SGD.....52	



FLOODLIGHT


BEAM SPREAD GUIDE

AVAILABLE BEAM SPREAD



MODEL				
	Colt Mini MBUL	Marshal	Colt LBUL	Lightscaper®
EQUIVALENCY	70WHID	100W	100W	70W 100W
LUMENS	1100lm	2100lm	2637-2690lm	1000lm 2000lm
WATTS	13W	26.6W	20W	8W 20W

Not all configurations and outputs shown, please visit website for the most up-to-date information. Due to our continued efforts to improve our products, product specifications are subject to change without notice.



Center Beam Axis @ 0°
(typically max beam intensity measured as Center Beam Candle Power / CBCP)

Beam Angle
(angle within the beam of light equal to 50% of the max beam intensity)

Field Angle
(angle within the beam of light equal to 10% of the max beam intensity)

NEMA BEAM SPREAD CLASSIFICATION

Beam Spread Degrees (Field Angle)	NEMA Type	Beam Description
10° up to 18°	1	Very Narrow
18°-29°	2	Narrow
29°-46°	3	Medium Narrow
46°-70°	4	Medium
70°-100°	5	Medium Wide
100°-130°	6	Wide
130° and up	7	Very Wide


LIGHTSCAPER®

ARCHITECTURAL FLOODLIGHT

A versatile LED floodlight perfect for illuminating signs, trees and entrances or small area illumination. It features switchable lumen and CCT as well as adjustable knuckle pivot from 0–75°, with wide 6X7 flood distribution and tempered glass lens.



NEW



- 5yr WARRANTY
- 5000K
- 20W
- 70CRI

Fixture	Length	Width	Height	Weight
LSP-LSCS	12.0in.	2.8in.	4.0in.	3.3 lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Locations				Ctn Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93134707	LSP-LSCS	840141403939	984-2009	8W-20W	3K, 4K, 5K	1	70-100W	PGM3XQL6


COLT LBUL

MINI LED BULLET

Versatile 120-277V compact LED floodlight perfect for a variety of applications including: landscape, accent, pole/column, facade and small area illumination. Stake or threaded mounting plus adjustable knuckle provides mounting flexibility. Durable die-cast design with corrosion resistant powder coat paint finish for years of maintenance free illumination.



NEW



- 5yr WARRANTY
- 3500K, 4000K
- 20W
- 70CRI


Length	Width	Height	Weight
7.4 in.	4.2 in.	4.2 in.	1.5 lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93139362	LBUL-20-3K	840141404318	2637	20W	3000K	576	100W	PL72FGF2XK3
93139363	LBUL-20-4K	840141404325	2690	20W	4000K	576	100W	PLA55EQWAFUZ

MINI COLT

MINI LED BULLET

Versatile compact LED floodlight perfect for a variety of applications including: landscape, accent, pole/column, facade and small area illumination. Stake or threaded mounting and an adjustable knuckle provides mounting flexibility. Durable die-cast design with corrosion resistant powder coat paint finish for years of maintenance free illumination.



- 5yr WARRANTY
- 3000K
- 13W
- 83CRI


Length	Width	Height	Weight
3.9in.	3.2in.	6.2in.	2.0lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency
						CA	GA	IL	NJ		
MBUL1L3K1	MBUL-1L3K-1	785988031955	1115	13W	3000K	12	100W

MARSHAL

SECURITY FLOOD

Attractive security floodlight with 180° motion sensor with a coverage area of 72 feet. A powerful LED system saves energy and maintenance. The sensor includes time, sensitivity and distance adjustments.




- 5yr WARRANTY
- 3000K
- 26W
- 83CRI

Fixture	Length	Width	Height	Weight
ML	12.75in.	-	5.0 in.	2.2lbs.
MS	6.0in.	0.25in.	0.2in.	0.5lbs.



Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency
						CA	GA	IL	NJ		
ML2L3K1DB	ML-2L3K-1-DB	785988032723	2104	26W	3000K	144	100W
ML2L3K1WH	ML-2L3K-1-WH	785988032730	2104	26W	3000K	144	100W
Motion Sensor Only											
MSDB	MS-DB	785988032952	-	-	-	-	-
MSWH	MS-WH	785988032969	-	-	-	-	-

FLOODLIGHTS

PRODUCT SELECTION GUIDE

	GOOD	GOOD	BETTER	
	 Colt Mini	 Marshal	 Colt LBUL	
FEATURES	Easy to Install	Yes	Yes	
	Mounting Options	½" 14 NPS	Junction box	
	Features	+	++	
	Maintenance	Low, Aiming	Low, Aiming	
PERFORMANCE	Lumens	1115	2104	
	Watts	13W	20W	
	Efficacy (maximum LPW)	85	100	
	Distribution	NEMA 6X6 Wide	NEMA 6X6 Wide	
	CCT	3000K	3000K	
	CRI	70	80	
	Certifications	Listed for Wet Locations	UL1598 IP65	Listed for Wet Locations UL1598 IP65
			Yes Yes Yes	Yes Yes Yes
	Product Life	>60,000hrs.	>60,000hrs.	>60,000 hrs.
	HID Equivalence	70W	100W	100W
	Energy Savings (Based on HID Equivalence)	86%	85%	83%
	Voltage	120V	120V	120-277V
CONTROLS	Basic occupancy	-	Yes	
	Occupancy and Daylight Harvesting	-	Yes	

tradeSELECT


	BETTER	BEST	
	 Lightscaper	 Ratio Flood	
PERFORMANCE	Easy to Install	Yes	
	Mounting Options	½" 14 NPS	Threaded Knuckle, Slipfitter & Trunnion
	Features	++	+++
	Maintenance	Med, Aiming, Adjustment	Low, Aiming
	Lumens	984, 2009	3500-30,000
	Watts	8W, 16W	25-265W
	Efficacy (maximum LPW)	116-128	140
	Distribution	NEMA 7X6 Wide	Narrow, Medium, Wide
	CCT	3000K, 4000K, 5000K	3000K, 4000K, 5000K
	CRI	70-100	70
	Certifications	Listed for Wet Locations	UL1598 IP65
			Yes Yes Yes
Product Life	60,000hrs.	>60,000hrs.	
HID Equivalence	100W, 120-277V	100W, 1000V	
Energy Savings (Based on HID Equivalence)	86%	76%	
Voltage	120-277V	120-277V & 347-480V	
CONTROLS	Basic occupancy	-	
	Occupancy and Daylight Harvesting	-	

Hubbell Lighting



WALL PACK

MOUNTING HEIGHT GUIDE




Not all configurations and outputs shown, please visit website for the most up-to-date information. Due to our continued efforts to improve our products, product specifications are subject to change without notice.

SLING

PERIMETER WALLPACK/ FLOODLIGHT

This slender wallpack is available in two sizes for a variety of applications. Its low profile form and wide range of outputs heights provide a scalable solution for mounting heights from eight to twenty feet. SLING luminaires feature a tempered glass lens, IP65 rating and floodlight mounting accessories.



Fixture	Length	Width	Height	Weight
SG1	7.4in.	4.2in.	7.8in.	4.4lbs.
SG2	9.0in.	9.5in.	11.1in.	11.0lbs.




Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
SLING Small												
SG1104KPCU	SG1-10-4K-PCU	785988044726	1424	11W	4000K	192	70W	P56L9PT8
SG1204KPCU	SG1-20-4K-PCU	785988033201	2310	21W	4000K	192	100W	PJXKHKE3
SG1304KPCU	SG1-30-4K-PCU	785988033225	3060	29W	4000K	192	150W	PH9F4HZ2
SG1404KPCU	SG1-40-4K-PCU	785988044740	4070	38W	4000K	192	175W	P56L9PT8
SG110PCU	SG1-10-PCU	785988044719	1349	11W	5000K	192	70W	P1RK1H5S
SG120PCU	SG1-20-PCU	785988033195	2263	21W	5000K	192	100W	PTSFD2YY
SG130PCU	SG1-30-PCU	785988033157	3270	29W	5000K	192	150W	PUCXBQEM
SG140PCU	SG1-40-PCU	785988044733	4008	38W	5000K	192	175W	P1RK1H5S
SLING Large												
SG2504KPCU	SG2-50-4K-PCU	785988033232	5526	51W	4000K	192	200W	PZTF3TT9
SG2804KPCU	SG2-80-4K-PCU	785988033232	8079	80W	4000K	192	250W	P25GRESH
SG250PCU	SG2-50-PCU	785988033171	5548	51W	5000K	192	200W	PK8TJMHT
SG280PCU	SG2-80-PCU	785988033188	8061	80W	5000K	192	250W	PXEQCQB8
Accessories												
SG1-KNUCKLE	SG1-KNUCKLE	785988033270	-	-	-	-	-	-
SG1-YOKE	SG1-YOKE	785988033249	-	-	-	-	-	-
SG2-KNUCKLE	SG2-KNUCKLE	785988038909	-	-	-	-	-	-
SG2-YOKE	SG2-YOKE	785988038893	-	-	-	-	-	-

PRELUDE

SWITCHABLE FULL CUTOFF WALLPACK

The Prelude Wallpack luminaire offers an architectural contemporary form with maximum flexibility. This luminaire features field selectable Wattages from 18 to 60 Watts. The cutoff configuration is perfect for applications requiring no up-light.



Fixture	Length	Width	Height	Weight
PRL-C-LS-4K	14.9in.	6.3in.	9.1in.	5.3lbs.


- 5 yr WARRANTY
- 4000K
- 29-100W
- 80CRI
- SWITCHABLE LUMEN

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93138997	PRL-C-LS-4K	840141404271	2537-8460	18-60W	4K	48	up to 250W	P10VAZ90

PRELUDE

SWITCHABLE REFRACTOR WALLPACK

The Prelude Wallpack luminaire offers an architectural contemporary form with maximum flexibility. This luminaire features field selectable Wattages from 18 to 60 Watts. The refractor configuration features a vandal resistant polycarbonate lens that provides ambient lighting for safety and security to any facility



Fixture	Length	Width	Height	Weight
PRL-R-LS-4K	14.9in.	5.1in.	9.1in.	5.3lbs.

- 5 yr WARRANTY
- 4000K
- 29-100W
- 80CRI
- SWITCHABLE LUMEN


Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93138996	PRL-R-LS-4K	840141404264	2553-8510	18-60W	4K	48	up to 250W	P10VAZ90



WGH 1/2/3

SWITCHABLE GLASS REFRACTOR WALLPACK

Featuring switchable lumen and wattage technology. Borosilicate glass refractor softens LED and provides uniform distribution. Field switchable lumens and LED color temperature (4000K, 4500K, & 5000K); wall mount at heights from 15-25ft.



Fixture	Length	Width	Height	Weight
WGH1-LS	10.8in.	7.6in.	8.3in.	8.38lbs.
WGH2-LSCS	14.4in.	9.3in.	7.4in.	10.8lbs.
WGH3-LSCS	17.9in.	9in.	9.4in.	13.89lbs.


- 5 yr WARRANTY
- 4000K, 5000K
- 29-100W
- 80CRI
- SWITCHABLE WATTAGE & CCT

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
WGH Small												
93139532	WGH1-LS-4K	840141404332	3,000-7,000	20-50W	4K	N/A	Up to 200W	PL3BWPOYJYAF
93139535	WGH1-LS-4K-PC		3,000-7,000	20-50W	4K	N/A	Up to 200W	PL3BWPOYJYAF
WGH Medium												
93131680	WGH2-LSCS	84014147950	4600-10,000	30-70W	4K, 4.5K, 5K	48	up to 250W	PLXSRKF8MH1M
WGH Large												
93131681	WGH3-LSCS	84014147967	11,500-17,150	80-120W	4K, 4.5K, 5K	32	up to 400W	PLF3SKV82KF6

PRS

PERIMASHIELD WALLPACK

Compact stylish wallpack constructed of die-cast aluminum. Features impact resistant UV stabilized polycarbonate refractor. Mounts to standard 3- 3-1/2" junction boxes with 1/2" conduit entry for surface mount applications. Optional photocontrol available for dusk to dawn operations.



Length	Width	Height	Weight
10.9 in.	4.1 in.	4.9 in.	2.75 lbs.


- 5 yr WARRANTY
- 4000K, 5000K
- 22W
- 80CRI

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93134453	PRS-20-4K-PC	785988045563	2841	20W	4000K	160	100W	PLNWIXXG7LNV
93134454	PRS-20-5K-PC	785988045570	2899	20W	5000K	160	100W	PLR2TUO8Y8TN

NRG® 300L

POLYCARBONATE WALLPACK

Energy-efficient LED, features a one-piece polycarbonate front, vandal proof construction, dark bronze architectural finish. Photocontrol is available. Entry or single story perimeter lighting for safety, security and identity. Ideal for commercial buildings, shopping centers, schools, apartment complexes as well as non-supervised vandal prone applications.






Length	Width	Height	Weight
5.4in.	6.9in.	11.2in.	6.0lbs.


- 5 yr WARRANTY
- 4000K, 5000K
- 16W
- 80CRI

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93092004	NRG-356L-4K-U	785988031399	1858	16W	4000K	144	70W	PS9D61BU
93092005	NRG-356L-4K-U-PC	785988031405	1858	16W	4000K	144	70W	PS9D61BU
93092006	NRG-356L-5K-U	785988031412	1794	16W	5000K	144	70W	PXT41W62
93092007	NRG-356L-5K-U-PC	785988031429	1794	16W	5000K	144	70W	PXT41W62

WALL PACK

PRODUCT SELECTION GUIDE



		GOOD			GOOD			BETTER		
		tradeSELECT®			tradeSELECT®			tradeSELECT®		
										
		NRG® 300L			PRS PERIMASHIELD			WGH1		
FEATURES	Easy to Install	Yes			Yes			Yes		
	Mounting Options	Junction box			Junction Box			Junction box		
	Features	+			+			++		
	Maintenance	Low			Low			Low		
PERFORMANCE	Lumens	1800			2841-2899			3000-7000		
	Watts	17W			20W			20-50W		
	Efficacy (maximum LPW)	110			106			140-146		
	Distribution	Type IV			Type IV			Type IV		
	CCT	4000K, 5000K			4000K, 5000K			4000K		
	CRI	70			70			70		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
	Yes	Yes	-	Yes	Yes	-	Yes	Yes	Yes	
CONTROLS	Product Life	>60,000hrs.			>60,000hrs.			>60,000hrs.		
	HID Equivalence	70W			100W			Up to 200W		
	Energy Savings (Based on HID Equivalence)	75%			77%			75-80%		
	Voltage	120-277V			120-277V			120-277V		
	Basic occupancy	Yes			Yes			Yes		
	Occupancy and Daylight Harvesting	Photocontrol			Photocontrol			Optional Photocontrol		
	Integrated Controls	-			-			-		

		BETTER						BEST BEST					
		tradeSELECT®			tradeSELECT®			tradeSELECT®			Additional Wallpaper		
													
		WGH2/WGH3			SLING WALL			PRELUDE WALLPACKS			Ratio Wall		
	Yes	Yes			Yes			Yes			Yes		
	Junction box	Junction box			Side door, Junction box			Mounting Plate, Junction box			Junction box, Conduit		
	+++	+++			+++			+++			+++		
	Low	Low			Low			Low			Low		
	4600-17,200	4600-17,200			2200-8100			2500-8600			1000-19,500		
	30-120W	30-120W			21-80W			18W-60W			10-155W		
	140-147	140-147			110-115			139-144			148		
	Type IV	Type IV			Type IV			Type III (Cut Off), Type IV (Reflector)			Type II, Type III, Type IV		
	4000K, 4500, 5000K	4000K, 4500, 5000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K			3000K, 4000K, 5000K		
	70	70			70			70			70		
	Listed for Wet Locations	UL1598	IP65	IP65	UL1598	IP65	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	>60,000hrs.	>60,000hrs.			>60,000hrs.			>60,000hrs.			>60,000hrs.		
	150-400W	150-400W			100-250W			70-250W			42-400W		
	75-80%	75-80%			70-80%			75-80%			76%		
	120-277V	120-277V			120-277V			120-277V			120-277V & 347-480V		
	Yes	Yes			Yes			-			Yes		
	Photocontrol	Photocontrol			Yes			-			Yes		
	-	-			SiteSync™			Switchable			SiteSync™, NX Integrated Intelligence™		

AIRO

AREA/SITE

Compact sleek design with high performance LED configurations and simple installation. The Airo TradeSelect offers four stock configurations which include a universal mounting block for easy pole installation.



2.0 fc 1.0 fc 0.5 fc

Fixture	Length	Width	Height	Weight
ASL1	10.9in.	11.7in	5.65in.	14.5lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93139453	ASL1-100-4W-ASQU	840141404370	12,000	100W	4000K	-	250W	PDHPPF527
93139454	ASL1-100-3-ASQU	840141404387	12,000	100W	4000K	-	250W	PKCERJHC
93139455	ASL1-135-4W-ASQU	840141404394	18,000	135W	4000K	-	400W	PUB3T3U6
93139456	ASL1-135-3-ASQU	840141404400	18,000	135W	4000K	-	400W	PUB3T3U6

STOCK POLE COMBO


Catalog Number	Pole	Single or Double	Fixture	Distribution
ASL1-100-4K7-3-S20	20' Square Straight Steel	Single Head	ASL-160L-100-4K7	3
ASL1-100-4K7-4W-S20	20' Square Straight Steel	Single Head	ASL-160L-100-4K7	4W
ASL1-100-4K7-3-S20-2X	20' Square Straight Steel	Double Head (180°)	ASL-160L-100-4K7	3
ASL1-100-4K7-4W-S20-2X	20' Square Straight Steel	Double Head (180°)	ASL-160L-100-4K7	4W
ASL1-100-4K7-3-S25	25' Square Straight Steel	Single Head	ASL-160L-100-4K7	3
ASL1-100-4K7-4W-S25	25' Square Straight Steel	Single Head	ASL-160L-100-4K7	4W
ASL1-100-4K7-3-S25-2X	25' Square Straight Steel	Double Head (180°)	ASL-160L-100-4K7	3
ASL1-100-4K7-4W-S25-2X	25' Square Straight Steel	Double Head (180°)	ASL-160L-100-4K7	4W
ASL1-135-4K7-3-S20	20' Square Straight Steel	Single Head	ASL-160L-135-4K7	3
ASL1-135-4K7-4W-S20	20' Square Straight Steel	Single Head	ASL-160L-135-4K7	4W
ASL1-135-4K7-3-S20-2X	20' Square Straight Steel	Double Head (180°)	ASL-160L-135-4K7	3
ASL1-135-4K7-4W-S20-2X	20' Square Straight Steel	Double Head (180°)	ASL-160L-135-4K7	4W
ASL1-135-4K7-3-S25	25' Square Straight Steel	Single Head	ASL-160L-135-4K7	3
ASL1-135-4K7-4W-S25	25' Square Straight Steel	Single Head	ASL-160L-135-4K7	4W
ASL1-135-4K7-3-S25-2X	25' Square Straight Steel	Double Head (180°)	ASL-160L-135-4K7	3
ASL1-135-4K7-4W-S25-2X	25' Square Straight Steel	Double Head (180°)	ASL-160L-135-4K7	4W



SLING SGD

DUSK TO DAWN SECURITY LUMINAIRE

This stylish dusk-to-dawn area luminaire can be pole mounted or wall mounted and comes standard with a drop-down lens and integral twist-lock photocell.



- 5 yr WARRANTY
- 4000K
- 40-60W
- 70CRI


Length	Width	Height	Weight
16.1in.	8.9in.	6.4in.	7.4lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93134449	SGD-40-4K-GR	785988045723	5700	40W	4000K	•	•	•	•	50	150W	PNWUPH67
93134450	SGD-60-4K-GR	785988045730	8300	60W	4000K	•	•	•	•	50	150W	POLM68DC
93134451	SGD-60-4K	785988045754	8300	60W	4000K	•	•	•	•	50	250W	POLM68DC
93134452	SGD-40-4K	785988045761	5700	40W	4000K	•	•	•	•	50	150W	PNWUPH67
Accessories												
ARMDD24	ARM-DD24	785988033287	-	-	-	•	•	•	•	192	-	-
ARMDD30	ARM-DD30	785988033294	-	-	-	•	•	•	•	192	-	-

PATROLMAN

MULTI-PURPOSE SECURITY LUMINAIRE

Rugged die-cast aluminum housing with both 2-3/8" & 1-5/8" OD mast arm mount capability as well as direct wall, surface mounting. Less refractor provides zero uplight design for environmentally friendly installations.



- 5 yr WARRANTY
- 5000K
- 32-111W
- 70CRI

Length	Width	Height	Weight
9.45in.	6.5in.	8.25in.	6.8lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
DDL9L1	DDL-9L1	785988030699	4230	39W	5000K	•	•	•	•	40	175W	PC9A87FGV


DUSK TO DAWN

PRODUCT SELECTION GUIDE

		GOOD	BETTER	BEST						
		<p>PATROLMAN</p>	<p>SLING SGD</p>	<p>Airo</p>						
FEATURES	Easy to Install	Yes	Yes	Yes						
	Mounting Options	2 3/8"-1 5/8", Pipe & Wall Mount	2 3/8"-1 5/8", Pipe & Wall Mount	Universal Arm Mount, Mast Arm Fitter Accessory, Wall Mount Accessory						
	Features	+	++	+++						
	Maintenance	Low	Low	Low						
PERFORMANCE	Lumens	4320	5700-8300	12,000-18,000						
	Watts	39W	40, 60W	100-135W						
	Efficacy (maximum LPW)	108	142-143	127-138						
	Distribution	Symmetric Type V	Type V	Type III, Type IV						
	CCT	5000K	4000K	4000K						
	CRI	70	70	70						
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
		Product Life	>60,000hrs.	>60,000hrs.	>60,000hrs.					
	HID Equivalence	150W	100-250W	250-400W						
Energy Savings (Based on HID Equivalence)	78%	78%	78%							
Voltage	120-277V	120-277V	120-277V							

SLING CANOPY

NEW



- 5 yr WARRANTY
- 4000K
- 25-60W
- 70CRI

Length	Width	Height	Weight
10.2in.	3.6in.	6.4in.	4.9lbs.

CANOPY

The low-profile SLING canopy luminaire provides a perfect retrofit solution for existing HID canopy luminaires up to 250W. The impact resistant polycarbonate lens increases durability while also reducing unwanted glare. Versatile surface or pendant mount.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency	DLC Listing
						CA	GA	IL	NJ			
93134457	SGC-F-20-4K	785988045792	3224	20	4000K	168	100W	PJMKOUYW
93134458	SGC-F-40-4K	785988045808	5807	40	4000K	168	150W	PL50390MM0P2
93134460	SGC-F-40-4K-WHT	785988045822	5807	40	4000K	168	150W	PAXG1BYV
93134459	SGC-F-60-4K	785988045815	8043	60	4000K	168	250W	PLFEFP38PUGM

CANOPY


PRODUCT SELECTION GUIDE

		GOOD	BETTER	BEST	
		 SLING CANOPY	 LUMASQUARE	 BEACON DRIVE	
FEATURES	Easy to Install	Yes	Yes	Yes	
	Mounting Options	Standard J-Box-3/4" Pendant, 3 sided 1/2" 14 NPS threaded conduit entry	Standard J-Box or 3/4" Pendant	Standard J-Box or 3/4" Pendant	
	Features	++	++	+++	
	Maintenance	Low	Low	Low	
PERFORMANCE	Lumens	3200-8000	3000-9000	2,500-16,000	
	Watts	20-60W	25-75W	20-55W	
	Efficacy (maximum LPW)	134-142	120-127	109-125	
	Distribution	Type V	Type V	Type V, Type VC, Type VRW, Type IV	
	CCT	4000K	3000K, 4000K, 5000K	3000K, 4000K, 5000K	
	CRI	70	70	70	
	Certifications	Listed for Wet Locations	UL1598 IP65	Listed for Wet Locations UL1598 IP65	Listed for Wet Locations UL1598 IP65
		Yes	Yes Yes	Yes Yes Yes	Yes Yes Yes
	Product Life	>60,000hrs.	>60,000hrs.	>60,000hrs.	
	HID Equivalence	100-250W	175-250W	175-250W	
Energy Savings	75%	75%	78%		
Voltage	120-277V	120-277V	120-277V		
CONTROLS	Basic occupancy	-	Yes	Yes	
	Occupancy and Daylight Harvesting	-	Yes	Yes	
	Integrated Controls	-	SiteSync™	NX	

VAPORTITES

CEILING/WALL VAPORTITES

Rugged die-cast aluminum construction, frosted globe with guard, wet location listed, energy-efficient LED vaportites for ceiling, pendant, wall mount. Use for entry, corridors, tunnels, service passages, stairwells. Gray powder paint finish.



- 5 YEAR WARRANTY
- 4100K
- 11W
- 80CRI

Colored Globe Accessories



VGL-GN VGL-YW VGL-BU VGL-RD



Fixture	Length	Width	Height	Weight
VGBL-1	-	5.2in.	10.37in.	3.5lbs.
VWGL-1	7.34in.	5.2in.	11.0in.	3.6lbs.
Accessories				
VGL-FG	-	3.8in.	8.2in.	1.0lbs.
Colored Globes	-	3.8in.	8.2in.	1.0lbs.
VGL-GUARD	-	4.2in.	8.3in.	0.5lbs.

Part #	Catalog #	UPC	Lumens	Watts	CCT	Stock Location				Pallet Qty	Equivalency
						CA	GA	IL	NJ		
93092008	VGBL-1	785988030651	757	11W	4100K	•	•	•	-	-	70W
93092009	VWGL-1	785988030668	757	11W	4100K	•	•	•	-	-	70W
Accessories											
VGL-FG	VGL-FG	78598841282	-	-	-	•	•	-	-	-	-
VGL-GUARD	VGL-GUARD	-	-	-	-	•	-	-	-	-	-
Colored Globes											
VGL-GN	VGL-GN	78598841299	-	-	-	•	-	-	-	-	-
VGL-YW	VGL-YW	78598841312	-	-	-	•	-	-	-	-	-
VGL-BU	VGL-BU	78598841275	-	-	-	•	-	-	-	-	-
VGL-RD	VGL-RD	78598841305	-	-	-	•	-	-	-	-	-

VAPORTITE

PRODUCT SELECTION GUIDE

GOOD

		tradeSELECT®			tradeSELECT®		
		 VGBL			 VWGL		
FEATURES	Easy to Install	Yes			Yes		
	Mounting Options	Standard J-Box-Ceiling-4 sided ½" 14 NPS threaded conduit entry			Standard J-Box-4 sided ½" 14 NPS threaded conduit entry		
	Features	++			++		
	Maintenance	Low			Low		
PERFORMANCE	Lumens	757			757		
	Wattage	11W			11W		
	Efficacy (maximum LPW)	70			70		
	CCT	4100K			4100K		
	CRI	80			80		
	Certifications	Listed for Wet Locations	UL1598	IP65	Listed for Wet Locations	UL1598	IP65
		Yes	Yes	Yes	Yes	Yes	Yes
	Product Life	60,000hrs.			60,000hrs.		
	HID Equivalence	100w			100w		
	Energy Savings (Based on HID Equivalence)	82%			82%		
Voltage	120-277V			120-277V			

