


WHOLESALE DISTRIBUTION CATALOG





For over 125 years Hubbell has been a manufacturer and innovator of best-in-class electrical and electronic products serving the residential, non-residential, construction, industrial and utility markets. The Hubbell Gas Utility Solutions group (HGUS) now brings that same business expertise and spirit of innovation to the natural gas market.

- Gas Distribution (LDC)
- Gas Transmission
- Wholesale Plumbing & LP
- Gas Transmission & Midstream

Please visit hubbell.com where you can learn more about the benefits and products from Hubbell Gas Utility Solutions.

Con-Stab ID Seal® Fittings	Page #
Con-Stab ID Seal® Full Couplings	4
Con-Stab ID Seal® End Caps	4
Con-Stab ID Seal® Cap-N-Go Couplings	4
Con-Stab ID Seal® 3-Way Tees	5
Con-Stab ID Seal® 90° Elbows	5
Con-Stab ID Seal® PE x Copper Transition Coupling	5
Con-Stab ID Seal® Reducer Couplings	6
Con-Stab ID Seal® Reducing 3-Way Tees	7
Con-Stab ID Seal® Eliminator Saddles	15
Con-Stab ID Seal® HVT Eliminator Saddles	16
Con-Stab ID Seal® Transition Fittings	19-22

LycoFit® Mechanical Fittings	Page #
LycoFit® Mechanical Couplings	10
LycoFit® Mechanical End Caps	10
LycoFit® Mechanical 3-Way Tees	10
LycoFit® 90° Elbows	10
LycoFit® Reducer Couplings	11
LycoFit® Steel to PE Transition Fittings	11
LycoFit® P.E. x Copper Tubing Adapter	11

Compression Fittings	Page #
Continental Industries PA Full Couplings	13
Continental Industries PA End Caps	13
Continental Industries PA 3-Way Tees	13
Continental Industries PA 90° Elbows	14
Continental Industries PA Reducer Couplings	14
Continental Industries Eliminator Saddles	15
Continental Industries HVT Saddles	16-17

Transition Fittings	Page #
Lyall Threaded Transition Fittings	19
Con-Stab ID Seal® Transition Fittings	20-22
Continental Industries Transition Fittings	20-22

Meter Risers	Page #
Lyall Anodeless Meter Risers	23
Continental Industries Anodeless Meter Risers	26
Lyall Flexible Service Head Adapter Risers	25
Continental Industries Conflex Risers	26
Lyall Transition (ANODE) Risers	27
Riser Brackets	28-29

PolyTec Ball Valves	Page #
PolyTec High Density PE Valve	30

Tools & Accessories	Page #
LycoFit® Assembly Tools	12
Con-Stab® Chamfer Tools	8
Accessories for Eliminator Saddles	9 & 18



Con-Stab ID Seal®
Full Couplings



Con-Stab ID Seal®
End Caps



Con-Stab ID Seal®
Cap-N-Go Couplings

PE SIZE	WALL	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	3259-52-1004-00
3/4" CTS (7/8" OD)	.090	3259-52-1006-00
1" CTS (1 1/8" OD)	.099/.101	3259-52-1008-00
	.090	3259-52-1008-AA
1 1/4" CTS (1 3/8" OD)	.090	3259-52-1039-AA
1/2" IPS	SDR-9.33 (.090)	3259-52-1012-00
3/4" IPS	SDR-11 (.095)	3259-52-1013-00
1" IPS	SDR-11 (.119)	3259-52-1014-00
1 1/4" IPS	SDR-10 (.166)	3259-52-1015-00
	SDR-11 (.151)	3259-52-1015-AA
1 1/2" IPS	SDR-11 (.173)	3259-52-1016-00
2" IPS	SDR-11 (.216)	3259-52-1017-00

• For sizes not listed, contact Continental Industries.

PE SIZE	WALL	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	3259-53-1004-00
3/4" CTS (7/8" OD)	.090	3259-53-1006-00
1" CTS (1 1/8" OD)	.099/.101	3259-53-1008-00
	.090	3259-53-1008-OA
1 1/4" CTS (1 3/8" OD)	.090	3259-53-1039-OA
1/2" IPS	SDR-9.33 (.090)	3259-53-1012-00
3/4" IPS	SDR-11 (.095)	3259-53-1013-00
1" IPS	SDR-11 (.119)	3259-53-1014-00
1 1/4" IPS	SDR-10 (.166)	3259-53-1015-00
	SDR-11 (.151)	3259-53-1015-OA
1 1/2" IPS	SDR-11 (.173)	3259-53-1016-00
2" IPS	SDR-11 (.216)	3259-53-1017-00

• For sizes not listed, contact Continental Industries.

PE SIZE	WALL	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	3259-57-1004-00
1" CTS (1 1/8" OD)	.099/.101	3259-57-1008-00
	.090	3259-57-1008-AA
1/2" IPS	SDR-9.33 (.090)	3259-57-1012-00
3/4" IPS	SDR-11 (.095)	3259-57-1013-00
1" IPS	SDR-11 (.119)	3259-57-1014-00
1 1/4" IPS	SDR-10 (.166)	3259-57-1015-00
	SDR-11 (.151)	3259-57-1015-AA
2" IPS	SDR-11 (.216)	3259-57-1017-00

• For sizes not listed, contact Continental Industries.

PE SIZE	WALL	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	3259-50-1004-00
3/4" CTS (7/8" OD)	.090	3259-50-1006-00
1" CTS (1 1/8" OD)	.099/.101	3259-50-1008-00
	.090	3259-50-1008-AA
1 1/4" CTS (1 3/8" OD)	.090	3259-50-1039-AA
1/2" IPS	SDR-9.33 (.090)	3259-50-1012-00
3/4" IPS	SDR-11 (.095)	3259-50-1013-00
1" IPS	SDR-11 (.119)	3259-50-1014-00
1 1/4" IPS	SDR-10 (.166)	3369-50-1015-00*
	SDR-11 (.151)	3259-50-1015-AA
1 1/2" IPS	SDR-11 (.173)	3259-50-1016-00
2" IPS	SDR-11 (.216)	3259-50-1017-00

- For sizes not listed, contact Continental Industries.
- * = 1 1/4" IPS SDR-10 Fitting is only available in PE 2406 yellow.

PE SIZE	WALL	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	3259-51-1004-00
3/4" CTS (7/8" OD)	.090	3259-51-1006-00
1" CTS (1 1/8" OD)	.099/.101	3259-51-1008-00
	.090	3259-51-1008-AA
1 1/4" CTS (1 3/8" OD)	.090	3259-51-1039-AA
1/2" IPS	SDR-9.33 (.090)	3259-51-1012-00
3/4" IPS	SDR-11 (.095)	3259-51-1013-00
1" IPS	SDR-11 (.119)	3259-51-1014-00
1 1/4" IPS	SDR-10 (.166)	3369-51-1015-00
	SDR-11 (.151)	3259-51-1015-AA
1 1/2" IPS	SDR-11 (.173)	3259-51-1016-00
2" IPS	SDR-11 (.216)	3259-51-1017-00

- For sizes not listed, contact Continental Industries.

PE SIZE	WALL	COPPER SIZE	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	1/4" OD	9943-99-0062-00
		3/8" OD	9943-99-0063-00
		1/2" OD	9943-99-0064-00
		5/8" OD	9943-99-0065-00
3/4" IPS	SDR-11 (.095)	5/8" OD	9943-99-0066-00

- For sizes not listed, contact Continental Industries.



Con-Stab ID Seal®
3-Way Tees



Con-Stab ID Seal®
90° Elbows



Con-Stab ID Seal®
P.E. x Copper Transition Couplings



Con-Stab ID Seal®
Reducer Couplings

PE SIZE	WALL	PE SIZE	WALL	PART NUMBER (3408/4710)
3/4" CTS (7/8" OD)	.090	1/2" CTS (5/8" OD)	.090	3259-54-0604-00
1" CTS (1 1/8" OD)	.099/.101	3/4" IPS	SDR-11 (.095)	3259-54-0813-00
	.090			3259-54-0813-A0
	.099/.101	3/4" CTS (7/8" OD)	.090	3259-54-0806-00
	.090			3259-54-0806-A0
	.099/.101	1/2" IPS	SDR-9.33 (.090)	3259-54-0812-00
	.090			3259-54-0812-A0
	.099/.101	1/2" CTS (5/8" OD)	.090	3259-54-0804-00
	.090			3259-54-0804-A0
1 1/4"CTS (1 3/8"OD)	.090	1" IPS	SDR-11	3259-54-3914-A0
		1" CTS (1 1/8" OD)	.099/.101	3259-54-3908-A0
				.090
1/2" IPS	SDR-9.33 (.090)	1/2" CTS (5/8" OD)	.090	3259-54-1204-00
3/4" IPS	SDR-11 (.095)	1/2" IPS	SDR-9.33 (.090)	3259-54-1312-00
		3/4" CTS (7/8" OD)	.090	3259-54-1306-00
		1/2" CTS (5/8" OD)	.090	3259-54-1304-00
1" IPS	SDR-11 (.119)	1" CTS (1 1/8" OD)	.099/.101	3259-54-1408-00
			.090	3259-54-1408-OA
		3/4" IPS	SDR-11 (.095)	3259-54-1413-00
		3/4" CTS (7/8" OD)	.090	3259-54-1406-00
		1/2" IPS	SDR-9.33 (.090)	3259-54-1412-00
		1/2" CTS	.090	3259-54-1404-00
1 1/4" IPS	SDR-10 (.166)	1 1/4" IPS	SDR-11 (.151)	3259-54-1515-OA
	SDR-11 (.151)	1 1/4" CTS (1 3/8" OD)	.090	3259-54-1539-AA
	SDR-10 (.166)	1" IPS	SDR-11 (.119)	3259-54-1514-00
	SDR-11 (.151)			3259-54-1514-A0
	SDR-10 (.166)	1" CTS (1 1/8" OD)	.099/.101	3259-54-1508-00
	SDR-11 (.151)		.090	3259-54-1508-OA
			.099/.101	3259-54-1508-A0
			.090	3259-54-1508-AA
	SDR-10 (.166)	3/4" IPS	SDR-11 (.095)	3259-54-1513-00
SDR-11 (.151)	3259-54-1513-A0			
1 1/2" IPS	SDR-11 (.173)	3/4" IPS	SDR-11 (.095)	3259-54-1613-00
		1" IPS	SDR-11 (.119)	3259-54-1614-00
		1 1/4" IPS	SDR-10 (.166)	3369-54-1615-00
			SDR-11 (.151)	3259-54-1615-OA
2" IPS	SDR-11	1 1/2" IPS	SDR-11 (.173)	3259-54-1716-00
		1 1/4" IPS	SDR-10 (.166)	3369-54-1715-00
			SDR-11 (.151)	3259-54-1715-OA
		1" IPS	SDR-11 (.119)	3259-54-1714-00
		1" CTS (1 1/8" OD)	.099/.101	3259-54-1708-00
			.090	3259-54-1708-OA

• For sizes not listed, contact Continental Industries.

PE SIZE (Run)	WALL	PE SIZE (Branch)	WALL	PART NUMBER (3408/4710) HDPE	PART NUMBER (2406) MDPE
1/2" CTS (5/8" OD)	.090	1" CTS (1 1/8" OD)	.099/.101	3259-49-0408-00	3369-49-0408-00
		1" CTS (1 1/8" OD)	.090	3259-49-0408-0A	3369-49-0408-0A
3/4" CTS (7/8" OD)	.090	1/2" CTS (5/8" OD)	.090	3259-49-0604-00	3369-49-0604-00
1" CTS (1 1/8" OD)	.099/.101	1/2" CTS (5/8" OD)	.090	3259-49-0804-00	3369-49-0804-00
	.090			3259-49-0804-A0	3369-49-0804-A0
1 1/4" CTS (1 3/8" OD)	.090	1/2" CTS (5/8" OD)	.090	3259-49-3904-A0	3369-49-3904-A0
1/2" IPS	SDR-9.33 (.090)	1/2" CTS (5/8" OD)	.090	3259-49-1204-00	3369-49-1204-00
3/4" IPS	SDR-11 (.095)	1/2" CTS (5/8" OD)	.090	3259-49-1304-00	3369-49-1304-00
1" IPS	SDR-11 (.119)	1" CTS (1 1/8" OD)	.099/.101	3259-49-1408-00	3369-49-1408-00
			.090	3259-49-1408-0A	3369-49-1408-0A
		3/4" IPS	SDR-11 (.095)	3259-49-1413-00	3369-49-1413-00
		1/2" CTS	.090	3259-49-1404-00	3369-49-1404-00
		1/2" IPS	SDR-9.33 (.090)	3259-49-1412-00	3369-49-1412-00
1 1/4" IPS	SDR-10 (.166)	1" CTS (1 1/8" OD)	.099/.101	Not Available	3369-49-1508-00
			.090	Not Available	3369-49-1508-0A
	SDR-11 (.151)		.099/.101	3259-49-1508-A0	Not Available
			.090	3259-49-1508-AA	Not Available
	SDR-10 (.166)	1" IPS	SDR-11 (.119)	3259-49-1514-00	3369-49-1514-00
	SDR-11 (.151)			3259-49-1514-A0	3369-49-1514-A0
	SDR-10 (.166)	3/4" IPS	SDR-11 (.095)	Not Available	3369-49-1513-00
	SDR-11 (.151)			3259-49-1513-A0	Not Available
1 1/2" IPS	SDR-11 (.173)	1 1/4" IPS	SDR-10 (.166)	3259-49-1615-00	3369-49-1615-00
			SDR-11 (.151)	3259-49-1615-0A	3369-49-1615-0A
		1" IPS	SDR-11 (.119)	3259-49-1614-00	3369-49-1614-00
		3/4" IPS	SDR-11 (.095)	3259-49-1613-00	3369-49-1613-00
2" IPS	SDR-11	1 1/2" IPS	SDR-11 (.173)	3259-49-1716-00	3369-49-1716-00
		1 1/4" IPS	SDR-10 (.166)	Not Available	3369-49-1715-00
			SDR-11 (.151)	3259-49-1715-0A	3369-49-1715-0A
		1" IPS	SDR-11 (.119)	3259-49-1714-00	3369-49-1714-00
		3/4" IPS	SDR-11 (.095)	3259-49-1713-00	3369-49-1713-00
		1" CTS (1 1/8" OD)	.099/.101	3259-49-1708-00	3369-49-1708-00
			.090	3259-49-1708-0A	3369-49-1708-0A

• For sizes not listed, contact Continental Industries.



Con-Stab ID Seal®
Reducing Tees





Double Ended ID Chamfer Tools



ID Chamfer Tools With Gauge

PART NUMBER	DESCRIPTION
0000-33-5647-00	1/2" IPS X 1/2" CTS (5/8" OD)
0000-33-5481-00	3/4" IPS X 1/2" CTS (5/8" OD)
0000-33-5652-00	3/4" IPS X 1/2" IPS
0000-33-5651-00	3/4" CTS (7/8" OD) X 1/2" CTS (5/8" OD)
0000-33-5609-00	3/4" CTS (7/8" OD) X 1/2" IPS
0000-33-5480-00	1" CTS (1 1/8" OD) X 1/2" CTS (5/8" OD)
0000-33-5963-00	1" CTS (1 1/8" OD) X 1/2" IPS
0000-33-5763-00	1" CTS (1 1/8" OD) X 3/4" CTS (7/8" OD)
0000-33-5589-00	1" CTS (1 1/8" OD) X 3/4" IPS
0000-33-5514-00	1" IPS X 1/2" CTS (5/8" OD)
0000-33-5516-00	1" IPS X 3/4" IPS
0000-33-5606-00	1" IPS X 1" CTS (1 1/8" OD)
0000-33-5515-00	1 1/4" CTS (1 3/8" OD) X 1/2" CTS (5/8" OD)
0000-33-5798-00	1 1/4" CTS (1 3/8" OD) X 3/4" IPS
0000-33-5631-00	1 1/4" CTS (1 3/8" OD) X 1" CTS (1 1/8" OD)
0000-33-6572-00	1 1/4" CTS (1 3/8" OD) X 1" IPS


PART NUMBER	DESCRIPTION
0000-33-6580-04	1/2" CTS (5/8" OD) .090 WALL
0000-33-6580-06	3/4" CTS (7/8" OD) .090 WALL
0000-33-6580-02	1" CTS (1 1/8" OD) .090 WALL
0000-33-6580-08	1" CTS (1 1/8" OD) .099/.101 WALL
0000-33-6580-12	1/2" IPS SDR-9.3
0000-33-6580-13	3/4" IPS SDR-11
0000-33-6580-14	1" IPS SDR-11
0000-33-6580-03	1 1/4" CTS (1 3/8" OD) .090 WALL
0000-33-6580-10	1 1/4" IPS SDR-11 (.151 WALL)
0000-33-6580-15	1 1/4" IPS SDR-10 (.166 WALL)
0000-33-6580-09	1 1/4" IPS SDR-9.3 (.178 WALL)
0000-33-6580-16	1 1/2" IPS SDR-11
0000-33-6580-17	2" IPS SDR-11

PART NUMBER	DESCRIPTION
0000-33-5505-00	Combination Tapping Tool & Saddle Bolt "T" Wrench for 1 1/4" thru 6" IPS Con-Stab ID Seal Eliminators & Saddle Bolt "T" Wrench for 1 1/4" thru 6" IPS Con-Stab ID Seal Eliminators
0000-33-5505-01	Combination Tapping Tool & Saddle Bolt "T" Wrench for 3" thru 8" IPS Con-Stab ID Seal Eliminators




Combination Tapping Tool & Saddle Bolt "T" Wrench

PART NUMBER	DESCRIPTION
0000-33-4363-00	1/2" Square Drive Key, Bushing & Socket Adapter Ass'y for HVT Eliminator Saddles



1/2" Square Drive Key, Bushing & Socket Adapter Ass'y for HVT Eliminator Saddles

PART NUMBER	DESCRIPTION
0000-33-5508-00	Test Plug Cap for Eliminator Saddles with 1/4" FPT for attachment of quick connect coupling
0000-33-6290-00	Test Plug Cap for HVT Saddles with 1/4" FPT for attachment of quick connect coupling



Test Plug Cap for Eliminator Saddles



Lycofit® Mechanical Couplings

PE SIZE	WALL	MINIMUM QTY.	PART NUMBER
1/2" CTS	DR7	3	LC010B-DER
3/4" IPS	DR11	3	LC060Y-DER
1" IPS	DR11	3	LC070Y-DER
1 1/4" IPS	DR10/11	3	LC080X-DESR
1 1/2" IPS	DR11	2	LC090Y-DESR
2" IPS	DR11	2	LC200Y-DESR



Lycofit® Mechanical End Caps

PE SIZE	WALL	MINIMUM QTY.	PART NUMBER
3/4" IPS	DR11	3	LC060Y-ECDF
1" IPS	DR11	3	LC070Y-ECDF
1 1/4" IPS	DR10/11	3	LC080X-ECDF
1 1/2" IPS	DR11	3	LC090Y-ECDF
2" IPS	DR11	3	LC200Y-ECDF



Lycofit® Mechanical 3-Way Tees

PE SIZE	WALL	MINIMUM QTY.	PART NUMBER
1/2" CTS	DR7	3	LC010B-M3T
3/4" IPS	DR11	3	LC060Y-M3T
1 IPS	DR11	3	LC070Y-M3T
1 1/4" IPS	DR10/11	3	LC080X-M3T
1 1/2" IPS	DR11	2	LC090Y-M3T
2" IPS	DR11	2	LC200Y-M3T



Lycofit® Mechanical 90° Elbows

PE PIPE SIZE	WALL THICKNESS	MIN. QTY	PRODUCT CODE
1/2 CTS	DR7	3	LC010B-MEL
3/4 IPS	DR11	3	LC060Y-MEL
1 IPS	DR11	3	LC070Y-MEL
1 1/4 IPS	DR10/11	3	LC080X-MEL
1 1/2 IPS	DR11	2	LC090Y-MEL
2 IPS	DR11	2	LC200Y-MEL

COUPLING SIZE	WALL THICKNESS	MIN. QTY	PRODUCT CODE
1 X ¾ IPS	DR11	3	LC070Y060Y-RR
1 ¼ X ¾ IPS	DR10/11	3	LC080X060Y-RR
1 ¼ X 1 IPS	DR10/11	3	LC080X070Y-RR
1 ½ X 1 ¼ IPS	DR11	3	LC090Y080X-RR
1 ½ X ¾ IPS	DR11	3	LC090Y060Y-RR
1 ½ X 1 IPS	DR11	3	LC090Y070Y-RR
2 X ¾ IPS	DR11	3	LC200Y060Y-RR
2 X 1 IPS	DR11	3	LC200Y070Y-RR
2 X 1 ¼ IPS	DR11	3	LC200Y080X-RR
2 X 1 ½ IPS	DR11	3	LC200Y090Y-RR

Note: Listed above are standard sizes available from Lyall. We can manufacture couplings in almost any configuration. If you don't see what you need listed, please contact Lyall customer service or your authorized sales representative for technical support and pricing information.

STEEL PIPE SIZE	PE PIPE SIZE	MIN. QTY	PRODUCT CODE
½ NPT SCH40	1/2 CTS .090/DR7	3	LC050S010B-SPB
¾ NPT SCH40	3/4 IPS DR11	3	LC060S060Y-SPB
1 NPT SCH40	1 IPS DR11	3	LC070S070Y-SPB
1 ¼ NPT SCH40	1-1/4 IPS DR10/11	3	LC080S080X-SPB
1 ½ NPT SCH40	1-1/2 IPS DR11	3	LC090S090Y-SPB
2 NPT SCH40	2 IPS DR11	3	LC200S200Y-SPB

PE SIZE	WALL	COPPER SIZE	PART NUMBER (3408/4710)
1/2" CTS	.090	3/8" OD GGS	LC375010B-GCR
		1/2" OD	LC500010B-GCR




Lycofit® Mechanical Reducer Couplings



Steel To PE Transition Fittings




Lycofit® P.E. x Copper Tubing Adapter (Grill Adapter)



QRP-100

Lycofit® Quick Ratchet Press
(QRP) Assembly Tools



QRP-200

TOOL	FITTING SIZES	MIN. QTY	PRODUCT CODE
QRP-100	½ CTS through 1 IPS	1	QRP-100
QRP-200	½ CTS through 2 IPS	1	QRP-200

Note: The QRP-100 tool requires one (1) long handled, ½” drive ratchet wrench to operate.
The QRP-200 tool requires two (2) long handled, ½” drive ratchet wrenches to operate.

Lycofit® LYCOFIT ASSEMBLY TOOL INSTALLA-
TION CHART

TOOL MODEL	1/2 CTS	3/4 CTS	1 CTS	1-1/4 CTS	1/2 IPS	3/4 IPS	1 IPS	1-1/4 IPS	1-1/2 IPS	2 IPS
QRP-100	YES	YES	YES		YES	YES	YES			
QRP-200	YES*	YES*	YES*	YES*	YES*	YES*	YES*	YES*	YES*	YES*
LHP-200								YES	YES	YES

* Installs the coupling/fitting size indicated when using the appropriate adapter plates.

PE SIZE	WALL	PART NUMBER
1/2" CTS (5/8" OD)	.090	5657-52-1004-00
	.062	5657-52-1004-AA
1" CTS (1 1/8" OD)	.099/.101	5657-52-1008-00
	.090	5657-52-1008-AA
3/4" IPS	SDR-11 (.095)	5657-52-1013-00
1" IPS	SDR-11 (.119)	5657-52-1014-00
1 1/4" IPS	SDR-10 (.166)	5657-52-1015-00
	SDR-11 (.151)	5657-52-1015-AA
2" IPS	SDR-11 (.216)	5657-52-1017-00

• For sizes not listed, contact Continental Industries.



PA Compression Full Couplings

PE SIZE	WALL	PART NUMBER
1/2" CTS (5/8" OD)	.090	5657-53-1004-00
	.062	5657-53-1004-OA
1" CTS (1 1/8" OD)	.099/.101	5657-53-1008-00
	.090	5657-53-1008-OA
3/4" IPS	SDR-11 (.095)	5657-53-1013-00
1" IPS	SDR-11 (.119)	5657-53-1014-00
1 1/4" IPS	SDR-10 (.166)	5657-53-1015-00
	SDR-11 (.151)	5657-53-1015-OA
2" IPS	SDR-11 (.216)	5657-53-1017-00

• For sizes not listed, contact Continental Industries.



PA Compression End Caps

PE SIZE	WALL	PART NUMBER
1/2" CTS (5/8" OD)	.090	5657-50-1004-00
	.062	5657-50-1004-AA
1" CTS (1 1/8" OD)	.099/.101	5657-50-1008-00
	.090	5657-50-1008-AA
3/4" IPS	SDR-11 (.095)	5657-50-1013-00

• For sizes not listed, contact Continental Industries.



PA Compression 3-Way Tees



PA Compression 90° Elbows

PE SIZE	WALL	PART NUMBER
1/2" CTS (5/8" OD)	.090	5657-51-1004-00
	.062	5657-51-1004-AA
1" CTS (1 1/8" OD)	.099/.101	5657-51-1008-00
	.090	5657-51-1008-AA
3/4" IPS	SDR-11 (.095)	5657-51-1013-00

• For sizes not listed, contact Continental Industries.



PA Compression Reducer Couplings

PE SIZE	WALL	PE SIZE	WALL	PART NUMBER
1/2" CTS (5/8" OD)	.090	1/2" CTS (5/8" OD)	.062	5657-54-0404-0A
	.062	1/4" CTS (3/8" OD)	.062	5657-54-0402-00 5657-54-0402-A0
1" CTS (1 1/8" OD)	.099/.101	3/4" IPS	SDR-11 (.095)	5657-54-0813-00
	.090			5657-54-0813-A0
	.099/.101	1/2" CTS (5/8" OD)	.062	5657-54-0804-0A 5657-54-0804-AA
	.090			5657-54-0804-00 5657-54-0804-A0
	.099/.101		.090	5657-54-1304-00 5657-54-1304-0A
	.090			5657-54-1408-00 5657-54-1408-0A
3/4" IPS	SDR-11 (.095)	1/2" CTS (5/8" OD)	.090	5657-54-1413-00
1" IPS	SDR-11 (.119)	1" CTS (1 1/8" OD)	.099/.101	5657-54-1404-00
			.090	5657-54-1404-0A
		3/4" IPS	SDR-11 (.095)	5657-54-1404-00 5657-54-1404-0A
		1/2" CTS	.090	5657-54-1015-0A
1 1/4" IPS	SDR-10 (.166)	1 1/4" IPS	SDR-11 (.151)	

• For sizes not listed, contact Continental Industries.

OUTLET (PE SIZE)	WALL	MAIN SIZE	PART NUMBER 5864 1/2" CR PUNCH	PART NUMBER 5764 13/16" CR PUNCH
1/2" CTS (5/8" OD)	.090	1 1/4"	5864-15-1604-00	N/A
		1 1/2"	5864-16-1604-00	N/A
		2"	5864-17-1604-00	5764-17-1604-00 [†]
		3"	5864-19-1604-00	5764-19-1604-00 [†]
		4"	5864-21-1604-00	5764-21-1604-00 [†]
		6"	5864-24-1604-00	5764-24-1604-00 [†]
		8"	N/A	5764-26-1604-00
1" CTS (1 1/8" OD)	.099/.101	1 1/4"	5864-15-1608-00	N/A
		2"	5864-17-1608-00	5764-17-1608-00
		3"	5864-19-1608-00	5764-19-1608-00
		4"	5864-21-1608-00	5764-21-1608-00
		6"	5864-24-1608-00	5764-24-1608-00
		8"	N/A	5764-26-1608-00
	.090	1 1/4"	5864-15-1608-0A	N/A
		2"	5864-17-1608-0A	5764-17-1608-0A
		3"	5864-19-1608-0A	5764-19-1608-0A
		4"	5864-21-1608-0A	5764-21-1608-0A
		6"	5864-24-1608-0A	5764-24-1608-0A
		8"	N/A	5764-26-1608-0A
1/2" IPS	SDR-9.33 (.090)	1 1/4"	5864-15-1612-00	N/A
		2"	5864-17-1612-00	5764-17-1612-00
		3"	5864-19-1612-00	5764-19-1612-00
		4"	5864-21-1612-00	5764-21-1612-00
		6"	5864-24-1612-00	5764-24-1612-00
		8"	N/A	5764-26-1612-00
3/4" IPS	SDR-11 (.095)	1 1/4"	5864-15-1613-00	N/A
		1 1/2"	5864-16-1613-00	5764-16-1613-00
		2"	5864-17-1613-00	5764-17-1613-00 [†]
		3"	5864-19-1613-00	5764-19-1613-00 [†]
		4"	5864-21-1613-00	5764-21-1613-00 [†]
		6"	5864-24-1613-00	5764-24-1613-00 [†]
		8"	N/A	5764-26-1613-00
1" IPS	SDR-11 (.119)	1 1/4"	5864-15-1614-00	N/A
		1 1/2"	5864-16-1614-00	5764-16-1614-00
		2"	5864-17-1614-00	5764-17-1614-00 [†]
		3"	5864-19-1614-00	5764-19-1614-00 [†]
		4"	5864-21-1614-00	5764-21-1614-00 [†]
		6"	5864-24-1614-00	5764-24-1614-00 [†]
		8"	N/A	5764-26-1614-00



Con-Stab ID Seal®
Eliminators



Con-Stab ID Seal®
HVT Eliminators

OUTLET (PE SIZE)	WALL	MAIN SIZE	PART NUMBER
1 1/4" IPS	SDR-10 (.166)	2"	5664-17-1615-00
		3"	5664-19-1615-00
		4"	5664-21-1615-00
		6"	5664-24-1615-00
	SDR-11 (.151)	2"	5664-17-1615-0A
		3"	5664-19-1615-0A
		4"	5664-21-1615-0A
		6"	5664-24-1615-0A
2" IPS	SDR-11 (.216)	2"	5664-17-1617-00
		3"	5664-19-1617-00
		4"	5664-21-1617-00
		6"	5664-24-1617-00

• For sizes not listed, contact Continental Industries.



PA HVT W/ Compression Outlets

OUTLET (PE SIZE)	WALL	MAIN SIZE	PART NUMBER 1 1/2" CR PUNCH
1 1/4" IPS	SDR-10 (.166)	2"	5664-17-1015-00
		3"	5664-19-1015-00
		4"	5664-21-1015-00
		6"	5664-24-1015-00
	SDR-11 (.151)	2"	5664-17-1015-0A
		3"	5664-19-1015-0A
		4"	5664-21-1015-0A
		6"	5664-24-1015-0A
2" IPS	SDR-11 (.216)	2"	5664-17-1017-00
		3"	5664-19-1017-00
		4"	5664-21-1017-00
		6"	5664-24-1017-00

OUTLET (PE SIZE)	WALL	MAIN SIZE	PART NUMBER 5864 1/2" CR PUNCH	PART NUMBER 5764 13/16" CR PUNCH
1/2" CTS (5/8" OD)	.090	1 1/4"	5864-15-1004-00	N/A
		1 1/2"	5864-16-1004-00	N/A
		2"	5864-17-1004-00	5764-17-1004-00
		3"	5864-19-1004-00	5764-19-1004-00
		4"	5864-21-1004-00	5764-21-1004-00
		6"	5864-24-1004-00	5764-24-1004-00
		8"	N/A	5764-26-1004-00
	.062	1 1/4"	5864-15-1004-0A	N/A
		2"	5864-17-1004-0A	5764-17-1004-0A
		3"	5864-19-1004-0A	5764-19-1004-0A
		4"	5864-21-1004-0A	5764-21-1004-0A
		6"	5864-24-1004-0A	5764-24-1004-0A
		8"	N/A	5764-26-1004-0A
1" CTS (1 1/8" OD)	.099/.101	1 1/4"	5864-15-1008-00	N/A
		2"	5864-17-1008-00	5764-17-1008-00
		3"	5864-19-1008-00	5764-19-1008-00
		4"	5864-21-1008-00	5764-21-1008-00
		6"	5864-24-1008-00	5764-24-1008-00
		8"	N/A	5764-26-1008-00
	.090	1 1/4"	5864-15-1008-0A	N/A
		2"	5864-17-1008-0A	5764-17-1008-0A
		3"	5864-19-1008-0A	5764-19-1008-0A
		4"	5864-21-1008-0A	5764-21-1008-0A
		6"	5864-24-1008-0A	5764-24-1008-0A
		8"	N/A	5764-26-1008-0A
3/4" IPS	SDR-11 (.095)	1 1/4"	5864-15-1013-00	N/A
		1 1/2"	5864-16-1013-00	5764-16-1013-00
		2"	5864-17-1013-00	5764-17-1013-00
		3"	5864-19-1013-00	5764-19-1013-00
		4"	5864-21-1013-00	5764-21-1013-00
		6"	5864-24-1013-00	5764-24-1013-00
		8"	N/A	5764-26-1013-00
1" IPS	SDR-11 (.119)	1 1/4"	5864-15-1014-00	N/A
		1 1/2"	5864-16-1014-00	5764-16-1014-00
		2"	5864-17-1014-00	5764-17-1014-00
		3"	5864-19-1014-00	5764-19-1014-00
		4"	5864-21-1014-00	5764-21-1014-00
		6"	5864-24-1014-00	5764-24-1014-00
		8"	N/A	5764-26-1014-00



PA Eliminators W/
Compression Outlets

• For sizes not listed, contact Continental Industries.




Combination Tapping Tool & Saddle Bolt "T" Wrench

PART NUMBER	DESCRIPTION
0000-33-5505-00	Combination Tapping Tool & Saddle Bolt "T" Wrench for 1 1/4" thru 6" IPS Con-Stab ID Seal Eliminators page 9
0000-33-5505-01	Combination Tapping Tool & Saddle Bolt "T" Wrench for 3" thru 8" IPS Con-Stab ID Seal Eliminators page 9




1/2" Square Drive Key, Bushing & Socket Adapter Ass'y for HVT Eliminator Saddles

PART NUMBER	DESCRIPTION
0000-33-4363-00	1/2" Square Drive Key, Bushing and Socket Adapter page 9



Test Plug Cap for Eliminator Saddles

PART NUMBER	DESCRIPTION
0000-33-5508-00	Test Plug Cap for Eliminator Saddles page 9



Steel To PE Threaded
Transition Fitting



SIZE STEEL X PE	PE TYPE	STEEL LENGTH "A"	PE LENGTH "B"	MIN. ORDER QTY	THD TRAN PRODUCT CODE	NOTES
3/4 NPT X 3/4 IPS DR11	PE2406/PE2708	5"	12"	6	101051050800	†‡
1 NPT X 1 IPS DR11	PE2406/PE2708	5"	12"	3	101321320800	†‡
1 1/4 NPT X 1 1/4 IPS DR10	PE2406/PE2708	5 1/2"	12"	2	101661660700	†‡
1 1/2 NPT X 1 1/2 IPS DR11	PE2406/PE2708	5 1/2"	12"	2	101901900800	†
2 NPT X 2 IPS DR11	PE2406/PE2708	5 3/4"	12"	2	102382380800	†‡

† = CSA Approved / ‡ = IAPMO/UPC Listed

Recommended accessories: socket fusion couplings, wire lugs, protector sleeves

Notes:

- A Fusion Bonded Epoxy (FBE) coating is applied to the external surface on all sizes
- In addition to threaded transition fittings, Lyall offers several other types of transition connections. Please contact us for pricing and technical information on the following configurations:



Beveled for Welding



Victaulic Groove




Flanged



Con-Stab ID Seal® Steel
Transition Fittings

OUTLET (PE SIZE)	WALL	INLET	PART NUMBER 2406 MDPE	PART NUMBER 3408/4710 HDPE
1/2" CTS (5/8" OD)	.090	1/2" MPT	4646-00-1904-25	4949-00-1904-25
1" CTS (1 1/8" OD)	.099/.101	1" MPT	4646-00-1908-25	4949-00-1908-25
1/2" IPS	SDR-9.33 (.090)	3/4" MPT	4646-00-1912-25	4949-00-1912-25
3/4" IPS	SDR-11 (.095)	3/4" MPT	4646-00-1913-25	4949-00-1913-25
1" IPS	SDR-11 (.119)	1" MPT	4646-00-1914-25	4949-00-1914-25
1 1/4" IPS	SDR-10 (.166)	1 1/4" MPT	4646-00-1915-25	4949-00-1915-25
1 1/4" IPS	SDR-11 (.151)	1 1/4" MPT	9946-00-0058-25	9949-00-0001-25
1 1/2" IPS	SDR-11 (.171)	1 1/2" MPT	4646-00-1916-25	4949-00-1916-25
2" IPS	SDR-11 (.166)	2" MPT	4646-00-1917-25	4949-00-1917-25


- For sizes not listed, contact Continental Industries.



Transition Fittings

OUTLET (PE SIZE)	WALL	INLET	PART NUMBER 2406 MDPE	PART NUMBER 3408/4710 HDPE
1/2" CTS (5/8" OD)	.090	1/2" MPT	4646-00-1904-00	4949-00-1904-00
1" CTS (1 1/8" OD)	.099/.101	1" MPT	4646-00-1908-00	4949-00-1908-00
1/2" IPS	SDR-9.33 (.090)	3/4" MPT	4646-00-1912-00	4949-00-1912-00
3/4" IPS	SDR-11 (.095)	3/4" MPT	4646-00-1913-00	4949-00-1913-00
1" IPS	SDR-11 (.119)	1" MPT	4646-00-1914-00	4949-00-1914-00
1 1/4" IPS	SDR-10 (.166)	1 1/4" MPT	4646-00-1915-00	4949-00-1915-00
1 1/4" IPS	SDR-11 (.151)	1 1/4" MPT	4646-00-1915-0A	4949-00-1915-0A
1 1/2" IPS	SDR-11 (.171)	1 1/2" MPT	4646-00-1916-00	4949-00-1916-00
2" IPS	SDR-11 (.166)	2" MPT	4646-00-1917-00	4949-00-1917-00


- For sizes not listed, contact Continental Industries.



Con-Stab ID Seal® Brass
Transition Fittings

OUTLET (PE SIZE)	WALL	INLET	PART NUMBER (3408/4710)
1/2" CTS (5/8" OD)	.090	1/2" MPT	9932-00-0002-00
		1/2" FPT	9932-00-0019-00
1" CTS (1 1/8" OD)	.099/.101	3/4" MPT	9932-00-0008-00
		3/4" FPT	9932-00-0025-00
	.090	3/4" MPT	9932-00-0007-00
		3/4" FPT	9932-00-0024-00
3/4" IPS	SDR-11 (.095)	3/4" MPT	9932-00-0015-00
		3/4" FPT	9932-00-0032-00


• For sizes not listed, contact Continental Industries.



Con-Stab ID Seal® Steel
Transition Fittings

OUTLET (PE SIZE)	WALL	INLET	PART NUMBER (3408/4710) HDPE
1/2" CTS (5/8" OD)	.090	1/2" MPT	0432-00-0912-00
		1/2" FPT	0432-00-1512-00
		3/4" MPT	0432-00-0913-00
		3/4" FPT	0432-00-1513-00
		3/4" BUTT WELD	0432-00-0613-00
1" CTS 1 1/8" OD)	.099/.101	3/4" MPT	0832-00-0913-00
		3/4" FPT	0832-00-1513-00
		1" MPT	0832-00-0914-00
		1" FPT	0832-00-1514-00
		3/4" BUTT WELD	0832-00-0613-00
	.090	3/4" MPT	0832-00-0913-A0
		3/4" FPT	0832-00-1513-A0
		1" MPT	0832-00-0914-A0
		1" FPT	0832-00-1514-A0
		3/4" BUTT WELD	0832-00-0613-A0
1/2" IPS	SDR-9.33 (.090)	1/2" MPT	1232-00-0912-00
		1/2" FPT	1232-00-1512-00
		3/4" MPT	1232-00-0913-00
		3/4" FPT	1232-00-1513-00
3/4" IPS	SDR-11 (.095)	3/4" MPT	1332-00-0913-00
		3/4" FPT	1332-00-1513-00
		1" MPT	1332-00-0914-00
		1" FPT	1332-00-1514-00
		3/4" BUTT WELD	1332-00-0613-00

• For sizes not listed, contact Continental Industries.




Service Riser

SIZE STEEL X PE	PE TYPE	VERTICAL LENGTH "V"	HORIZONTAL LENGTH "H"	PE LENGTH "C"	BUNDLE/ MIN. ORDER QTY.	PART NUMBER	NOTES
¾ NPT X ½ CTS .090	PE2406/PE2708	30"	16"	10"	12	241050630130	†‡
¾ NPT X ¾ IPS DR11	PE2406/PE2708	30"	16"	10"	9	241051050830	†‡
1 NPT X 1 IPS DR11	PE2406/PE2708	30"	16"	10"	6	241321320830	†‡
1 ¼ NPT X 1 ¼ IPS DR10	PE2406/PE2708	30"	22"	10"	4	241661660760	†‡
1 ½ NPT X 1 ½ IPS DR11	PE2406/PE2708	30"	32"	10"	4	241901900830	†
2 NPT X 2 IPS DR11	PE2406/PE2708	30"	30"	10"	2	242382380840	†‡

• For sizes or PE Type not listed, please contact Lyall Customer Service.

† = CSA Approved / ‡ = IAPMO/UPC Listed


RISERS MUST BE ORDERED IN MULTIPLES OF BUNDLE QUANTITY LISTED



Meter Riser

SIZE (MPT X PE)	WALL	VERTICAL LENGTH	HORIZONTAL LENGTH	PART NUMBER	PART NUMBER with Con-Stab
1/2"MPT X 1/2"CTS (5/8" OD) PE	0.090	30"	15"	1253-91-4604-00	1253-91-4604-25
3/4"MPT X 1/2"CTS (5/8" OD) PE	0.090	18"	19"	9953-99-0520-00	9953-99-0521-00
3/4"MPT X 1/2"CTS (5/8" OD) PE	0.090	30"	17"	1353-91-4604-00	1353-91-4604-25
3/4"MPT X 1/2"IPS PE	SDR-9.3 (.090)	30"	17"	1353-91-4612-00	1353-91-4612-25
3/4"MPT X 3/4" IPS PE	SDR-11 (.095)	30"	16"	1353-91-4613-00	1353-91-4613-25
3/4"MPT X 1" CTS (1 1/8"OD) PE	099/.101	30"	16"	1353-91-4608-00	1353-91-4608-25
1" MPT X 1" IPS PE	SDR-11 (.119)	30"	16"	1453-91-4614-00	1453-91-4614-25
1 1/4"MPT X 1 1/4"IPS PE	SDR-10 (.166)	30"	22"	1553-91-4615-00	1553-91-4615-25
1 1/4" MPT X 1 1/4" IPS PE	SDR-11 (.151)	30"	22"	1553-91-4615-0A	9953-99-0503-25
1 1/2"MPT X 1 1/2"IPS PE	SDR-11 (.173)	36"	26"	1652-91-4616-00	1652-91-4616-25
2"MPT X 2" IPS PE	SDR-11 (.216)	36"	30"	1752-91-4617-00	1752-91-4617-25

• For sizes not listed, contact Continental Industries.



Service Head Adaptor Riser

THREADED END	SPIGOT END SIZE (PE PIPE)	LENGTH	BOX/MIN. ORDER QTY.	PART NUMBER	NOTES
½ NPT	½ CTS .090/DR7	36"	10	SHAF050010B-36	‡
½ NPT	½ CTS .090/DR7	48"	10	SHAF050010B-48	‡
½ NPT	½ CTS .090/DR7	84"	10	SHAF050010B-84	‡
½ NPT	½ IPS DR9.3	36"	10	SHAF050050W-36	‡
½ NPT	½ IPS DR9.3	48"	10	SHAF050050W-48	‡
½ NPT	½ IPS DR9.3	84"	10	SHAF050050W-84	‡
¾ NPT	½ CTS .090/DR7	36"	10	SHAF060010B-36	‡‡
¾ NPT	½ CTS .090/DR7	48"	10	SHAF060010B-48	‡‡
¾ NPT	½ CTS .090/DR7	84"	10	SHAF060010B-84	‡‡
¾ NPT	¾ IPS DR11	36"	10	SHAF060060Y-36	‡
¾ NPT	¾ IPS DR11	48"	10	SHAF060060Y-48	‡
¾ NPT	¾ IPS DR11	84"	10	SHAF060060Y-84	‡


RISERS MUST BE ORDERED IN MULTIPLES OF BUNDLE OR BOX QUANTITY LISTED



Conflex Risers

SIZE (MPT X PE)	WALL	LENGTH	PART NUMBER
1/2" MPT X 1/2" CTS (5/8" OD) PE	.090	36"	1253-92-1004-36
		48"	1253-92-1004-48
		60"	1253-92-1004-60
		72"	1253-92-1004-72
		84"	1253-92-1004-84
		96"	1253-92-1004-96
3/4" MPT X 1/2" CTS (5/8" OD) PE	.090	36"	1353-92-1004-36
		48"	1353-92-1004-48
		60"	1353-92-1004-60
		72"	1353-92-1004-72
		84"	1353-92-1004-84
		96"	1353-92-1004-96
3/4" MPT X 3/4" IPS PE	SDR-11 (.095)	36"	1353-92-1013-36
		48"	1353-92-1013-48
		60"	1353-92-1013-60
		72"	1353-92-1013-72
		84"	1353-92-1013-84
		96"	1353-92-1013-96
1" MPT X 1" CTS (1 1/8" OD) PE	.099/.101	36"	1453-92-1008-36
		60"	1453-92-1008-60
		72"	1453-92-1008-72
		84"	1453-92-1008-84
		96"	1453-92-1008-96
1" MPT X 1" IPS PE	SDR-11 (.119)	36"	1453-92-1014-36
		60"	1453-92-1014-60
1 1/4" MPT X 1 1/4" IPS PE	SDR-10 (.116)	36"	1553-96-1015-36
	SDR-11 (.151)	36"	9953-99-0445-00
1 1/2" MPT X 1 1/2" IPS PE	SDR-11 (.173)	36"	1653-96-1016-36
2" MPT X 2" IPS PE	SDR-11 (.216)	36"	1753-96-1017-36

• For sizes not listed, contact Continental Industries.



Transition (Anode) Risers

SIZE STEEL X PE	PE TYPE	VERTICAL LENGTH "A"	HORIZONTAL LENGTH "B"	PE LENGTH "C"	BUNDLE/ MIN. ORDER QTY.	PART NUMBER	NOTES
¾ NPT X ¾ IPS DR11	PE2406/PE2708	30"	30"	6"	9	201051050830	‡
1 NPT X 1 IPS DR11	PE2406/PE2708	30"	30"	6"	6	201321320830	‡
1 ¼ NPT X 1 ¼ IPS DR10	PE2406/PE2708	30"	30"	6"	4	201661660730	‡
1 ½ NPT X 1 ½ IPS DR11	PE2406/PE2708	30"	30"	6"	4	201901900830	‡
2 NPT X 2 IPS DR11	PE2406/PE2708	30"	30"	6"	2	202382380830	‡

‡ = IAPMO/UPC Listed

Recommended accessories: riser brackets, stakes, anodes


RISERS MUST BE ORDERED IN MULTIPLES OF BUNDLE OR BOX QUANTITY LISTED



Riser Wall Bracket





Offset Adjustable Riser Wall Bracket



Adjustable Riser Wall Bracket



Riser Support Stake

**Bracket & Support Stakes**

PRODUCT DESCRIPTION	PRODUCT SUPPORT	BUNDLE/MIN. ORDER QTY.	PART NUMBER
Wall Bracket - 9"	Riser	10	BRK9H
Offset Adjustable Wall Bracket - 14"	Riser	10	BRK38-01
Support Stake - 48"	Riser	20	BRK32



Ball Valves - High Density PE 3408/4710

PE PIPE SIZE	WALL THICKNESS	PORT	BOX QTY.	PRODUCT CODE
1/2	.090	Full	5	BV0010B-MFNO-000
1 CTS	.099-.102	Full	5	BV0030D-MFNO-000
3/4 IPS	DR11	Full	5	BV0060Y-MFNO-000
				BV00700-MFNO-000
1 IPS	DR11	Full	5	BV0070Y-MFNO-000
1 1/4	DR11	Standard	5	BV0080Y-MSNO-000
1 1/2	DR11	Standard	5	BV0090Y-MSNO-000
2 IPS	DR11	Standard	1	BV0200Y-MSNO-000
2 IPS	DR11	Full	1	BV0200Y-MFNO-000
3 IPS	DR11	Full	1	BV0300Y-MFNO-000
4 IPS	DR11	Standard	1	BV0400Y-MSNO-000
4 IPS	DR11	Full	1	BV0400Y-MFNO-000
6 IPS	DR11	Standard	1	BV0600Y-MSNO-000
6 IPS	DR11	Full	1	BV0600Y-MFNO-000
8 IPS	DR11	Full	1	BV0800Y-MFNO-000
10 IPS	DR11	Full	1	BV1000Y-MFNO-000
12 IPS	DR11	Standard	1	BV1200Y-MSNO-000
12 IPS	DR11	Full	1	BV1200Y-MFNO-000
14 IPS	DR11	Full	1	BV1400Y-MFNO-000
16 IPS	DR11	Full	1	BV1600Y-MFNO-000

BALL VALVES MUST BE ORDERED IN MULTIPLES OF BUNDLE OR BOX QUANTITY LISTED

The products listed on the previous pages represent the most commonly used sizes and configurations. Additional sizes, custom configurations and options for these products are available as Special Orders. In addition, the following products and services are also available as Special Orders. Contact your Lyall sales representative or customer service for pricing, minimum order quantities and lead times for these products.

Lycofit® Reducer Tess



Insulated Unions



COPO Copper To PE Fittings



Field Assembled Service Risers



Factory Assembled Riser Options



Anodeless Riser with factory assembled valve, LYCOFIT coupling and support stake options.

Please visit the following webpage for the HGUS Terms and Conditions:
<https://www.hubbell.com/continentalindustries/en/terms-and-conditions>

Product Notes




Product Notes

Product Notes





Broken Arrow, OK



Corona, CA

Superior Quality **Superior** Service **Superior** Selection

For Assistance Contact HGUS Headquarters
Phone: 1-800-558-1373 • 6100 S Yale Ave, STE 1110, Tulsa, OK 74136
hubbell.com

