

Euclid™ Pendants and Pushbuttons

2015/16/17

Price List 2015/16/17 • January 2021, Replaces August 2018

Type PBC Enclosure Discount Code EA

NEMA Type 1 Enclosure

Length	Without Space For Toggle Switch			With Space For Toggle Switch		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
4 Buttons	C2	28578-002	\$1,644	CT2	65012-002	\$1,664
6 Buttons	C3	28578-003	\$1,812	CT3	65012-003	\$1,884
8 Buttons	C4	28578-004	\$1,982	CT4	65012-004	\$2,124
10 Buttons	C5	28578-005	\$2,520	CT5	65012-005	\$2,690
12 Buttons	C6	28578-006	\$3,186	CT6	65012-006	\$3,356

Ordering Instructions

Total price of an assembled pushbutton station is obtained by adding the enclosure price and pushbutton insert prices plus pricing for any special nameplate markings require. Standard nameplate markings are included in enclosed price.

Example Catalog No. PBC-P1R135T

Qty.	Cat. No.	Description	List Price
1	CT4	8 Button 7 Toggle Enclosure	\$2,124
1	P1	110 VAC Pilot Light Marked: Power On	\$814
1	R	Reset Button Marked: Reset	\$326
1	A1	Single Speed Mrkd: Fwd-Bridge-Rev	\$510
1	A3	Three Speed Mrkd: Fwd-Trolley-Rev	\$716
1	A5	Five Speed Mrkd: Up-Hoist-Down	\$970
1	T	Toggle Switch Marked: Off-On	\$1,162

Total List Price \$6,622
Refer to your local sales office for special inserts or features.

Type WPBC Enclosure Discount Code EA

NEMA Type 3R¹/13 Enclosure

Length	Type WPBC Pendant Mounted			Type SWPBC Surface Mounted		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
2 Buttons	WC1	28581-001	\$1,460	SWC1	28581-301	\$2,308
4 Buttons	WC2	28581-002	\$1,798	SWC2	28581-302	\$2,804
6 Buttons	WC3	28581-003	\$2,266	SWC3	28581-303	\$3,356
8 Buttons	WC4	28581-004	\$2,776	SWC4	28581-304	\$4,050
10 Buttons	WC5	28581-005	\$3,328	SWC5	28581-305	\$4,828
12 Buttons	WC6	28581-006	\$4,008	SWC6	28581-306	\$5,664
14 Buttons	WC7	28581-007	\$4,702	SWC7	28581-307	\$6,626

¹ For NEMA 4 constructions add \$722 list and specify voltage for internal space heater

Type XPBC Enclosure Discount Code EF

NEMA Type 7 Class 1, Group C or D, Div. 1 or 2 enclosure for indoor applications and NEMA Type 9, Class 2, Group E, F or G, Div. 1 or 2 enclosures for indoor applications.

Length	Type XPBC Pendant Mounted			Type 2XPBC Duplex Pendant Mounted			Type SXPBC Surface Mounted		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
2 Buttons	XC1	28595-301	\$3,196	12 Buttons	2XC3	\$13,112	SXC1	28595-306	\$3,446
4 Buttons	XC2	28595-302	\$4,732	16 Buttons	2XC4	\$16,184	SXC2	28595-307	\$4,982
6 Buttons	XC3	28595-303	\$6,268	20 Buttons	2XC5	\$26,800	SXC3	28595-308	\$6,518
8 Buttons	XC4	28595-304	\$7,804				SXC4	28595-309	\$8,054
10 Buttons	XC5	28595-305	\$9,340				SXC5	28595-310	\$9,592

Standard Nameplate Marking²

Up	Raise	East	On	Open	Lift	Reset	Hoist	Main Hoist
Down	Lower	West	Off	Close	Drop	Inch	Bridge	Aux. Hoist
Fwd	Left	North	Start	Fast	In	Run	Trolley	Magnet
Rev	Right	South	Stop	Slow	Out	Jog	Crane	Power On ³

² Specify nameplate marking arrangement. Add \$47 each for special nameplate markings not listed.

³ Standard marking for pilot light only.



Price List 2015/16/17

Standard Pushbutton Inserts

Description	Type PBC Disc Code EA			Type WPBC Disc Code EA			Type XPBC Disc Code EF		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part. No.	List Price
Start - Stop	A1A	54601-145	\$510	A1A	54601-145	\$510	X1A	74601-145	\$616
Stop-Start	A1C	54601-148	\$510	A1C	54601-148	\$510	X1C	74601-148	\$616
Single Speed	A1	54601-023	\$510	A1	54601-023	\$510	X1	74601-023	\$616
Two Speed	A2	54602-002	\$716	A2	54602-002	\$716	X2	74602-002	\$822
Three Speed	A3	54603-001	\$716	A3	54603-001	\$716	X3	74603-001	\$822
Four Speed	A4	54604-001	\$970	A4	54604-001	\$970	X4	74604-001	\$1,076
Five Speed	A5	54605-001	\$970	A5	54605-001	\$970	X5	74605-001	\$1,076
120 VAC Pilot Light	P1	54698-001	\$814	P1	54698-001	\$814	XP1	74698-001	\$1,352
250 VDC Pilot Light	P5	54698-005	\$814	P5	54698-005	\$814	XP5	74698-005	\$1,352
30A 2-Pole Toggle Switch	T	28484-100	\$1,162	WT*	28436-102	\$1,516	XT*	28436-103	\$3,560
Reset Button	R	54691-150	\$326	R	54691-150	\$326	XR	74691-150	\$380
Maintained Type On-Off	M	54601-036	\$716	M	54601-036	\$716	XM	74601-036	\$822

"Off-On" toggle switch or pushbutton recommended to comply with provisions of NEMA ICS 3-422.15. Consult factory for special contact sequences. Requests must include sequence of operation and nameplate markings. *Note: WT and XT Toggles require two button spaces.

Special Pushbutton Inserts

Description	Type PBC Disc Code EA			Type WPBC Disc Code EA			Type XPBC Disc Code EF		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part. No.	List Price
Alarm Button	A1-22	54691-022	\$326	A1-22	54691-022	\$326	X1-22	74691-022	\$380
Lift/Drop - Magnet	A1-37	54601-037	\$850	A1-37	54601-037	\$850	X1-37	74601-370	\$956
2 Speed with Overlapping Contacts	A2-3	54602-003	\$716	A2-3	54602-003	\$716	X2-3	74602-003	\$822
Std. 3 Speed with LV (N/C) Circuit	A3-6	54603-006	\$970	A3-6	54603-006	\$970	A3-6	74603-006	\$1,076
Std. 3 Speed with LV (N/C) & M (N/O) Circuits	A3-12	54603-012	\$1,224	A3-12	54603-012	\$1,224	A3-12	74603-012	\$1,332
4 Speed/Dynamic Lowering - Std. 4121 Hoist	A4-90	54604-090	\$1,224	A4-90	54604-090	\$1,224	A4-90	74604-090	\$1,332
Std. 4 Speed with LV & M Circuits - Std. 4120 Travel	A4-7	54604-007	\$1,224	A4-7	54604-007	\$1,224	A4-7	74604-007	\$1,332
Std. 5 Speed with LV Circuit - Std. 4120 Travel	A5-6	54605-006	\$1,224	A5-6	54605-006	\$1,224	A5-6	74605-006	\$1,332
Std. 5 Speed with LV & M Circuits - Std. 4110 Travel	A5-13	54605-013	\$1,500	A5-13	54605-013	\$1,500	A5-13	74605-013	\$1,608
5 Speed/Dynamic Lowering - Std. 4111 Hoist	A5-380	54605-380	\$1,500	A5-380	54605-380	\$1,500	A5-380	74605-380	\$1,608

Price Additions for Modifications

Standard modifications of PBC, WPBC & XPBC Pushbutton Stations. Order by modification number and complete specifications.

Description	Type PBC Disc Code EA		Type WPBC Disc Code EA		Type XPBC Disc Code EF	
	Mod. No.	List Price	Mod. No.	List Price	Mod. No.	List Price
Mounting Two Stations Together, Side-By-Side, Including Duplex Tie Straps	M1	\$424	M9	\$424	See 2XPBC	
Additions of U-Shaped Handle to Bottom Tie Strap	M2	\$694	M10	\$694	M17	\$694
Top Interconnecting Conduit Box for Duplex Station with One Top Conduit Fitting (1-1/2"), also with Duplex Tie Strap	M3	\$4,000	M11	\$4,248	---	N/A
Addition of Vertical Side Handles to a Single or Duplex Station	M4	\$744	M12	\$744	M18	\$1,118
Addition of Complete Circular Guard to Pushbutton Operator	M5	\$744	M13	\$496	---	N/A
Addition of Standard 1-5/8" Diameter Mushroom Head to Pushbutton Operator	M6	\$148	M14	\$148	M21	\$500
Addition to "W" Wobble Stick to Bottom of Single Station	M7	\$1,472	M15	\$1,962	---	N/A
Addition of Euclid 2 or 3 Position Selector Switch to Std. Station Including Nameplate	M8	\$1,118	M16	\$1,544	M22	\$1,976
Double Potentiometer Stepless Insert*	M19D	\$7,080	M20D	\$7,080	M24D	\$7,186
Single Potentiometer Stepless Insert*	M19S	\$4,602	M20S	\$4,602	M24S	\$4,708

Note: For modifications not shown, refer to your local sales office or the factory. *Furnish complete specifications..



Hubbell Industrial Controls, Inc.
 4301 Cheyenne Drive, Archdale, NC 27263
 Phone (336) 434-2800 | Fax (336) 434-2801
www.hubbell.com/hubbellindustrialcontrols/en
sales@hubbell-icd.com