

DISCOUNT CODE EE

Enclosures

Pushbutton station enclosures range from 3-button through 11-button units, each including a molded hole plug (MHP2) and label packs for motion and direction nameplates. Enclosures are fully-gasketed, NEMA 4X, CSA and UL Listed.

Catalog No.	Part No.	NEMA 4X Enclosure	ELK1 Label Pack	ELK2 Label Pack	List Price	
					Unassembled	Assembled
ME2	HC80300-101	3 Buttons	Included	-	Consult Factory	Consult Factory
ME4	HC80300-201	5 Buttons	Included	-	Consult Factory	Consult Factory
ME6	HC80300-301	7 Buttons	Included	Included	Consult Factory	Consult Factory
ME8	HC80300-401	9 Buttons	Included	Included	Consult Factory	Consult Factory
ME10	HC80300-501	11 Buttons	Included	Included	Consult Factory	Consult Factory

Ordering Instructions

When ordering, please specify:

- **Enclosure Part Number**
- **Enclosure Accessories** - Cord connector kit, Hole Plug, Label Pack.
- **Control Inserts** - Pushbuttons (One to Five Speed), Selector Switch, Pilot Light, Push/Pull, Toggle Switch.
- **Insert Accessories** - Interlocks, Rubber Button Covers, Molded Nut/Wrench.

Notes:

1. All inserts, except three speed M3G1 and five speed M5G1, are single button assemblies. Two assemblies are required for each motion. M3G1 and M5G1 are two button mechanically interlocked assemblies.
2. When assembled stations are desired, use assembled enclosure price, specify all components and top-to-bottom arrangement including nameplate markings.
3. Consult local sales office for items not listed or for assistance in placing your order.

Enclosure Accessories

Catalog No.	Part No.	Description	List Price
MHP1	HC80313-100	Hole Plug - Yellow	\$20
MHP2	HC80313-101	Hole Plug - Black	\$20
ELK1	HC80318-001	Extra Label Pack for ME2 through ME10	\$30
ELK2	HC80318-002	Extra Label Pack for ME6 through ME10	\$30
CCK1	HC80820-750	Cord Connector Kit 3/4" NPT for Cable 0.62" to 0.87" for ME2 and ME4 enclosures	\$112
CCK2	HC80820-100	Cord Connector Kit 1" NPT for Cable 0.87" to 1.12" (22.1 - 28.4 mm) for ME6, ME8 and ME10 enclosures	\$132
NPX1	HC80830-500	Single Insert Nameplate with Special Markings	\$80
NPX2	HC80830-600	Double Insert Nameplate with Special Markings	\$100

Pilot Light Inserts

Catalog No.	Part No.	Voltage (AC/DC)	Color Lens	Type of Bulb	List Price
MPL1R	HC80324-100	120 V	Red	Neon	\$120
MPL1A	HC80324-101	120 V	Amber	Neon	\$120
MPL1G	HC80324-102	120 V	Green	Neon	\$120
MPL2R	HC80324-210	120 V	Red	Incandescent	\$160
MPL2A	HC80324-211	120 V	Amber	Incandescent	\$160
MPL2G	HC80324-212	120 V	Green	Incandescent	\$160
MPL3R	HC80324-213	250 V	Red	Incandescent	\$160
MPL3A	HC80324-214	250 V	Amber	Incandescent	\$160
MPL3G	HC80324-215	250 V	Green	Incandescent	\$160
MPL4R	HC80324-108	120 V	Red	LED	\$276
MPL4A	HC80324-109	120 V	Amber	LED	\$276
MPL4G	HC80324-110	120 V	Green	LED	\$276
MPL5R	HC80324-112	240 V	Red	LED	\$276
MPL5A	HC80324-113	240 V	Amber	LED	\$276
MPL5G	HC80324-114	240 V	Green	LED	\$276



DISCOUNT CODE EE

Control Inserts

Cat. No.	Part No.	Switch Type	Description	Operator	Contacts	Notes	List Price
M1G1B	HC80320-100	■	One Speed	Black	NO/NC		\$96
M1G1R	HC80320-101	■	One Speed	Red	NO/NC		\$96
M1G1G	HC80320-102	■	One Speed	Green	NO/NC		\$96
M0G1B	HC80320-103	■	One Speed	Black	NO		\$84
M0G1R	HC80320-104	■	One Speed	Red	NC		\$84
M0G1G	HC80320-105	■	One Speed	Green	NO		\$84
M2G1B	HC80320-110	■	Two Speed	Black	2 NO		\$96
M1G3B	HC80320-400	■	One Speed	Black	2 NO/2 NC	①	\$168
M1G3R	HC80320-401	■	One Speed	Red	2 NO/2 NC	①	\$180
M1G3G	HC80320-402	■	One Speed	Green	2 NO/2 NC	①	\$180
MSS1	HC80321-100	□	Maintained	2 Pos.	2 CKT	①	\$140
MSS3LCCR	HC80321-301	□	Maintained	3Pos.	2 CKT	⑥	\$160
MSS3LCR	HC80321-302	□	Maintained	3 Pos.	3 CKT	⑥	\$160
MSS3LR	HC80321-303	□	Maintained	3 Pos.	2 CKT	⑥	\$160
MSS3SLR	HC80321-304	□	Spring Ret.	3 Pos.	2 CKT	⑥	\$200
MSS3SR	HC80321-305	□	Spring Ret.	3 Pos.	2 CKT	⑥	\$200
MSS3SL	HC80321-306	□	Spring Ret.	3 Pos.	2 CKT	⑥	\$200
M1OT	HC80321-101	⏏	Maintained	2 Pos.	NO/NC	⑥	\$140
M1G2B	HC80322-100	⏏	One Speed	Black	NO/NC		\$140
M1G2R	HC80322-101	⏏	One Speed	Red	NO/NC	②	\$152
M1G2G	HC80322-102	⏏	One Speed	Green	NO/NC	②	\$152
MIG2E	HC80322-103	⏏	One Speed	"Stop"	NO/NC	②	\$160
M1G4B	HC80322-400	⏏	One Speed	Black	2 NO/2 NC	②	\$224
M1G4R	HC80322-401	⏏	One Speed	Red	2 NO/2 NC	①②	\$224
M1G4G	HC80322-402	⏏	One Speed	Green	2 NO/2 NC	①②	\$224
M1G4E	HC80322-403	⏏	One Speed	"Stop"	2 NO/2 NC	①②	\$232
M1GPPB	HC80323-100	⏏	Push-Pull	Black	NO/NC		\$216
M1GPPR	HC80323-101	⏏	Push-Pull	Red	NO/NC		\$204
M1GPPG	HC80323-102	⏏	Push-Pull	Green	NO/NC		\$216
M1GMB	HC80323-103	■	Maintained	Black	NO/NC	③	\$192
M1GMR	HC80323-104	■	Maintained	Red	NO/NC	③	\$192
MIGMG	HC80323-105	■	Maintained	Green	NO/NC	③	\$192
M3G1	HC80825-100	■ ■	Three Speed	2 Black	---	⑥⑦	\$430
M5G1	HC80825-000	■ ■	Five Speed	2 Black	---	④⑥	\$530

Type of Switch Symbol Key

- --- Pushbutton Switch
- --- Selector Switch
- ⏏ --- Toggle Switch
- ⏏ --- Mushroom Head Switch

Notes:

- ① Cannot be mechanically interlocked.
- ② All Mushroom head inserts require Part No. HC80325-104 molded clamping wrench for installation.
- ③ (2) ea - M1Gm inserts and (1) ea - MRI interlock required for maintained operation. Maintained and momentary buttons can be combined with MRI interlock.
- ④ This is a two button insert with a mechanical interlock and (6) ea - N.O. sequential contacts per button. It is CSA approved only.
- ⑤ Add-A-Block adds extra contacts to standard single deck buttons. However, they cannot be used with mechanical interlocks in pendants due to lack of space.
- ⑥ See specification booklet for contact sequence.
- ⑦ This is a two button insert with a mechanical interlock and (4) ea - N.O. sequential contacts per button. It is CSA approved only.

Accessories

Cat. No.	Part No.	Description	List Price	Cat. No.	Part No.	Description	List Price
MABC	HC80320-115	Add-A-Block – NO/NC Contacts ⑤	\$64	M21	HC80325-102	Momentary Mech/elec Interlock 2 NC	\$140
MABA	HC80320-116	Add-A-Block – 2 NO Contacts ⑤	\$64	MRI	HC80325-103	Maintained Reset Interlock ③	\$72
MABB	HC80320-117	Add-A-Block – 2 NC Contacts ⑤	\$64	MNOW	HC80325-104	Nut Wrench for 22mm Mushroom Hd ②	\$48
MLR	HC80324-800	Red Pilot Light Lens/Nut	\$24	MBB	HC80325-900	Black Push-Pull Cap 1-3/8"	\$56
MLA	HC80324-801	Amber Pilot Light Lens/Nut	\$24	MBR	HC80325-901	Red Push-Pull Cap 1-3/8"	\$56
MLG	HC80324-802	Green Pilot Light Lens/Nut	\$24	MBG	HC80325-902	Green Push-Pull Cap 1-3/8"	\$56
MLW	HC80324-803	White Pilot Light Lens/Nut	\$24	MCB	HC80325-905	Black Maintained Cap	\$20
MLB	HC80324-804	Blue Pilot Light Lens/Nut	\$24	MCR	HC80325-906	Red Maintained Cap	\$20
MLC	HC80324-805	Clear Pilot Light Lens/Nut	\$24	MCG	HC80325-907	Green Maintained Cap	\$20
MBNR	HC80324-900	Bulb Neon Red 120 VAC/DC	\$12	MRBB	HC80325-911	Black Rubber Boot for Standard Button	\$60
MBNG	HC80324-901	Bulb Neon Green 120 VAC/DC	\$12	MRBR	HC80325-912	Red Rubber Boot for Standard Button	\$60
MBR250	HC80324-905	Bulb Incandescent Clear 250 VAC/DC	\$28	MRBG	HC80325-913	Green Rubber Boot for Standard Button	\$60
MBR120	HC80324-906	Bulb Incandescent Clear 120 VAC/DC	\$28	MRBY	HC80325-914	Yellow Rubber Boot for Standard Button	\$60
MBI	HC80325-100	Mechanical Interlock for M1G, M2G, M0G and MCG Inserts	\$52				
MNW	HC80325-101	Molded Nut Wrench for 22mm Inserts	\$52				

Prices Subject to Change without Notice



Hubbell Industrial Controls, Inc.

a subsidiary of Hubbell Incorporated

4301 Cheyenne Drive, Archdale, NC 27263

Phone (336) 434-2800 | Fax (336) 434-2801

www.hubbell.com/hubbellindustrialcontrols/en

sales@hubbell-icd.com