


# Speed Responsive Switch

# 2200

Price List 2200 • January 2021, Replaces May 2010

EXAMPLE CATALOG NUMBER: **2200-PRS-031-01WPE**



STANDARD CATALOG NUMBERS	PART NUMBERS	CONTACT ADJUSTMENT RANGE (2)				MAXIMUM RUNNING SPEED RPM WITHOUT SPEED INCREASER	CONTACTS (3)		LIST PRICE DISC. CODE FF
		CONTACTS OPERATE					LEFT HAND	RIGHT HAND	
		MIN. RPM		MAX. RPM					
		INCR(2) SPEED	DECR SPEED	INCR. SPEED	DECR SPEED				
<b>SNAP-ACTION - PRECISION SWITCH TYPE NON-DIRECTIONAL CONTACTS - A-C</b>									
2200-PRS-031-01	HC00707310	100	65	180	140	1800	· N.O. — N.C.	· N.O. — N.C.	\$6,700
2200-PRS-031-11	HC00707320	115	85	210	170	2000	· N.O. — N.C.	· N.O. — N.C.	\$6,500
2200-PRS-031-21	HC00707330	185	140	330	280	3600	· N.O. — N.C.	· N.O. — N.C.	\$6,500
2200-PRS-031-22	HC00707340	250	200	800	680	3600	· N.O. — N.C.	· N.O. — N.C.	\$6,500
2200-PRS-031-32	HC00707350	420	350	1500	1370	3600	· N.O. — N.C.	· N.O. — N.C.	\$6,500
2200-PRS-031-42	HC00707360	800	650	2800	2600	3600	· N.O. — N.C.	· N.O. — N.C.	\$6,500
2200-PRS-031-52	HC00707370	1550	141	3600	3340	4000	· N.O. — N.C.	· N.O. — N.C.	\$6,500
<b>SNAP-ACTION - PRECISION SWITCH TYPE NON-DIRECTIONAL CONTACTS - D-C</b>									
2200-PRD-031-01	HC00704810	115	80	207	157	1800	· N.O. — N.C.	· N.O. — N.C.	\$7,300
2200-PRD-031-11	HC00704820	130	90	210	160	2000	· N.O. — N.C.	· N.O. — N.C.	\$7,100
2200-PRD-031-21	HC00704830	200	150	340	250	3600	· N.O. — N.C.	· N.O. — N.C.	\$7,100
2200-PRD-031-22	HC00704840	300	190	760	630	3600	· N.O. — N.C.	· N.O. — N.C.	\$7,100
2200-PRD-031-32	HC00704850	640	420	1700	1300	3600	· N.O. — N.C.	· N.O. — N.C.	\$7,100
2200-PRD-031-42	HC00704860	950	670	3000	2320	3600	· N.O. — N.C.	· N.O. — N.C.	\$7,100
2200-PRD-031-52	HC00704870	160	113	4000	3090	4000	· N.O. — N.C.	· N.O. — N.C.	\$7,100
<b>SNAP-ACTION - PRECISION SWITCH TYPE NON-DIRECTIONAL MANUALLY RESET CONTACTS - A-C</b>									
2200-PRS-038M-01	HC00707410	115		207		1800	· N.O. — N.C.	· N.O. — N.C.	\$8,000
2200-PRS-038M-11	HC00707420	130		210		2000	· N.O. — N.C.	· N.O. — N.C.	\$7,800
2200-PRS-038M-21	HC00707430	200		340		3600	· N.O. — N.C.	· N.O. — N.C.	\$7,800
2200-PRS-038M-22	HC00707440	300		760		3600	· N.O. — N.C.	· N.O. — N.C.	\$7,800
2200-PRS-038M-32	HC00707450	640		1700		3600	· N.O. — N.C.	· N.O. — N.C.	\$7,800
2200-PRS-038M-42	HC00707460	950		3000		3600	· N.O. — N.C.	· N.O. — N.C.	\$7,800
2200-PRS-038M-52	HC00707470	1600		4000		4000	· N.O. — N.C.	· N.O. — N.C.	\$7,800

Repeatability: ± 5% of set RPM. Speed Ranges shown in table are for horizontally mounted switches with contacts set for simultaneous operation. If switches are to be vertically mounted and/or the contacts are adjusted for independent operation, consult factory. Switch contact may be set for either increasing speed or decreasing speed operation. However, the differential speed is non-adjustable and subject to mechanical tolerances.

Price List 2200 • January 2021, Replaces May 2010

2200 TYPE PR OPTIONS		LIST PRICES - ADD TO SWITCH BASE PRICE		
NEMA TYPE	SURFACE MOUNTING	- E - FLATED REAR SHAFT EXTENSION	- EX9- KEYED REAR SHAFT EXTENSION	- F - FLANGE MOUNTING
1	Standard	\$618	\$618	\$1500
3R	\$300	\$618	\$618	-

TYPE OF CONTACT	A.C. 35% P.F.			D.C. Inductive	
	120v	240v	480v	125v	250v
Snap Action A.C. Type	3.0	1.5	.75	.25	.12
Snap Action D.C. Type	-	-	-	.60	.25

REFER TO FACTORY FOR OPTIONAL FEATURES NOT SHOWN.

**NOTES**

- (1) Enclosures meet NEMA standards for protection against lint, dust, seepage and spraying of water, oil or coolant. For NEMA 1, 3, 5 and 13 applications.
- (2) Contacts are factory calibrated at minimum ascending RPM unless otherwise specified on customer's purchase order.
- (3) Contact symbols are shown with switch at rest and viewed from the rear.

Prices are subject to change without notice.



**Hubbell Industrial Controls, Inc.**

*a subsidiary of Hubbell Incorporated*  
 4301 Cheyenne Drive, Archdale, NC 27263  
 Phone (336) 434-2800 • Fax (336) 434-2803  
[www.hubbell.com/hubbellindustrialcontrols/en](http://www.hubbell.com/hubbellindustrialcontrols/en)  
[sales@hubbell-icd.com](mailto:sales@hubbell-icd.com)