


# Speed Responsive Switch

# 2210

Price List 2210 • January 2021, Replaces July 2013

EXAMPLE CATALOG NUMBER: **2210-132CC13F**



STANDARD CATALOG NUMBERS	PART NUMBERS	CONTACT ADJUSTMENT RANGE				MAXIMUM RUNNING SPEED RPM WITHOUT SPEED INCREASER	CONTACTS		LIST PRICE SCHEDULE FG
		CONTACTS OPERATE					LEFT HAND	RIGHT HAND	
		MIN. RPM		MAX. RPM					
		INCR(2) SPEED	DECR SPEED	INCR. SPEED	DECR SPEED				
<b>SNAP-ACTION - PRECISION SWITCH TYPE NON-DIRECTIONAL CONTACTS - A-C</b>									
2210-132CC13	HC00710406	120	85	590	550	1800	· N.O. — N.C.	· N.O. — N.C.	\$3,398
2210-142CC13	HC00711126	90	75	425	410	1800	· N.O. — N.C.	· N.O. — N.C.	\$3,540
2210-222CC13	HC00782566	190	160	1300	1150	4000	· N.O. — N.C.	· N.O. — N.C.	\$3,256
2210-232CC13	HC00713286	130	95	750	690	4000	· N.O. — N.C.	· N.O. — N.C.	\$3,328
2210-312CC13	HC00785446	470	315	3700	3500	5000	· N.O. — N.C.	· N.O. — N.C.	\$3,116
<b>SNAP-ACTION - PRECISION SWITCH TYPE NON-DIRECTIONAL CONTACTS - D-C</b>									
2210-133CC13	HC00710646	165	115	700	575	1800	· N.O. — N.C.	· N.O. — N.C.	\$3,752
2210-223CC13	HC00782806	250	175	1350	1120	4000	· N.O. — N.C.	· N.O. — N.C.	\$3,610
2210-233CC13	HC00713526	225	135	750	610	4000	· N.O. — N.C.	· N.O. — N.C.	\$3,682
2210-313CC13	HC00785686	520	390	3600	3250	5000	· N.O. — N.C.	· N.O. — N.C.	\$3,470

Repeatability: ± 5% of set point RPM. Speed Ranges shown in table are for horizontally mounted switches. If switches are to be vertically mounted, consult factory. Switch contact may be set for either increasing speed or decreasing speed operation. However, the differential speed is non-adjustable and subject to mechanical tolerances.

MAXIMUM CONTACT INTERRUPTING RATINGS					
TYPE OF CONTACT	A.C. 35% P.F.			D.C. Inductive	
	120v	240v	480v	125v	250v
Snap Action A.C. Type	3.0	1.5	.75	.25	.12
Snap Action D.C. Type	-	-	-	.60	.25

2210 TYPE C OPTIONS		LIST PRICES - ADD TO SWITCH BASE PRICE					
NEMA TYPE	SURFACE MOUNTING	- S -	- SS -	- F -	- FS -	- M -	- MM -
		SURFACE MOUNTING W/ SINGLE SPEED INCREASER	SURFACE MOUNTING W/ DOUBLE SPEED INCREASER	FLANGE MOUNTING	FLANGE MOUNTING W/ SINGLE SPEED INCREASER	SINGLE MANUAL RESET	DOUBLE MANUAL RESET
AC SPST ONLY							
13	Standard	\$1,558	\$4,886	\$708	\$2,762	\$778	\$1,416
4	\$284	\$1,840	\$5,168	-	-	\$778	\$1,416
7	\$2,336	\$3,894	\$7,222	\$2,690	-	\$778	\$1,416
9	\$2,620	\$4,178	\$7,504	\$2,690	-	\$778	\$1,416
10	\$2,478	\$4,036	-	-	-	-	-

REFER TO FACTORY FOR OPTIONAL FEATURES NOT SHOWN.

**NOTES**

- (1) Enclosures meet NEMA standards for protection against lint, dust, seepage and spraying of water, oil or coolant. For NEMA 1, 3, 5 and 13 applications.
- (2) Contacts are factory calibrated at minimum ascending RPM unless otherwise specified on customer's purchase order.
- (3) Contact symbols are shown with switch at rest and viewed from the rear.

Prices are subject to change without notice.



**Hubbell Industrial Controls, Inc.**  
*a subsidiary of Hubbell Incorporated*  
 4301 Cheyenne Drive, Archdale, NC 27263  
 Phone (336) 434-2800 · Fax (336) 434-2803  
 www.hubbell.com/hubbellindustrialcontrols/en  
 sales@hubbell-icd.com