



A66939

DC/AC Inverter with 3000W Output Ruggedized Cabinet for Industrial Applications

Specification		
Input	Input Voltage Range	127 ~ 370 Vdc
Output	Output Power (typ.)	3000W
	Maximum Output Power	3450W for 180sec
	Output Voltage	120Vac
	Frequency	60Hz
	AC Regulation	+/-3%
Environment	Working Temp	-20 ~ +70 C
	Humidity	20 ~ 90% RH non Condensing
	Storage Temp	-30 ~ +70 C
	Storage Humidity	10 ~ 95% RH
Mechanical	Dimensions	30" x 30" x 12"
	Weight	50 Lbs

The information contained in this specification is subject to change without prior notification.

Cableform Inc.
8845 Three Notch Road, Troy, VA 22974 USA
Tel: 434-589-8224 Fax: 434-589-3803 Email: sales@cableform.com

www.cableform.com

Specifications are subject to change without notice ©2012 Cableform Inc. BR-0004_R0