

Z-Switch™

HEATER CONTACTOR



REDUNDANT IGBT SOLID STATE CONTACTOR WITH INTEGRAL CIRCUIT AND LOAD MONITORING FOR SWITCHING OF DC LOADS

Specifications:

Nominal Load Current:	60 Amps
Maximum Load Current:	125 Amps
Supply Voltage:	530 VDC Nominal 600 VDC Max 450 VDC Min
Control Voltage:	72 VDC Nominal 90 VDC Max 50 VDC Min
Auxiliary Contact Rating:	10 ma @ 72 VDC
Operating Temperature Range:	-10°C to +40°C
Heat Sink Temperature Range:	-25°C to +75°C



Part Number: A65045



8845 Three Notch Rd., Troy, VA 22974
 Phone: (434)589-8224 | Fax: (434)589-3803
www.CABLEFORM.com

Call us today or visit us online for more information.