


Ultra-flexible  
compact design



**Pad Mount Deadfront**  
Primary Metering Gear




## Grounding provisions.

- Meets all current ANSI standards.
- All manufacturers' outdoor PTs and CTs can be supplied via use of universal mountings.
- Powder finish exceeds ANSI C57.12.28 requirements; Munsell green (7GY 3.29/1.5) to blend with surroundings.
- Phase isolated design with white electrical grade fiberglass barriers for ease of operation.
- Stainless steel hinges and hardware for long operational life.

Primary metering gear provides a safe, convenient means to meter primary voltages from 15-35kV. Single- or three-phase units are supplied completely assembled and wired, ready for installation. Available in loop or radial feed with 200A (standard) bushing wells or 600A (optional) bushings.

## One Line Diagrams



Mimic bus on dead-front side and on individual lift-out rear barriers on metering transformer side.



Light gray metal dead-front barrier provides maximum contrast with black elbows.

Recessed lifting lugs.



Penta-head bolt and three-point latch on both live and dead-front sides for greater security.

Open bottom design with "C" channel and two-inch lip.

Pad Mount Primary Metering Enclosures

Options:

- 600A bushings
- Meter socket installed
- PTs and CTs installed

Trinetics, a division of Maysteel, LLC, PO Box 1240, Menomonee Falls, WI 53052-1240 [Trinetics.com](http://Trinetics.com)

**ISO 9001:2008**  
QUALITY CERTIFIED