

EV4R

Recessed Ceiling Mount LED Emergency Light


EMERGENCY LIGHT



FEATURES

- Architectural recessed ceiling mount, emergency light with superior emergency lighting coverage
- Flame-rated, UV stable thermoplastic housing
- Choice of round or rectangular trim-plate in white or black finish
- 4 LEDs housed within an aluminum heat-sink and adjustable optic assembly
- Individual LEDs are driven at 1 watt each for 88 lumens per LED
- UL924 damp location listed
- IC Rated

ORDERING INFORMATION



¹ Each model includes round or rectangular trim-plate
² Each model is damp listed
³ Not for 220-240VAC input

ELECTRONICS

- 120/277VAC input with Intelligent 2 wire connection
- AC lockout and Low Voltage disconnect
- Battery re-charge within 24 hours
- Optional Self-Test/Self-Diagnostic circuitry

POWER CONSUMPTION

	AC Voltage	Hz.	Amps.	Max. Watts	Power Factor
EV4R	120	60	0.022	2.00	0.73
	240	60	0.015	2.51	0.65
	277	60	0.014	2.75	0.63

Maintenance mode power consumption less than 0.5 watts.



MULTI-UNIT SPACING



Meets Life Safety Code minimum illuminance of 0.1 fc and average illuminance of 1.0 fc. Assumes open space with no obstructions, ceiling height of 9' and reflectances of 80/50/20. Photometry files available on the Dual-Lite web site (www.dual-lite.com).

Mounting Height: 9'
 Path Width: 6'
 Spacing: 42'

