

Outdoor Geometric LED Wallpack

EMERGENCY LIGHTING



FEATURES

- "Normally On" emergency luminaire for architectural applications
- Made from die-cast aluminum with four finishes; Dark Bronze, Platinum Silver, White and Black
- Available in three geometric shapes: Radius, Trapezoid and Quartersphere
- 12 high-power LEDs create 3115 lumens in AC and 658 lumens in emergency mode
- Environmentally friendly, long-life Lithium Iron Phosphate battery
- Standard Temperature Range: 0°C to 40°C, Optional Heater: -30°C to 40°C
- Wet Location Listed to UL924

ORDERING INFORMATION

MODEL	CCT	VOLTAGE	FINISH	OPTIONS
RD11 Radius	3K 3000K	U 120/277 VAC	DB Dark Bronze	E Emergency with Battery
TRP1 Trapezoid	4K 4000K		PS Platinum Silver	EH Emergency with Battery and Heater (-30°C to 40°C)
QSP1 Quartersphere			WH White	
			BL Black	

¹ Stocked models have a CCT of 4000K.

² Order AC only models through Hubbell Outdoor

INPUT POWER CONSUMPTION



	INPUT VOLTS	AMPS	MAXIMUM WATTAGE
GeoPak	120	0.27	31.8
	277	0.15	32.2
GeoPak with heater	120	0.42	50.2
	277	0.20	50.7

ELECTRONICS

- Includes Spectron Self-Test/Self-Diagnostic circuitry
- 120/277VAC input with Transient Surge Protection
- AC lockout and Low Voltage disconnect
- Battery re-charge within 24 hours
- Automatic transfer in brown-out conditions

DIMENSIONS



Quartersphere



WEIGHT

TRP1- 11.5 lbs
QSP1- 10.5 lbs
RD11- 11.5 lbs

Radius



Trapezoid

