

Chicago LED Steel Emergency Unit



FEATURES

- Chicago Approved Unit for industrial and commercial applications
- 20 gauge steel with white finish
- Long-life LED lamps provide bright and even illumination
- Dual 120/277VAC input
- Includes Sealed Lead Acid battery
- Knockouts for wall mounting
- Knockouts for top and side mounting lamp heads
- AC-on and test switch
- Approved for use in the City of Chicago

ORDERING INFORMATION

CCU2

MODEL



WATTS


- Blank** 10W
- RC** Remote Capacity (20W)

MAXIMUM POWER CONSUMPTION

CATALOG NUMBER	INPUT WATTS (W)		INPUT AMPS (A)	
	120V	277V	120V	277V
CCU2	8.4	9.4	0.08A	0.04A
CCU2RC	8.7	10.0	0.09A	0.05A

ELECTRONICS

- Sealed Lead Acid Battery
- Dual 120/277 Temperature Range
- Operating Temp: 20°C to 50°C



- CRHO** - Outdoor Remote for Chicago
- CRHI** - Indoor Remote for Chicago



Outdoor Remote Head



Indoor Remote Head