



ANDERSON® VERSA-CRIMP® BATTERY POWERED ACSR CUTTING TOOL TYPE BP18CC129ACSR

TOOL
BP18C- C129ACSR

For Use On:

- Copper Cable- up to 1.29 "(32.7 mm)
- Aluminum cable- up to 1.29"(32.7 mm)
- ACSR - up to 1113 ACSR
- Standard Guy Wire-up to 1/2 (12.7 mm)
- EHS Guy Wire-up to 3/8" (9.5 mm)
- Ground Rod-up to 5/8"(15.8 mm)
- Rebar- up to 1/2"(12.7 mm)
- Soft Steel Bolts- up to 5/8"(15.8 mm)
- 18 volt Lithium-Ion rechargeable batteries
- Latch type head rotates 180 degrees
- Comfortable overmolded handle balanced for one hand operation



Includes:

- 18-volt battery powered cable cutter tool
- Two 18-volt Lithium-Ion batteries
- AC charger - 30 minutes recharge
- High impact plastic case - ergonomic carrying design with storage.
- Lanyard strap
- Instruction manual and warranty card
- 5-year limited warranty on tool (excludes blades) with 1-year on batteries and charger

ACCESSORIES

Battery:

(3.0 AH) Hi-capacity Cat.# BAT18VLI

Chargers:

120V-AC Cat.# PATCHGR-LI
12/24-DC Cat.# PATCHGR-LIDC
240/250V-AC Cat.# PATCHGR-LI250V

Lanyard:

Cat.# PT208620

Approx. Wt. Each:

1 lbs. (4.9 kg) with Battery

Kit Shipping Wt.:

23 lbs. (10.s kg)

ANDERSON® VERSA-CRIMP® HYDRAULIC COMPRESSION TOOL BATTERY OPERATED TYPE VCBP63

TOOL
VCBP63
AL/CU

- 18-volt Lithium-Ion rechargeable batteries
- Open head design allows for direct access to the connector in restricted areas.
- Four-nib dieless head with 360 degree rotation
- Crimps range-taking Versa-Crimp and Versatile connectors
- Comfortable overmolded handle balanced for one hand operation



Type VCBP63

Includes:

- 18-volt battery powered dieless crimp tool
- Two 18-volt 3.0 Ah Lithium-Ion batteries
- AC charger - 30 minutes recharge
- High impact plastic case - ergonomic carrying design with storage.
- Lanyard strap
- Instruction manual and warranty card
- 5-year limited tool warranty with 1-year on batteries and charger

ACCESSORIES

Battery:

(3.0 AH) Hi-capacity Cat.# BAT18VLI

Chargers:

120V-AC Cat.# PATCHGR-LI
12/24-DC Cat.# PATCHGR-LIDC
240/250V-AC Cat.# PATCHGR-LI250V

Lanyard:

Cat.# PT208620

Conductor Range:

#10 Str. - 750 MCM Al/Cu

Approx. Weight Each:

13.2 lbs. (5.9 kg.) with Battery

Kit Shipping Wt.:

25 lbs. (11.1 kg)

DG
7