


# DEADENDS FORMED WIRE DISTRIBUTION GRIP

ALUMINUM/STEEL  
DGFW

- For deadending bare or plastic jacketed conductor on primaries, secondaries, and substation feeder applications.
- Fargo DGFW series formed wire deadends are designed for use with ACSR, AAC, AAAC, Compacted ACSR and AWAC®.
- DGFW deadends will hold a minimum of 60% of the cable (RBS) rated breaking strength..



**Note:** Consult factory for information on other applications. Right hand lay standard.



## DGFW

CATALOG NUMBER	NOMINAL CONDUCTOR SIZE					DIAMETER RANGE		PACKAGING PER BOX		LENGTH	COLOR
	ACSR	AAC	AAAC	COMP ACSR	AWAC®	MIN	MAX	UNITS	WT LBS (KG)		
DGFW4554	#6 (6/1)	#6, 7W	#6, 7W	#6 (6/1)		0.182 (4.62)	0.203 (5.15)	100	13.4 (6.1)	16 (406)	BLUE
DGFW4541	#4 (6/1) #4 (7/1)	#4, 7W	#4, 7W	#4 (6/1)	#4 (6/1)	0.229 (5.81)	0.257 (6.53)	100	17.9 (8.1)	16.9 (430)	ORANGE
DGFW4542	#2 (6/1) #2 (7/1)	#2, 7W	#2, 7W	#2 (6/1)	#2 (6/1), #3 (5/2)	0.290 (7.36)	0.325 (8.27)	100	30.6 (13.9)	24 (610)	RED
DGFW4543	#1 (6/1)	#1, 7W	#1, 7W	#1 (6/1)	#1 (6/1), #2 (5/2)	.326 (8.28)	.364 (9.25)	50	25.5 (11.6)	26 (660)	GREEN
DGFW4544	1/0 (6/1)	1/0, 7W	1/0, 7W	1/0 (6/1)	1/0 (6/1), #1 (5/2)	0.365 (9.27)	0.409 (10.40)	50	27.2 (12.4)	26.4 (671)	YELLOW
DGFW4545	2/0 (6/1)	2/0, 7W	2/0, 7W	2/0 (6/1)	2/0 (6/1), 1/0 (5/2)	0.410 (10.41)	0.460 (11.69)	50	29.2 (13.3)	27.9 (710)	BLUE
DGFW4546	3/0 (6/1)	3/0, 7W	3/0, 7W	3/0 (6/1)	3/0 (6/1), 2/0 (5/2)	0.461 (11.70)	0.516 (13.12)	25	21.0 (9.5)	32.5 (825)	ORANGE
DGFW4547	4/0 (6/1)	4/0, 7W	4/0, 7W	4/0 (6/1)	4/0 (6/1), 3/0 (5/2)	0.517 (13.13)	0.577 (14.67)	25	60.0 (27.3)	34.0 (865)	RED
DGFW4548	266.8 (18/1) 266.8 (26/7) 300 (18/1)	266.8 19W 266.8 37W 300 19W 300 37W	266.8 19W	300 (18/1) 336.4 (18/1)	266.8 (18/1)	.578 (14.68)	.653 (16.60)	25	34.0 (865)	35 (889)	BLACK
DGFW4549	300 (26/7) 300 (30/7) 336.4 (18/1) 336.4 (36/1) 336.4 (26/7) 397.5 (36/1)	336.4 19 W, 336.4 37W, 350 19W, 350 37W, 397.5 19W, 397.5 37W, 400 19W, 400 37W	336.4, 7W	397.5 (18/1)	336.4 (18/1)	0.654 (16.61)	0.739 (18.77)	25	52.7 (24.0)	38.6 (980)	GREEN

**NOTES:** All dimensions: inches (mm) unless otherwise noted.  
Dimension "X" equals 1.0" (25.4 mm) in all cases.  
Neck (open helix loop) diameter equals 2" (50 mm) in all cases.  
AWAC is a registered trademark of Copperweld Co.