

Caress

FINISH
● Polished Nickel - 104

ALSO IN
Close-to-Ceiling
Bath

PAIR WITH
Equinox
Stratham

P4645-104WB

Gently sweeping arms cradle richly textured water glass shades that capture and cast shimmering light against a bright Polished Nickel frame. Etched glass diffusers add to the playful reflections while a unique stem-hung construction carries a clean line to the ceiling.

Water Glass Shades



Etched Glass Diffusers

Gentle Sweeping Arms



P4646-104WB



P4645-104WB



P3946-104



P7046-104WB

Caress

ONE-LIGHT FOYER

P3946-104 Polished Nickel
14" dia., 30" ht.,
Overall ht. w/stem 96"; wire 15'.
One medium base lamp,
100w max.

FIVE-LIGHT CHANDELIER

P4645-104WB Polished Nickel
27" dia., 22" ht.,
Overall ht. w/stem 88"; wire 15'.
Five candelabra base krypton lamps*,
each 60w max., included.

NINE-LIGHT CHANDELIER

P4646-104WB Polished Nickel
36-5/8" dia., 33-5/8" ht.,
Overall ht. w/stem 100"; wire 15'.
Nine candelabra base krypton lamps*,
each 60w max., included.

WALL BRACKET

P7046-104WB Polished Nickel
8" W., 15" ht.,
Extends 9-1/2". H/CTR 8-7/8".
One candelabra base krypton lamp*,
60w max. included.

*Replacement lamp P7807-01.



Reflect with Sparkle & Shine

All white is just right when it is coupled with a polished wooden table and floorboards to ground the look. Make the most of a small dining area by using mirrors to reflect light and open up the space. Use a chandelier like Caress as a focal point, whose water glass shades add rich texture and playful reflections from the striking mirrored wall.



Caress


THREE-LIGHT CHANDELIER
P4644-104WB Polished Nickel
22" dia., 24-1/2" ht.,
Overall ht. w/stem 91"; wire 15'.
Three candelabra base krypton
lamps*, each 60w max., included.

SIXTEEN-LIGHT CHANDELIER
P4685-104WB Polished Nickel
47" dia., 46" ht.,
Overall ht. w/stem 181"; wire 15'.
Sixteen candelabra base krypton
lamps*, each 60w max., included.
*Weight of fixture exceeds NEC limits for
outlet box hanging. Consult professional
electrician for proper installation.*

MINI-PENDANT
P5044-104WB Polished Nickel
6-3/8" dia., 10-3/4" ht.,
Overall ht w/chain or stem 77"; wire 15'.
One candelabra base krypton lamp*,
60w max., included.

MINI-PENDANT
P5306-104WB Polished Nickel
8" dia., 12-1/2" ht.,
Overall ht. w/stem 78"; wire 15'.
One candelabra base krypton lamp*,
60w max., included.

*Replacement lamp P7807-01.



Caress

FINISH

● Polished Nickel - 104

ALSO IN

Collections
Close-to-Ceiling

P3076-104WB

Chic sophistication with cylindrical glass shades. Etched glass diffuser inside clear water glass floats in a traditional profile.

Etched Glass Diffuser



Traditional Profile

Cylindrical Glass Shades



P3076-104WB



P7046-104WB



P3077-104WB



P3078-104WB

ONE-LIGHT BATH

P7046-104WB Polished Nickel
8" W., 15" ht.
Extends 9-1/2". H/CTR 8-7/8".
One candelabra base krypton lamp,
60w max., included.

TWO-LIGHT BATH

P3076-104WB Polished Nickel
18-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Two candelabra base krypton lamps,
each 60w max., included.

THREE-LIGHT BATH

P3077-104WB Polished Nickel
26-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Three candelabra base krypton lamps,
each 60w max., included.

FOUR-LIGHT BATH

P3078-104WB Polished Nickel
34-1/2" W., 5-5/8" ht. Extends 7".
H/CTR 2-3/4".
Four candelabra base krypton lamps,
each 60w max., included.

*Replacement lamp P7807-01.
See page 824.*

Caress

Shimmering water glass shade surrounds an etched glass diffuser.

TWO-LIGHT SEMI-FLUSH

P3434-104 Polished Nickel

16" dia., 12" ht.

Two medium base lamps,
each 100w max.

SEMI-FLUSH CONVERTIBLE

P5044-104WB Polished Nickel

Hanging and ceiling mount
hardware included.

6-3/8" dia., 11" ht.,

Overall ht w/chain or stem 76"; wire 15'

One candelabra base lamp,
60w max. Krypton lamp included.



P5044-104WB



P3434-104

Replacement lamp P7807-01.

Caress

A shimmering water glass shade and polished frame add rich textures and playful reflections.

P7046-104WB Polished Nickel
8" W., 15" ht.
Extends 9-1/2". H/CTR 8-7/8".
One candelabra base krypton lamp,
60w max, included.

Replacement lamp P7807-01.



P7046-104WB