

Tinsley

P400066-109

FINISHES

- Polished Chrome - 015
- Brushed Bronze - 109

ALSO IN

Close-to-Ceiling

PAIR WITH


Celeste
Landree
Clarion

Featuring soft angles and impressive sculptural curves, Tinsley is a refreshingly updated design for Luxe, Transitional and Traditional interiors. The frame is complemented by classic etched glass shades or open candle designs. Overscale details found in Tinsley are ideal for welcoming guests and visitors in a foyer or entryway, as well as in luxe dining room or classic living room settings.

Sculptural Curves

Soft Angles

Classic Design



Tinsley

SEMI-FLUSH CONVERTIBLE

P350079-109 Brushed Bronze
Hanging and ceiling mount hardware included.
16-1/2" dia., 11-1/2" ht.,
Overall ht. w/chain 51", wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400065-109 Brushed Bronze
23-1/2" dia., 19" ht.,
Overall ht. w/chain 94", wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400066-109 Brushed Bronze
23" dia., 24" ht.,
Overall ht. w/chain 99", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400067-109 Brushed Bronze
29-1/4" dia., 31" ht.,
Overall ht. w/chain 154", wire 15'.
Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400110-109 Brushed Bronze
42" dia., 41-3/4" ht.,
Overall ht. w/chain 154", wire 15'.
Fifteen candelabra base lamps, each 60w max.

THREE-LIGHT PENDANT


P500062-109 Brushed Bronze
22-1/2" dia., 22-1/2" ht.,
Overall ht. w/chain 97-1/2", wire 15'.
Three medium base lamps, each 100w max.

MINI-PENDANT

P500072-109 Brushed Bronze
7-1/2" dia., 12-1/2" ht.,
Overall ht. w/stem 80-1/2", wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710028-109 Brushed Bronze
4-7/8" W., 15-1/2" ht.,
Extends 5-1/2". H/CTR 8".
One candelabra base lamp, 60w max.



Tinsley

SEMI-FLUSH CONVERTIBLE

P350079-015 Polished Chrome
Hanging and ceiling mount hardware included.
16-1/2" dia., 11-1/2" ht.,
Overall ht. w/chain 51", wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400065-015 Polished Chrome
23-1/2" dia., 19" ht.,
Overall ht. w/chain 94", wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400066-015 Polished Chrome
23" dia., 24" ht.,
Overall ht. w/chain 99", wire 15'.
Five candelabra base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400067-015 Polished Chrome
29-1/4" dia., 31" ht.,
Overall ht. w/chain 154", wire 15'.
Nine candelabra base lamps, each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400110-015 Polished Chrome
42" dia., 41-3/4" ht.,
Overall ht. w/chain 154", wire 15'.
Fifteen candelabra base lamps, each 60w max.

THREE-LIGHT PENDANT

P500062-015 Polished Chrome
22-1/2" dia., 22-1/2" ht.,
Overall ht. w/chain 97-1/2", wire 15'.
Three medium base lamps, each 100w max.

MINI-PENDANT

P500072-015 Polished Chrome
7-1/2" dia., 12-1/2" ht.,
Overall ht. w/stem 80-1/2", wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710028-015 Polished Chrome
4-7/8" W., 15-1/2" ht.,
Extends 5-1/2". H/CTR 8".
One candelabra base, 60w max.

Tinsley

Soft angles and impressive curves complement etched glass or open candle designs.

SEMI-FLUSH CONVERTIBLE

P350079-015 Polished Chrome

P350079-109 Brushed Bronze

Hanging and ceiling mount hardware included.

16-1/2" dia., 11-1/2" ht.,

Overall ht. w/chain 51", wire 10'.

Two medium base lamps, each 100w max.

P350079-015



P350079-109



TWO-LIGHT FLUSH MOUNT

P350103-015 Polished Chrome

P350103-109 Brushed Bronze

16-1/2" dia., 5-7/8" ht.

Two medium base lamps, each 60w max.

P350103-015



P350103-109



Tinsley

Soft angles and impressive sculptural curves complement an open candle design.

P710028-109 Brushed Bronze
P710028-015 Polished Chrome
4-7/8" W., 15-1/2" ht.
Extends 5-1/2". H/CTR 8".
One candelabra base lamp,
60w max.



P710028-015



P710028-109