

Kene

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ALSO IN

Bath

PAIR WITH

Chadwick
Lassiter

P400095-143

With flowing ribbons of metal that hold double glass shades with balance and grace, Kene is inspired by traditional forms yet has a modern edge. Etched glass diffusers offer a patterned texture that shines through clear outer shades providing a luxurious touch. A semi-flush convertible ceiling fixture with a textured fabric shade rounds out the collection beautifully.

Clean Outer Shades



Graphite Finish

Etched Glass Diffusers



P400096-143



P400095-143



P350098-143



P500103-143

Kene

SEMI-FLUSH CONVERTIBLE

P350098-143 Graphite
Hanging and ceiling mount hardware included.
16" dia., 10-7/8" ht.,
Overall ht. w/chain 50-1/2", wire 10'.
Two medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER

P400095-143 Graphite
27-1/4" dia., 22-1/2" ht.,
Overall ht. w/chain 97-1/2", wire 15'.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER

P400096-143 Graphite
32-3/4" dia., 29-7/8" ht.,
Overall ht. w/chain 152-1/2", wire 15'.
Nine medium base lamps, each 75w max.

MINI-PENDANT

P500103-143 Graphite
6" dia., 15-7/8" ht.,
Overall ht. w/chain 82-1/2", wire 10'.
One medium base lamp, 75w max.

P400095-009



Tranquil and Romantic

Clean Glass Shades

Brushed Nickel

P400096-009



P400095-009



P350098-009



P500103-009



Kene

SEMI-FLUSH CONVERTIBLE
P350098-009 Brushed Nickel
 Hanging and ceiling mount hardware included.
 16" dia., 10-7/8" ht.,
 Overall ht. w/chain 50-1/2", wire 10'.
 Two medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER
P400095-009 Brushed Nickel
 27-1/4" dia., 22-1/2" ht.,
 Overall ht. w/chain 97-1/2", wire 15'.
 Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER
P400096-009 Brushed Nickel
 32-3/4" dia., 29-7/8" ht.,
 Overall ht. w/chain 152-1/2", wire 15'.
 Nine medium base lamps, each 75w max.

MINI-PENDANT
P500103-009 Brushed Nickel
 6" dia., 15-7/8" ht.,
 Overall ht. w/chain 82-1/2", wire 10'.
 One medium base lamp, 75w max.

Kene

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ALSO IN

- Collections
- Close-to-Ceiling

P300121-009

Add a whimsy romance to the heart of your home with the lovely Kene Collection. Quiet, etched glass diffusers surrounded by clear, outer shades mark this collection with a soft luxurious touch. Kene is guaranteed to help make your home a calming, tranquil oasis infused with elegance and charm.



Brushed Nickel

WALL BRACKET

P300120-009 Brushed Nickel
4-3/4" W., 12-7/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
75w max.

TWO-LIGHT BATH

P300121-009 Brushed Nickel
16-1/4" W., 7-3/8" ht.
Extends 7-1/4". H/CTR 4-5/8".
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH

P300122-009 Brushed Nickel
23-3/8" W., 7-3/8" ht.
Extends 7-7/8". H/CTR 4-5/8".
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH

P300123-009 Brushed Nickel
30-3/4" W., 7-3/8" ht.
Extends 8-1/8". H/CTR 4-5/8".
Four medium base lamps,
each 75w max.



P300123-009

P300120-009



P300121-009



P300122-009

All fixtures mount up or down.

Kene

WALL BRACKET

P300120-143 Graphite
4-3/4" W., 12-7/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
75w max.

TWO-LIGHT BATH

P300121-143 Graphite
16-1/4" W., 7-3/8" ht.
Extends 7-1/4". H/CTR 4-5/8".
Two medium base lamps,
each 75w max.

THREE-LIGHT BATH

P300122-143 Graphite
23-3/8" W., 7-3/8" ht.
Extends 7-7/8". H/CTR 4-5/8".
Three medium base lamps,
each 75w max.

FOUR-LIGHT BATH

P300123-143 Graphite
30-3/4" W., 7-3/8" ht.
Extends 8-1/8". H/CTR 4-5/8".
Four medium base lamps,
each 75w max.

All fixtures mount up or down.



P300120-143



P300121-143



P300122-143



P300123-143

Kene

A soft metal curve supports an etched glass shade offering elegance and charm.

P300120-143 Graphite
P300120-009 Brushed Nickel
4-3/4" W., 12-7/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
75w max.



P300120-143



P300120-009

Kene

Etched glass diffusers surrounded by clear outer shades lend a soft luxurious touch.

SEMI-FLUSH CONVERTIBLE

P350098-009 Brushed Nickel

P350098-143 Graphite

Hanging and ceiling mount hardware included.

16" dia., 10-7/8" ht.,

Overall ht. w/chain 50-1/2", wire 10'.

Two medium base lamps, each 75w max.



P350098-143



P350098-009