

Torino

FINISH

● Brushed Nickel - 09

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

PAIR WITH

Markor

SEMI-FLUSH CONVERTIBLE

P3843-09 Brushed Nickel
Hanging and ceiling mount hardware included.
18" dia., 18-1/2" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3847-09 Brushed Nickel
22" dia., 27" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4405-09 Brushed Nickel
19-1/8" dia., 19-1/8" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4416-09 Brushed Nickel
26-1/8" dia., 24-3/4" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps,
each 100w max.

SIX-LIGHT CHANDELIER WITH THREE-LIGHT BOWL

P4417-09 Brushed Nickel
28-5/8" dia., 29-7/8" ht.,
Overall ht. w/chain 105"; wire 15'.
Six medium base lamps, each 100w
max. and three medium base lamps,
each 75w max.

WALL SCONCE

P7181-09 Brushed Nickel
9-1/2" W., 6-3/4" ht.,
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp,
100w max.



Torino

WALL BRACKET

P2881-09 Brushed Nickel
7" W., 8-1/4" ht.,
Extends 9-1/8".
One medium base lamp,
100w max.

NINE-LIGHT CHANDELIER WITH THREE-LIGHT BOWL

P4418-09 Brushed Nickel
32" dia., 32-5/8" ht.,
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps,
each 100w max. and three
medium base lamps,
each 75w max.

TWELVE-LIGHT CHANDELIER

P4419-09 Brushed Nickel
34" dia., 41-5/8" ht.,
Overall ht. w/chain 164"; wire 15'.
Twelve medium base lamps,
each 100w max.

MINI-PENDANT

P5153-09 Brushed Nickel
7-1/2" dia., 11" ht.,
Overall ht. w/stem 62"; wire 10'.
One medium base lamp,
100w max.

Torino

FINISH

● Forged Bronze - 77

ALSO IN

Bath
Close-to-Ceiling
Ceiling Fan

SEMI-FLUSH CONVERTIBLE

P3843-77 Forged Bronze
Hanging and ceiling mount hardware included.
18" dia., 18-1/2" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps, each 100w max.

THREE-LIGHT PENDANT

P3847-77 Forged Bronze
22" dia., 27" ht.,
Overall ht. w/chain 102"; wire 15'.
Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4405-77 Forged Bronze
19-1/8" dia., 19-1/8" ht.,
Overall ht. w/chain 94"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4416-77 Forged Bronze
26-1/8" dia., 24-3/4" ht.,
Overall ht. w/chain 100"; wire 15'.
Five medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER WITH THREE-LIGHT BOWL

P4417-77 Forged Bronze
28-5/8" dia., 29-7/8" ht.,
Overall ht. w/chain 105"; wire 15'.
Six medium base lamps, each 100w max. and three medium base lamps, each 75w max.

WALL SCONCE

P7181-77 Forged Bronze
9-1/2" W., 6-3/4" ht.,
Extends 4-3/4". H/CTR 2-7/8".
One medium base lamp, 100w max.



Torino

WALL BRACKET

P2881-77 Forged Bronze
7" W., 8-1/4" ht.
Extends 9-1/8".
One medium base lamp, 100w max.

NINE-LIGHT CHANDELIER WITH THREE-LIGHT BOWL

P4418-77 Forged Bronze
32" dia., 32-5/8" ht.,
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max. and three medium base lamps, each 75w max.

TWELVE-LIGHT CHANDELIER

P4419-77 Forged Bronze
34" dia., 41-5/8" ht.,
Overall ht. w/chain 164"; wire 15'.
Twelve medium base lamps, each 100w max.

MINI-PENDANT

P5153-77 Forged Bronze
7-1/2" dia., 11" ht.,
Overall ht. w/stem 62"; wire 10'.
One medium base lamp, 100w max.

Torino

Elegant rectangular scrolled arms with casual undertones. Forged Bronze finish with tea stained glass or Brushed Nickel finish with etched glass.



P2882-09



P2881-09



P2883-09



P2884-09



P2882-77



P2881-77



P2883-77



P2884-77

FINISHES

- Brushed Nickel - 09
- Forged Bronze - 77

ALSO IN

Collections
Close-to-Ceiling
Sconces

ONE-LIGHT BATH

P2881-09 Brushed Nickel

P2881-77 Forged Bronze

7" W., 8-1/4" ht.

Extends 9-1/4". H/CTR 4-5/8".

One medium base lamp,
100w max.

TWO-LIGHT BATH

P2882-09 Brushed Nickel

P2882-77 Forged Bronze

16" W., 7-5/8" ht.

Extends 9-1/4". H/CTR 3-3/8".

Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2883-09 Brushed Nickel

P2883-77 Forged Bronze

25" W., 7-5/8" ht.

Extends 9-1/4". H/CTR 3-3/8".

Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2884-09 Brushed Nickel

P2884-77 Forged Bronze

34" W., 7-5/8" ht.

Extends 9-1/4". H/CTR 3-3/8".

Four medium base lamps,
each 100w max.

All fixtures mount up or down.

Torino

Elegantly formed metal frames are completed by rich finishes and bell-shaped glass.

P2881-09 Brushed Nickel

P2881-77 Forged Bronze

7" W., 8-1/4" ht.

Extends 9-1/8".

One medium base lamp,
100w max.



P2881-09



P2881-77



P7181-09



P7181-77

P7181-09 Brushed Nickel

P7181-77 Forged Bronze

9-1/2" W., 6-3/4" ht.

Extends 4-3/4". H/CTR 2-7/8".

One medium base lamp,
100w max.

Torino

Oversized, bell-shaped glass bowl offset squared scrolls or simple banding.



P3843-77



P3843-09

TWO-LIGHT FLUSH MOUNT

P3184-09 Brushed Nickel

P3184-77 Forged Bronze

14-5/8" dia., 7-1/8" ht.

Two medium base lamps, each 100w max.

SEMI-FLUSH CONVERTIBLE

P3843-09 Brushed Nickel

P3843-77 Forged Bronze

Hanging and ceiling mount hardware included.

18" dia., 18-1/2" ht.,

Overall ht. w/chain 94"; wire 15'

Three medium base lamps, each 100w max.



P3184-77



P3184-09