

# Chadwick

## FINISHES

- Brushed Nickel - 009
- Matte Black - 031

## PAIR WITH

- Tobin
- Haven

Simple geometric forms and clean crisp lines form the Chadwick Collection. Opal glass shades visually calm the sharp edges of the boxy frames. This collection is perfect for minimalist settings in need of a subtle, feminine touch.

P400226-009

*Simple Geometric Form*



*Brushed Nickel*

*Opal Glass Shades*



P400225-009



P400226-009



P500274-009



P710089-009

## Chadwick

### THREE-LIGHT LINEAR CHANDELIER

**P400225-009** Brushed Nickel  
40" W., 12" D., 8-3/4" ht.,  
Overall ht. w/stem 59", wire 15'.  
Three medium base lamps,  
each 100w max.

### FOUR-LIGHT CHANDELIER

**P400226-009** Brushed Nickel  
21-5/8" sq., 12-7/8" ht.,  
Overall ht. w/stem 70", wire 15'.  
Four medium base lamps,  
each 100w max.

### ONE-LIGHT PENDANT


**P500274-009** Brushed Nickel  
10-1/2" sq., 14-3/4" ht.,  
Overall ht. w/stem 72", wire 10'.  
One medium base lamp,  
100w max.

### WALL SCONCE

**P710089-009** Brushed Nickel  
5-1/2" W., 18" ht.,  
Extends 5-3/8". H/CTR 14-1/4".  
One medium base lamp,  
100w max.

# Chadwick

P400226-031



*Clean Lines*

*Minimalist Design*

*Matte Black*

P400225-031



## THREE-LIGHT LINEAR CHANDELIER

**P400225-031** Matte Black  
40" W., 12" D., 8-3/4" ht.,  
Overall ht. w/stem 59", wire 15'.  
Three medium base lamps,  
each 100w max.

## FOUR-LIGHT CHANDELIER

**P400226-031** Matte Black  
21-5/8" sq., 12-7/8" ht.,  
Overall ht. w/stem 70", wire 15'.  
Four medium base lamps,  
each 100w max.


## ONE-LIGHT PENDANT

**P500274-031** Matte Black  
10-1/2" sq., 14-3/4" ht.,  
Overall ht. w/stem 72", wire 10'.  
One medium base lamp,  
100w max.

## WALL SCONCE

**P710089-031** Matte Black  
5-1/2" W., 18" ht.,  
Extends 5-3/8". H/CTR 14-1/4".  
One medium base lamp,  
100w max.

P400226-031



P500274-031



P710089-031

# Chadwick

---

Overscale geometric forms, clean, crisp lines accented by a soft glass shade are ideal for minimalist settings.

**P710089-009** Brushed Nickel

**P710089-031** Black

5-1/2" W., 18" ht.

Extends 5-3/8". H/CTR 14-1/4".

One medium base lamp,

100w max.



P710089-031



P710089-009

# Chadwick

---

Beautiful opal glass shades offer a simple contrast to the geometric styling of the boxy frames.

## **TWO-LIGHT FLUSH MOUNT**

**P350171-009** Brushed Nickel

**P350171-031** Black

15-3/8" sq., 5-1/2" ht.

Two medium base lamps,  
each 60w max.



P350171-009



P350171-031