

Trinity

FINISH

● Brushed Nickel - 09

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Markor
Classic
Applause

SEMI-FLUSH CONVERTIBLE

P3473-09 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 17-1/2" ht.,
Overall ht. w/chain 93"; wire 15'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3474-09 Brushed Nickel
18" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

LINEAR CHANDELIER

P4325-09 Brushed Nickel
26-1/2" W., 6-1/2" D., 28-1/4" ht.,
Overall ht. w/chain 103"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P4326-09 Brushed Nickel
19" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4328-09 Brushed Nickel
23" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.

ONE-LIGHT PENDANT

P5095-09 Brushed Nickel
18" dia., 9-1/2" ht.,
Overall ht. w/chain 85"; wire 15'.
One medium base lamp,
150w max.

MINI-PENDANT

P5096-09 Brushed Nickel
6-1/2" dia., 7" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp,
100w max.



P3474-09



P3473-09

shown hanging



P5095-09



P5096-09



P4328-09



P4326-09



P4325-09



P4365-09



P4329-09



P4324-09



P3807-09



P3806-09



P3190-09

Trinity

WALL BRACKET

P3190-09 Brushed Nickel
6-1/2" W., 7-1/2" ht.,
Extends 9" H/CTR 3-1/2".
One medium base lamp,
100w max.

TWO-LIGHT FOYER

P3806-09 Brushed Nickel
12" dia., 18" ht.,
Overall ht. w/chain 93"; wire 15'.
Two candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER

P3807-09 Brushed Nickel
13-1/2" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER

P4324-09 Brushed Nickel
19" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4329-09 Brushed Nickel
30" dia., 33" ht.,
Overall ht. w/chain 156"; wire 15'.
Nine medium base lamps,
each 100w max.

FIFTEEN-LIGHT CHANDELIER

P4365-09 Brushed Nickel
43-3/4" dia., 43-5/8" ht.,
Overall ht. w/chain 167"; wire 15'.
Fifteen medium base lamps,
each 75w max.

Trinity

FINISH

● Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

SEMI-FLUSH CONVERTIBLE

P3473-20 Antique Bronze
Hanging and ceiling mount hardware included.
16" dia., 17-1/2" ht.,
Overall ht. w/chain 93"; wire 15'.
Two medium base lamps,
each 100w max.

THREE-LIGHT PENDANT

P3474-20 Antique Bronze
Glass top diffuser.
18" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three medium base lamps,
each 100w max.

LINEAR CHANDELIER

P4325-20 Antique Bronze
26-1/2" W., 6-1/2" D., 28-1/4" ht.,
Overall ht. w/chain 103"; wire 15'.
Three medium base lamps,
each 100w max.

FOUR-LIGHT CHANDELIER

P4326-20 Antique Bronze
19" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Four medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4328-20 Antique Bronze
23" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Five medium base lamps,
each 100w max.

ONE-LIGHT PENDANT

P5095-20 Antique Bronze
18" dia., 9-1/2" ht.,
Overall ht. w/chain 85"; wire 15'.
One medium base lamp,
150w max.

MINI-PENDANT

P5096-20 Antique Bronze
6-1/2" dia., 7" ht.,
Overall ht. w/stem 64"; wire 10'.
One medium base lamp,
100w max.



P3474-20



P4328-20



P4365-20



P4324-20



P3473-20


shown hanging



P4326-20



P3807-20



P5095-20



P4325-20



P4329-20



P3806-20



P3190-20

Trinity

WALL BRACKET

P3190-20 Antique Bronze
6-1/2" W., 7-1/2" ht.,
Extends 9". H/CTR 3-1/2".
One medium base lamp,
100w max.

TWO-LIGHT FOYER

P3806-20 Antique Bronze
12" dia., 18" ht.,
Overall ht. w/chain 93"; wire 15'.
Two candelabra base lamps,
each 60w max.

THREE-LIGHT FOYER

P3807-20 Antique Bronze
13-1/2" dia., 24" ht.,
Overall ht. w/chain 99"; wire 15'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER

P4324-20 Antique Bronze
19" dia., 20" ht.,
Overall ht. w/chain 95"; wire 15'.
Three medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4329-20 Antique Bronze
30" dia., 33" ht.,
Overall ht. w/chain 156"; wire 15'.
Nine medium base lamps,
each 100w max.

FIFTEEN-LIGHT CHANDELIER

P4365-20 Antique Bronze
43-3/4" dia., 43-5/8" ht.,
Overall ht. w/chain 167"; wire 15'.
Fifteen medium base lamps,
each 75w max.

Trinity

Soft angles and curved lines in the Trinity collection are ideal for today's understated interiors. Etched glass shades curve outward.

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P3190-09 Brushed Nickel
P3190-15 Polished Chrome
P3190-20 Antique Bronze
 6-1/2" W., 7-1/2" ht.
 Extends 9". H/CTR 3-1/2".
 One medium base lamp,
 100w max.



P3190-15



P3193-15



P3191-15



P3192-15

TWO-LIGHT BATH

P3191-09 Brushed Nickel
P3191-15 Polished Chrome
P3191-20 Antique Bronze
 17-1/2" W., 8-1/8" ht.
 Extends 7-3/8". H/CTR 5-7/8".
 Two medium base lamps,
 each 100w max.



P3190-09



P3193-09



P3191-09



P3192-09

THREE-LIGHT BATH

P3192-09 Brushed Nickel
P3192-15 Polished Chrome
P3192-20 Antique Bronze
 24" W., 8-1/8" ht.
 Extends 7-3/8". H/CTR 5-7/8".
 Three medium base lamps,
 each 100w max.



P3190-20



P3193-20

FOUR-LIGHT BATH

P3193-09 Brushed Nickel
P3193-15 Polished Chrome
P3193-20 Antique Bronze
 33-1/4" W., 8-1/8" ht.
 Extends 7-3/8". H/CTR 5-7/8".
 Four medium base lamps,
 each 100w max.



P3191-20



P3192-20

All fixtures mount up or down.

Trinity

Gracefully exotic soft angles, curving lines and etched glass offer classic sophistication.

SEMI-FLUSH CONVERTIBLE

P3473-09 Brushed Nickel

P3473-20 Antique Bronze

Hanging and ceiling mount hardware included.

16" dia., 14-3/4" ht.

Two medium base lamps, each 100w max.



P3473-09



P3473-20

ONE-LIGHT FLUSH MOUNT

P3475-09 Brushed Nickel

P3475-20 Antique Bronze

12-1/2" dia., 7-3/8" ht.

One medium base lamp, 100w max.



P3475-09



P3475-20

TWO-LIGHT FLUSH MOUNT

P3476-09 Brushed Nickel

P3476-20 Antique Bronze

15" dia., 7-1/4" ht.

Two medium base lamps, each 60w max.



P3476-09



P3476-20