



In Perfect Balance

Mix it up in a formal dining room by placing two upholstered armchairs at the head and foot of the table, disrupting the scale but still bringing a sense of balance to the room. Beige is anything but boring in a color scheme that incorporates light colors using fun wall art and curvy chairs. The Winslett chandelier adds to the room's charm with its perfectly imperfect seeded glass shades and sweeping arms.

Winslett



P400207-009

SEMI-FLUSH CONVERTIBLE
P350153-009 Brushed Nickel
 Hanging and ceiling mount hardware included
 13-3/4" dia., 11-7/8" ht.,
 Overall ht. w/chain 50-1/2", wire 10'.
 Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER
P400206-009 Brushed Nickel
 27-1/8" dia., 21-1/8" ht.,
 Overall ht. w/chain 95-1/2", wire 15'.
 Five medium base lamps, each 60w max.



P400208-009



P500240-009

SIX-LIGHT OVAL LINEAR CHANDELIER
P400207-009 Brushed Nickel
 34-1/8" W., 24-3/4" D., 21-1/4" ht.,
 Overall ht. w/chain 96", wire 15'.
 Six medium base lamps, each 60w max.

NINE-LIGHT CHANDELIER
P400208-009 Brushed Nickel
 34-1/8" dia., 31-5/8" ht.,
 Overall ht. w/chain 155", wire 15'.
 Nine medium base lamps, each 60w max.

MINI-PENDANT
P500238-009 Brushed Nickel
 9-1/4" dia., 15-7/8" ht.,
 Overall ht. w/chain 80", wire 10'.
 One medium base lamp, 60w max.



P400206-009



P500239-009

THREE-LIGHT PENDANT
P500239-009 Brushed Nickel
 12-7/8" dia., 17-1/8" ht.,
 Overall ht. w/chain 91-1/2", wire 15'.
 Three candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER
P500240-009 Brushed Nickel
 19-5/8" sq., 25" ht.,
 Overall ht. w/chain 99-1/2", wire 15'.
 Four candelabra base lamps, each 60w max.



P350153-009



P350153-009
 shown as semi-flush



P500238-009

All fixtures shown with F4B10LED927/JA8 or F7ST19DLED927/JA8 LED lamps, not included.

Winslett

FINISHES

- Brushed Nickel - 009
- Matte Black - 031

ALSO IN

- Bath
- Close-to-Ceiling

PAIR WITH

- Passage
- Greyson

P400206-031



Modern Personality

Seeded Glass Shades

Graceful Arms

Immerse yourself in a home atmosphere primed for relaxation and inspired thinking with the beautiful imperfection of the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces graceful arms and clean crisp lines. Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional collection.



P400207-031



P400208-031



P500240-031



P400206-031



P500239-031



P350153-031



P350153-031
shown as semi-flush



P500238-031

Winslett

SEMI-FLUSH CONVERTIBLE

P350153-031 Matte Black
Hanging and ceiling mount hardware included
13-3/4" dia., 11-7/8" ht.,
Overall ht. w/chain 50-1/2", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400206-031 Matte Black
27-1/8" dia., 21-1/8" ht.,
Overall ht. w/chain 95-1/2", wire 15'.
Five medium base lamps, each 60w max.

SIX-LIGHT OVAL LINEAR CHANDELIER

P400207-031 Matte Black
34-1/8" W., 24-3/4" D., 21-1/4" ht.,
Overall ht. w/chain 96", wire 15'.
Six medium base lamps, each 60w max.

NINE-LIGHT CHANDELIER

P400208-031 Matte Black
34-1/8" dia., 31-5/8" ht.,
Overall ht. w/chain 155", wire 15'.
Nine medium base lamps, each 60w max.

MINI-PENDANT

P500238-031 Matte Black
9-1/4" dia., 15-7/8" ht.,
Overall ht. w/chain 80", wire 10'.
One medium base lamp, 60w max.

THREE-LIGHT PENDANT

P500239-031 Matte Black
12-7/8" dia., 17-1/8" ht.,
Overall ht. w/chain 91-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER

P500240-031 Matte Black
19-5/8" sq., 25" ht.,
Overall ht. w/chain 99-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

All fixtures shown with F4B10LED927/JA8 or F7ST19DLED927/JA8 LED lamps, not included.

Winslett

FINISHES

- Brushed Nickel - 009
- Black - 031

ALSO IN

- Collections
- Close-to-Ceiling

P300273-009

Immerse yourself in a bathroom that is primed for relaxation with the beautiful imperfection of the Winslett Collection. Savor this fresh take on a classic light choice as your gaze traces its clean crisp lines. Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases that adds an unexpected, but welcomed dash of modern personality to this clean, traditional collection.



Modern

Clean Lines

Seeded Glass Shades

Winslett

ONE-LIGHT BATH

P300272-031 Black
4-3/4" W., 9-1/2" ht.
Extends 6-3/4". H/CTR 4-3/4".
One medium base lamp,
60w max.

TWO-LIGHT BATH

P300273-031 Black
14-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.

THREE-LIGHT BATH

P300274-031 Black
23-3/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Three medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300275-031 Black
33-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Four medium base lamps,
each 60w max.

*All fixtures mount up or down.
Shown with P7825-01 vintage lamps,
not included.*

ONE-LIGHT BATH

P300272-009 Brushed Nickel
4-3/4" W., 9-1/2" ht.
Extends 6-3/4". H/CTR 4-3/4".
One medium base lamp,
60w max.



P300272-009

TWO-LIGHT BATH

P300273-009 Brushed Nickel
14-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Two medium base lamps,
each 60w max.



P300273-009

THREE-LIGHT BATH

P300274-009 Brushed Nickel
23-3/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Three medium base lamps,
each 60w max.



P300274-009

FOUR-LIGHT BATH

P300275-009 Brushed Nickel
33-1/4" W., 7-1/4" ht.
Extends 7-3/8". H/CTR 4-1/4".
Four medium base lamps,
each 60w max.



P300275-009

*All fixtures mount up or down.
Shown with P7825-01 vintage lamps,
not included.*



P300273-031



P300272-031



P300274-031



P300275-031

Winslett

Perfectly imperfect lightly seeded glass shades rest in shiny pedestal light bases.

SEMI-FLUSH CONVERTIBLE

P350153-009 Brushed Nickel

P350153-031 Black

Hanging and ceiling mount hardware included.

13-3/4" dia., 11-7/8" ht.,

Overall ht. w/chain 50-1/2", wire 10'.

Three candelabra base lamps, each 60w max.



P350153-031



P350153-009