

Mast

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN


- Bath
- Close-to-Ceiling
- Sconces

PAIR WITH

- Alexa
- Chadwick
- Hemsworth

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to the linear pendant and mini-pendant. An oversized cylindrical frame banded top and bottom with faux wood accents gives a warm organic feel to the flush mount fixture.

P400190-020



Subtly Alluring

Faux Wood Accents

Modern meets Farmhouse



P400190-009

Mast

FOUR-LIGHT LINEAR CHANDELIER

P400190-009 Brushed Nickel
P400190-020 Antique Bronze
 38" W., 4-7/8" D., 14-3/4" ht.,
 Overall ht. w/stem 80-1/2"; wire 15'.
 Four medium base lamps,
 each 100w max.

MINI-PENDANT

P500192-009 Brushed Nickel
P500192-020 Antique Bronze
 6-1/4" dia., 14" ht.,
 Overall ht. w/stem 80"; wire 10'.
 One medium base lamp,
 100w max.



P500192-009



P500192-020



P400190-020

Mast

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

- Collections
- Close-to-Ceiling

P300216-009

Mast combines a clean, modern design expression with faux wood accents for a modern-meets-farmhouse approach to lighting. The contrast of warm wood paired with sleek metallic lines and double glass shades offers a subtly alluring, Zen look to these vanity fixtures. An oversized cylindrical frame banded top and bottom in Brushed Nickel or Antique Bronze and trimmed with faux wood accents gives a warm organic feel to the flush mount fixture.

*Modern Meets
Farmhouse*



*Double Glass
Shades*

Faux Wood Accents

ONE-LIGHT BATH

P710015-009 Brushed Nickel
5" W., 13" ht.,
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300216-009 Brushed Nickel
13-7/8" W., 7-5/8" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300217-009 Brushed Nickel
24" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300218-009 Brushed Nickel
33-7/8" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.



P710015-009



P300218-009



P300216-009



P300217-009



P710015-020



P300216-020



P300217-020



P300218-020

Mast

ONE-LIGHT BATH

P710015-020 Antique Bronze
5" W., 13" ht.,
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300216-020 Antique Bronze
13-7/8" W., 7-5/8" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300217-020 Antique Bronze
24" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300218-020 Antique Bronze
33-7/8" W., 7-3/4" ht.,
Extends 6-1/4". H/CTR 5-1/4".
Four medium base lamps,
each 100w max.

All fixtures mount up or down.

All fixtures mount up or down.

Mast

A faux wood backplate blends with a clean, modern pediment and double glass shade.

P710015-009 Brushed Nickel
P710015-020 Antique Bronze
5" W., 13" ht.
Extends 6-3/8". H/CTR 6-1/2".
One medium base lamp,
100w max.



P710015-009



P710015-020

Mast

Faux wood accents a circular metal frame that secures an etched glass shade.

TWO-LIGHT FLUSH MOUNT

P350144-009 Brushed Nickel

P350144-020 Antique Bronze

13" dia., 5-1/4" ht.

Two medium base lamps,
each 60w max.



P350144-020



P350144-009