

Tilley

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

- Bath
- Close-to-Ceiling

PAIR WITH

- Briarwood
- Gulliver
- Hemsworth


P400074-009

Rustic and vintage décor is a popular trend that can transform a home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet Industrial style.

Rustic meets Vintage Decor

Mesh Shades

Faux-painted Wooden Rim



P400074-020



P400073-020



P500078-020



P500079-020

Tilley

THREE-LIGHT CHANDELIER

P400073-009 Brushed Nickel
20" dia., 15-1/4" ht.,
Overall ht. w/chain 90-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400074-009 Brushed Nickel
24" dia., 16-7/8" ht.,
Overall ht. w/chain 92", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT

P500078-009 Brushed Nickel
8" dia., 7-1/2" ht.,
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P500079-009 Brushed Nickel
16" dia., 10-7/8" ht.,
Overall ht. w/stem 77", wire 10'.
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included.



Focus on Wow

When designing your kitchen, think about which wow factor to focus on.

1

A Modern Farmhouse look is complete when the choice is made to go with bold lighting against a clean, neutral background.

2

The iron mesh shade and painted wood trim of the Tilley pendants join together the kitchen's farmhouse-style.

3

Open shelving and the kitchen vent hood finish the look with symmetry and harmony.

Tilley

P400074-009



THREE-LIGHT CHANDELIER
P400073-020 Antique Bronze
20" dia., 15-1/4" ht.,
Overall ht. w/chain 90-1/2", wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER
P400074-020 Antique Bronze
24" dia., 16-7/8" ht.,
Overall ht. w/chain 92", wire 15'.
Five medium base lamps,
each 100w max.

MINI-PENDANT
P500078-020 Antique Bronze
8" dia., 7-1/2" ht.,
Overall ht. w/stem 73-1/2", wire 10'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT
P500079-020 Antique Bronze
16" dia., 10-7/8" ht.,
Overall ht. w/stem 77", wire 10'.
Three medium base lamps,
each 60w max.

All fixtures shown with P7825-01 vintage lamps, not included.

P400073-009



P500078-009



P500079-009



Tilley

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ALSO IN

- Collections
- Close-to-Ceiling

P300044-020

Rustic and vintage décor is a popular trend that can help transform your home into a nostalgic retreat. Tilley features warehouse style shades formed from metal mesh that merge with a faux-painted, wooden rim for an artful yet industrial style.



ONE-LIGHT BATH

P300042-009 Brushed Nickel
P300042-020 Antique Bronze
 6-3/8" W., 8-1/2" ht.
 Extends 8-1/4". H/CTR 4-1/4".
 One medium base lamp,
 100w max.



P300042-020



P300044-020

TWO-LIGHT BATH

P300043-009 Brushed Nickel
P300043-020 Antique Bronze
 15" W., 8-3/8" ht.
 Extends 8-3/8". H/CTR 4-1/4".
 Two medium base lamps,
 each 100w max.



P300043-020



P300043-009

THREE-LIGHT BATH

P300044-009 Brushed Nickel
P300044-020 Antique Bronze
 23-3/8" W., 8-3/8" ht.
 Extends 8-3/8". H/CTR 4-1/4".
 Three medium base lamps,
 each 100w max.



P300042-009



P300044-009

All fixtures mount up or down.
 Shown with P7825-01 vintage lamps,
 not included. See page 824.

Tilley

Warehouse-style mesh shades merge with a faux-painted, wooden rim.

THREE-LIGHT FLUSH MOUNT

P350091-009 Brushed Nickel

P350091-020 Antique Bronze

16" dia., 9-7/8" ht.

Three medium base lamps,
each 60w max.

*All fixtures shown with P7825-01 vintage
lamps, not included.*



P350091-020



P350091-009