

# Conestee

P500094-141



*Dual Tone Finish*

## FINISHES

- Galvanized - 141
- Graphite - 143

## PAIR WITH

- Fontayne
- Calhoun

Truly eye-catching yet classic, the Conestee collection features graceful orb shapes uniquely finished in complementing dual-tone, hand-painted metalwork. Exposed bulbs are tucked into vintage style light bases offering a look that is ideal for Farmhouse and Industrial settings, while its hand-painted finishes in Galvanized and weathered tones easily complement Coastal and Rustic spaces.

*Spherical Design*

*Rotating Rings*



P500093-143



P500092-143



P500094-143

# Conestee

## MINI-PENDANT

**P500092-143** Graphite  
12" dia., 14" ht.,  
Overall ht. w/chain 89", wire 10'.  
One medium base lamp,  
60w max.

## THREE-LIGHT PENDANT

**P500093-143** Graphite  
21-1/4" dia., 24" ht.,  
Overall ht. w/chain 99", wire 15'.  
Three medium base lamps,  
each 60w max.

## SIX-LIGHT PENDANT

**P500094-143** Graphite  
28" dia., 30-3/4" ht.,  
Overall ht. w/chain 106", wire 15'.  
Six medium base lamps,  
each 60w max.

*All fixtures shown with P7825-01 vintage lamps, not included.*



P500094-141



P500093-141



P500092-141

# Conestee

## MINI-PENDANT

**P500092-141** Galvanized  
12" dia., 14" ht.,  
Overall ht. w/chain 89", wire 10'.  
One medium base lamp,  
60w max.

## THREE-LIGHT PENDANT

**P500093-141** Galvanized  
21-1/4" dia., 24" ht.,  
Overall ht. w/chain 99", wire 15'.  
Three medium base lamps,  
each 60w max.

## SIX-LIGHT PENDANT

**P500094-141** Galvanized  
28" dia., 30-3/4" ht.,  
Overall ht. w/chain 106", wire 15'.  
Six medium base lamps,  
each 60w max.

*All fixtures shown with P7825-01 vintage lamps, not included.*