

# Hansford

**FINISHES**

- Antique Bronze - 020
- Polished Nickel - 104

**ALSO IN**

- Bath
- Close-to-Ceiling

**PAIR WITH**

- Archives
- Saluda
- Judson

P400147-020

Hansford features a clear, spherical shade paired with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the elegant nickel finish to bring tranquility to your home with Hansford's classic style. Featuring a clean and precise design with generous scale. Hansford lends itself to Farmhouse, Coastal or Industrial interiors.



*Antique Bronze*

*Brass Accents*

*Clear Spherical Shades*



P400147-104



P400147-020



P400146-104



P400146-020



P400146-020  
shown as  
ceiling mount

## Hansford

**THREE-LIGHT CHANDELIER**

**P400146-020** Antique Bronze  
**P400146-104** Polished Nickel  
Hanging and ceiling mount  
hardware included.  
21" dia., 16-7/8" ht.,  
Overall ht. w/stem 85", wire 12'.  
Three medium base lamps,  
each 100w max.

**FIVE-LIGHT CHANDELIER**

**P400147-020** Antique Bronze  
**P400147-104** Polished Nickel  
25" dia., 19-1/8" ht.,  
Overall ht. w/stem 87", wire 12'.  
Five medium base lamps,  
each 100w max.

*All fixtures shown with  
F8.5A19DLED927/JA8 LED lamps,  
not included.*

# Hansford

## FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

## ALSO IN

- Collections
- Close-to-Ceiling

P300051-020

Hansford features a clear, spherical shade with vintage style metal fittings. Choose the antique style bronze and brass combinations, or the gleaming nickel finish to bring tranquility to your home with Hansford's classic style.



### ONE-LIGHT BATH

**P300049-020** Antique Bronze  
6-1/2" W., 9-1/2" ht.  
Extends 7-1/4". H/CTR 6-7/8".  
One medium base lamp,  
100w max.



P300049-020

### TWO-LIGHT BATH

**P300050-020** Antique Bronze  
15-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Two medium base lamps,  
each 100w max.



P300050-020

### THREE-LIGHT BATH

**P300051-020** Antique Bronze  
24-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Three medium base lamps,  
each 100w max.



P300050-020

### FOUR-LIGHT BATH

**P300052-020** Antique Bronze  
33-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Four medium base lamps,  
each 100w max.



P300051-020

All fixtures mount up or down.  
Shown with P7825-01 vintage lamps,  
not included.

# Hansford

### ONE-LIGHT BATH

**P300049-104** Polished Nickel  
6-1/2" W., 9-1/2" ht.  
Extends 7-1/4". H/CTR 6-7/8".  
One medium base lamp,  
100w max.



P300052-104

### TWO-LIGHT BATH

**P300050-104** Polished Nickel  
15-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Two medium base lamps,  
each 100w max.



P300049-104

### THREE-LIGHT BATH

**P300051-104** Polished Nickel  
24-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Three medium base lamps,  
each 100w max.



P300051-104

### FOUR-LIGHT BATH

**P300052-104** Polished Nickel  
33-1/2" W., 10-7/8" ht.  
Extends 7-1/4". H/CTR 8-1/4".  
Four medium base lamps,  
each 100w max.



P300050-104

All fixtures mount up or down.



Featuring Hansford  
Image: Tresidio Homes

# Hansford

---

Vintage-style metal fittings capture a clear, spherical shade for a precise design with generous scale.



P350046-104



P350046-020

**ONE-LIGHT FLUSH MOUNT**  
**P350046-020** Antique Bronze  
**P350046-104** Polished Nickel  
10" dia., 12-5/8" ht.  
One medium base lamp,  
100w max.