

Kempsey

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

PAIR WITH

- Tally
- Archie
- Alexa

P350110-020

For Farmhouse styling with a twist, look no further than Kempsey, whose inside-out design showcases stylish charm. A structural metal frame on the outside captures the textured linen shade within its arms, so that the structure becomes part of the design. The shade has an inner transparent backing, so its texture is visible from inside out. A wall bracket featuring a multi-directional arm holding the shade completes the collection.

Modern Farmhouse

Structural Metal Frame



Visible Shade Texture



P350110-020
shown hanging



P350110-020
shown as ceiling mount



P500139-020



P500138-020



P710045-020

Kempsey

SEMI-FLUSH CONVERTIBLE

P350110-020 Antique Bronze
Hanging and ceiling mount
hardware included
21-3/4" dia., 11" ht.,
Overall ht. w/stem 76"; wire 10'.
Three medium base lamps,
each 60w max.

ONE-LIGHT PENDANT

P500138-020 Antique Bronze
11-3/4" dia., 9" ht.,
Overall ht. w/stem 76"; wire 10'.
One medium base lamp,
75w max.

THREE-LIGHT PENDANT

P500139-020 Antique Bronze
17-3/4" dia., 21-3/8" ht.,
Overall ht. w/stem 87-1/2"; wire 10'.
Three medium base lamps,
each 60w max.

ONE-LIGHT ADJUSTABLE WALL BRACKET

P710045-020 Antique Bronze
12" dia., 19-3/4" ht.,
Extends 23-5/8".
One medium base lamp,
75w max.
On/off rotary switch on backplate.

Kempsey

P350110-009



Classic Transitional

Stylish Charm

Warm and Inviting

P350110-009
shown hanging



P500138-009



SEMI-FLUSH CONVERTIBLE
P350110-009 Brushed Nickel
Hanging and ceiling mount
hardware included
21-3/4" dia., 11" ht.,
Overall ht. w/stem 76"; wire 10'.
Three medium base lamps,
each 60w max.

ONE-LIGHT PENDANT
P500138-009 Brushed Nickel
11-3/4" dia., 9" ht.,
Overall ht. w/stem 76"; wire 10'.
One medium base lamp,
75w max.

THREE-LIGHT PENDANT
P500139-009 Brushed Nickel
17-3/4" dia., 21-3/8" ht.,
Overall ht. w/stem 87-1/2"; wire 10'.
Three medium base lamps,
each 60w max.

**ONE-LIGHT ADJUSTABLE
WALL BRACKET**
P710045-009 Brushed Nickel
12" dia., 19-3/4" ht.,
Extends 23-5/8".
One medium base lamp,
75w max.
On/off rotary switch on backplate.

P350110-009
shown as ceiling mount



P500139-009



P710045-009

Kempsey

A smooth, arced arm holds the small, curved bar that supports an elegant fabric shade.

P710045-009 Brushed Nickel

P710045-020 Antique Bronze

Adjustable arm.

On/off rotary switch on backplate.

12" dia., 19-3/4" ht.,

Extends 23-5/8".

One medium base lamp,

75w max.



P710045-020



P710045-009