

Cascadia

FINISH

- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Bath
Close-to-Ceiling

PAIR WITH

Ratio
Tally

WALL BRACKET

P2146-15 Polished Chrome
5-7/8" W., 8" ht.,
Extends 6-1/2". H/CTR 5-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3644-15 Polished Chrome
Hanging and ceiling mount
hardware included.
14" dia., 10" ht.,
Overall ht. w/chain 49"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4612-15 Polished Chrome
21" dia., 16-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4613-15 Polished Chrome
26" dia., 10-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4614-15 Polished Chrome
30" dia., 21-7/8" ht.,
Overall ht. w/chain 88"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P5066-15 Polished Chrome
5-7/8" dia., 6-3/4" ht.,
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.



Cascadia

WALL BRACKET

P2146-20 Antique Bronze
5-7/8" W., 8" ht.,
Extends 6-1/2". H/CTR 5-1/2".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P3644-20 Antique Bronze
Hanging and ceiling mount
hardware included.
14" dia., 10" ht.,
Overall ht. w/chain 49"; wire 10'.
Two medium base lamps,
each 100w max.

THREE-LIGHT CHANDELIER

P4612-20 Antique Bronze
21" dia., 16-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P4613-20 Antique Bronze
26" dia., 10-3/4" ht.,
Overall ht. w/stem 83"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P4614-20 Antique Bronze
30" dia., 21-7/8" ht.,
Overall ht. w/chain 88"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P5066-20 Antique Bronze
5-7/8" dia., 6-3/4" ht.,
Overall ht. w/stem 73"; wire 10'.
One medium base lamp,
100w max.

Cascadia

Overscale frames and etched glass shades offer substance in a sleek frame.

FINISHES

- Polished Chrome - 15
- Antique Bronze - 20

ALSO IN

Collections
Close-to-Ceiling

ONE-LIGHT BATH

P2146-15 Polished Chrome

P2146-20 Antique Bronze


5-7/8" W., 8" ht.

Extends 6-1/2". H/CTR 5-1/2".

One medium base lamp,
100w max.



P2146-15



P2147-15



P2148-15

TWO-LIGHT BATH

P2147-15 Polished Chrome

P2147-20 Antique Bronze

16" W., 8" ht.

Extends 6-1/2". H/CTR 5-5/8".

Two medium base lamps,
each 100w max.



P2149-15

THREE-LIGHT BATH

P2148-15 Polished Chrome

P2148-20 Antique Bronze

24-1/8" W., 8" ht.

Extends 6-1/2". H/CTR 5-5/8".

Three medium base lamps,
each 100w max.



P2146-20



P2147-20

FOUR-LIGHT BATH

P2149-15 Polished Chrome

P2149-20 Antique Bronze

32" W., 8" ht.

Extends 6-1/2". H/CTR 5-5/8".

Four medium base lamps,
each 100w max.



P2148-20



P2149-20

All fixtures mount up or down.

Cascadia



P3633-20



P3633-15



P3644-20



P3644-15

Smooth forms and etched glass produce a beautiful, modern gaslight effect.

TWO-LIGHT FLUSH MOUNT

P3633-15 Polished Chrome

P3633-20 Antique Bronze

14" dia., 6" ht.

Two medium base lamps,
each 60w max.

SEMI-FLUSH CONVERTIBLE

P3644-15 Polished Chrome

P3644-20 Antique Bronze

Hanging and ceiling mount
hardware included.

14" dia., 10" ht.,

Overall ht. w/chain 49"; wire 10'.

Two medium base lamps,
each 100w max.